

6.0 RETURN LOSS:

1MHz TO 30MHz	: 18dB MIN.
60MHz TO 80MHz	: 12dB MIN.

7.0 VOLTAGE WITHSTAND:

(J1, J2) TO (P1, P2)	: 1500 VAC
(J3, J6) TO (P8,P7)	: 1500 VAC

8.0 INSERTION LOSS:

100KHz TO 100MHz	1.1 dB MAX
------------------	------------

9.0 RISE TIME:

OUTPUT VOLTAGE = 1 V peak	3.0 nS MAX
PULSE WIDTH= 112nS	3.0 nS MAX

10.0 CROSS TALK:

1MHz TO 100MHz	35 dB TYP
----------------	-----------

11.0 COMMON TO COMMON MODE ATTENUATION:

1MHz TO 100MHz	45dB TYP
----------------	----------

InNet Technologies Inc.

<http://www.innet-tech.com>

Stewart Connector Systems

<http://www.stewartconnector.com>

SHEET



2 of 4

DRAWING NO.

SI-10015

REV.

03




NOTES:

- TOLERANCES COMPLY WITH F.C.C. DIMENSION REQUIREMENTS
- DIMENSIONS SHOWN WITH "*" TO BE CENTRAL ABOUT CENTER LINE
- "***" ON DIMENSION INDICATES HIGHEST POINT OF BEAM
- DIMENSIONS SHOWN ARE SUBJECT TO CHANGE WITHOUT NOTICE
- PIN NOT ELECTRICALLY CONNECTED MAYBE OMITTED. SEE ELECTRICAL DRAWING FOR OMITTED PINS.

AVAILABLE WITH:

- STANDARD 50 MICRO-INCH SELECTIVE GOLD PLATING (30 AVAILABLE UPON REQUEST)

Ref: SS-668804S-A-PG4 -BC



P.C.B. RECOMMENDED HOLE LAYOUT
SEEN FROM COMPONENT SIDE
TOLERANCE $\pm .003$ [0.08] UNLESS OTHERWISE SPECIFIED

CT720035X1/24-001701

InNet Technologies Inc.

<http://www.innet-tech.com>


Stewart Connector Systems

<http://www.stewartconnector.com>


SHEET
3 of 4

DRAWING NO.
SI-10015


REV.
01



PANEL GROUNDING BEAM DEFLECTION
S.O.S. = SUGGESTED OPENING SIZE



THE SUGGESTED PANEL OPENING IS INTENDED TO GIVE THE USER THE ABILITY TO HAVE REASONABLE JACK / PANEL CLEARANCES YET MAINTAIN RELIABLE GROUNDING CAPABILITY. THESE VARIABLES CAN BE ADJUSTED IN EITHER DIRECTION BUT MAY CARRY SOME CONSEQUENCES IN THE FORM OF LOWER MATING FORCES OR TIGHTER ASSEMBLY TOLERANCES. FORCE VALUES ON THE GRAPH ARE GENERAL AVERAGES TAKEN AT THE POINT OF CONTACT SHOWN ABOVE. THE SUGGESTED PANEL OPENING INCLUDES APPROXIMATELY .020 CLEARANCE ON THE SIDES AND TOP AND .005 ON THE BOTTOM.



CT720035X1/24-001701

InNet Technologies Inc.

<http://www.innet-tech.com>

Stewart Connector Systems

<http://www.stewartconnector.com>

SHEET
4 of 4

DRAWING NO. SI-10015 REV. 01