

	TOTAL PIN LENGTH		TAIL LENGTH		MATING LENGTH		POLARIZED POSITION	LF OPTION
PRODUCT	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H		
NUMBER	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC		
79275-YYY	0.450	11.43	0.120	3.05	0.230	5.84	2	NOTE 1,4
79285-YYY	0.538	13.67	0.120	3.05	0.318	8.08	2	
79430-YYY	0.538	13.67	0.120	3.05	0.318	8.08	3	
86613-YYY	0.422	10.72	0.130	3.30	0.192	4.88	2	
86614-YYY	0.510	12.95	0.130	3.30	0.280	7.11	2	
87079-YYY	0.450	11.43	0.120	3.05	0.230	5.84	2 & 4	

NOTES:

① PART NUMBER OPTIONS:

FOR PRODUCT GEOMETRY, LEAD FREE AND GENERAL INFORMATION
SEE DRAWING 93197 (e.i. 79275-YYYHLF NEW LF NUMBER)

PACKAGING:
PACKAGED IN POLYBAGS ONLY

LEAD FREE OPTION:

ADD "HLF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE
OPTION.

NUMBER OF POSITIONS:

ANY NUMBER OF POSITION FROM 3 THRU 36.

XXXX-YYYHLF

- LEAD FREE OPTION
- HIGH TEMPERATURE PLASTIC
- NO. OF POSITIONS
- PIN PLATING
- BASE PART NUMBER


3. PART NUMBERS WITH "H" SUFFIX WILL WITHSTAND EXPOSURE
TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN
WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

PART NUMBERS WITHOUT "H" SUFFIX WILL WITHSTAND EXPOSURE
TO 260°C PEAK TEMPERATURE FOR WAVE SOLDER PROCESS.

④ THESE PRODUCTS MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

5. PLATING OPTIONS:

MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.



mat'l. code				surface	tolerance	projection	product family
-				ISO 1302 ✓	ISO 406 ISO 1101	⊕	BERGSTIK
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM	title
H	v30710	DEW	4/16/93	angles	linear		
J	v41572	HTB	10/24/94				BERGSTIK® II HEADER
K	v20791	GIP	4/24/02	0'±2'		scale 1:1	.100 SR POLARIZED
L	v21903	SA	6/06/03	dr	T.BREWBAKER	10/24/94	dwg no
M	M05-0027	MHT	4/21/05	enr	T. HANNA	10/24/94	
N	M06-0269	AEA	7/19/06	chr	T. HANNA	10/24/94	sheet 1 of 1 size
				appd	T. HANNA	10/24/94	A3
sheet	revision	N					type
index	sheet	1					Product Customer Drawing