





## Glass Passivated Single-Phase Bridge Rectifier



Case Style GBPC6

## FEATURES

- UL recognition file number E54214
- Ideal for printed circuit boards
- Typical  $I_R$  less than 0.5  $\mu A$
- High surge current capability
- High case dielectric strength 1500  $V_{RMS}$
- Solder dip 275 °C max. 10 s, per JESD 22-B106
- Material categorization: For definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)

RoHS  
COMPLIANT

## PRIMARY CHARACTERISTICS

|                        |                                                 |
|------------------------|-------------------------------------------------|
| Package                | GBPC6                                           |
| $I_{F(AV)}$            | 6 A                                             |
| $V_{RRM}$              | 50 V, 100 V, 200 V, 400 V, 600 V, 800 V, 1000 V |
| $I_{FSM}$              | 175 A                                           |
| $I_R$                  | 5 $\mu A$                                       |
| $V_F$ at $I_F = 3.0$ A | 1.0 V                                           |
| $T_J$ max.             | 150 °C                                          |
| Diode variations       | Quad                                            |

## TYPICAL APPLICATIONS

General purpose use in AC/DC bridge full wave rectification for power supply, home appliances, office equipment, industrial automation applications.

## MECHANICAL DATA

**Case:** GBPC6

Molding compound meets UL 94 V-0 flammability rating  
Base P/N-E4 - RoHS-compliant, commercial grade

**Terminals:** Silver plated leads, solderable per J-STD-002 and JESD22-B102

**Polarity:** As marked, positive lead by beveled corner

**Mounting Torque:** 10 cm·kg (8.8 in·lbs) maximum

**Recommended Torque:** 5.7 cm·kg (5 in·lbs) maximum

MAXIMUM RATINGS ( $T_A = 25$  °C unless otherwise noted)

| PARAMETER                                                                                                                                | SYMBOL                            | GBPC 6005     | GBPC 601 | GBPC 602 | GBPC 604 | GBPC 606 | GBPC 608 | GBPC 610 | UNIT             |
|------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|---------------|----------|----------|----------|----------|----------|----------|------------------|
| Maximum repetitive peak reverse voltage                                                                                                  | V <sub>RRM</sub>                  | 50            | 100      | 200      | 400      | 600      | 800      | 1000     | V                |
| Maximum RMS bridge input voltage                                                                                                         | V <sub>RMS</sub>                  | 35            | 70       | 140      | 280      | 420      | 560      | 700      | V                |
| Maximum DC blocking voltage                                                                                                              | V <sub>DC</sub>                   | 50            | 100      | 200      | 400      | 600      | 800      | 1000     | V                |
| Maximum average forward rectified output current at<br>T <sub>C</sub> = 50 °C <sup>(1)(2)</sup><br>T <sub>A</sub> = 40 °C <sup>(3)</sup> | I <sub>F(AV)</sub>                | 6.0           |          |          |          |          |          |          | A                |
|                                                                                                                                          |                                   | 3.0           |          |          |          |          |          |          |                  |
| Peak forward surge current single sine-wave superimposed on rated load                                                                   | I <sub>FSM</sub>                  | 175           |          |          |          |          |          |          | A                |
| Rating for fusing (t = 8.3 ms)                                                                                                           | I <sup>2</sup> t                  | 127           |          |          |          |          |          |          | A <sup>2</sup> s |
| Operating junction and storage temperature range                                                                                         | T <sub>J</sub> , T <sub>STG</sub> | - 55 to + 150 |          |          |          |          |          |          | °C               |

## Notes

- (1) Bolt down on heat-sink with silicone thermal compound between bridge and mounting surface for maximum heat transfer with #6 screw
- (2) Unit mounted on 5.5" x 6.0" x 0.11" thick (14 cm x 15 cm x 0.3 cm) aluminum plate
- (3) Unit mounted on PCB at 0.375" (9.5 mm) lead length with 0.5" x 0.5" (12 mm x 12 mm) copper pads

**ELECTRICAL CHARACTERISTICS** ( $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)

| PARAMETER                                                         | SYMBOL         | TEST CONDITIONS         | GBPC 6005 | GBPC 601 | GBPC 602 | GBPC 604 | GBPC 606 | GBPC 608 | GBPC 610 | UNIT |
|-------------------------------------------------------------------|----------------|-------------------------|-----------|----------|----------|----------|----------|----------|----------|------|
| Maximum instantaneous forward voltage drop per diode              | V <sub>F</sub> | 3.0 A                   | 1.0       |          |          |          |          |          |          | V    |
| Maximum DC reverse current at rated DC blocking voltage per diode | I <sub>R</sub> | T <sub>A</sub> = 25 °C  | 5.0       |          |          |          |          |          |          | μA   |
|                                                                   |                | T <sub>A</sub> = 125 °C | 500       |          |          |          |          |          |          |      |
| Typical junction capacitance per diode                            | C <sub>J</sub> | 4.0 V, 1 MHz            | 186       |          |          |          | 90       |          |          | pF   |

**THERMAL CHARACTERISTICS** ( $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)

| PARAMETER                      | SYMBOL           | GBPC 6005 | GBPC 601 | GBPC 602 | GBPC 604 | GBPC 606 | GBPC 608 | GBPC 610 | UNIT |
|--------------------------------|------------------|-----------|----------|----------|----------|----------|----------|----------|------|
| Typical thermal resistance (1) | R <sub>θJA</sub> | 22        |          |          |          |          |          |          | °C/W |
|                                | R <sub>θJC</sub> | 7.3       |          |          |          |          |          |          |      |

**Notes**

- (1) Bolt down on heat-sink with silicone thermal compound between bridge and mounting surface for maximum heat transfer with #6 screw  
(2) Unit mounted on 5.5" x 6.0" x 0.11" thick (14 cm x 15 cm x 0.3 cm) aluminum plate  
(3) Unit mounted on PCB at 0.375" (9.5 mm) lead length with 0.5" x 0.5" (12 mm x 12 mm) copper pads

**ORDERING INFORMATION** (Example)

| PREFERRED P/N | UNIT WEIGHT (g) | PACKAGE CODE | BASE QUANTITY | DELIVERY MODE |
|---------------|-----------------|--------------|---------------|---------------|
| GBPC606-E4/51 | 3.2             | 51           | 100           | Paper box     |


**RATINGS AND CHARACTERISTICS CURVES** ( $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)

Fig. 1 - Derating Curve Output Rectified Current




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current Per Diode




Fig. 3 - Typical Forward Characteristics Per Diode




Fig. 5 - Typical Junction Capacitance Per Diode




Fig. 4 - Typical Reverse Leakage Characteristics Per Diode





Fig. 6 - Typical Transient Thermal Impedance Per Diode

## PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[GBPC602/1](#) [GBPC601/1](#) [GBPC608/1](#) [GBPC6005/1](#) [GBPC604/1](#) [GBPC606-E4/51](#) [GBPC610/1](#) [GBPC606/1](#)  
[GBPC6005-E4/51](#) [GBPC601-E4/51](#) [GBPC602-E4/51](#) [GBPC604-E4/51](#) [GBPC608-E4/51](#) [GBPC610-E4/51](#)