




LTE-M CELLULAR
SMART MODEM
FOR NORTH AMERICA



DIGI XBEE³ CELLULAR LTE-M

Compact, flexible cellular connectivity for IoT devices and gateways.

Digi XBee3™ modules accelerate time to market for designers, OEMs and solution providers by quickly enabling wireless connectivity and easy-to-add functionality. Building on industry-leading technology, pre-certified Digi XBee3 modules offer the flexibility to switch between multiple frequencies and wireless protocols as needed.

Digi XBee3 modules are the latest addition to the expanding Digi XBee Ecosystem of wireless modules, adapters and software – all engineered to accelerate development and deployment. Ideal for low data (typically <5 MB per month and where latency is not critical), low power, low-cost applications,

Digi XBee3 Cellular LTE-M modules feature a power saving mode which extends sleep time and battery life.

With Digi Remote Manager®, XBee3 modules can be easily configured and controlled from a simple, central platform. Built-in Digi TrustFence® security, identity and data privacy features use more than 175 controls to protect against new and evolving cyber threats. Standard XBee API frames and AT commands, MicroPython and XCTU software tools simplify adding functionality, set-up, configuration and testing.

BENEFITS

- FCC certified and carrier end-device certified
- Integrated MicroPython Programmability
- 90 days of free cellular service with development kits
- Excellent coverage and building penetration
- Low power consumption optimized for long battery life
- Direct USB provides easy PPP integration option
- Enhanced with Digi TrustFence® security framework
- Manage and configure with XCTU and Digi Remote Manager®
- Digi XBee Transparent and API modes simplify design
- Reduced hardware complexity with only 1 antenna required

RELATED PRODUCTS



Development
Kits



ConnectCore®
6UL SBC Pro



XCTU



Digi Remote
Manager®



Digi Design
Services

APPLICATION EXAMPLE



END USER




CLOUD-BASED
APPLICATION



CELL TOWER



LTE-M



SPECIFICATIONS		Digi XBee3 Cellular Smart Modem, LTE-M	
HARDWARE			
CELLULAR CHIPSET	u-blox SARA-R410M-02B		
FORM FACTOR	Digi XBee 20-pin through-hole		
ANTENNA OPTIONS	1 U.FL (Cellular), 1 U.FL (Bluetooth)		
DIMENSIONS	24.38 mm x 32.94 mm		
OPERATING TEMPERATURE	-40° C to +85° C		
SIM SIZE	4FF Nano		
INTERFACE AND I/O			
DATA INTERFACE	UART, SPI, USB		
OPERATING MODES	Transparent and API over serial, PPP over USB or Serial		
SECURITY	Digi Trustfence™ security with Secure Boot and Protected JTAG		
CONFIGURATION TOOLS	Digi XCTU (Local), Digi Remote Manager (OTA)		
EMBEDDED PROGRAMMABILITY	MicroPython with 32 KB Flash / 32 KB RAM		
I/O	4 ADC lines (10-bit), 13 Digital I/O, USB, I2C		
BLUETOOTH	Bluetooth LE Ready		
CELLULAR CHARACTERISTICS			
TRANSMIT POWER	Up to 23 dBm		
RECEIVE SENSITIVITY	-105dBm		
CARRIER APPROVALS	AT&T End Device Certified Verizon End Device Certification (Pending) Telus End Device Certification (Pending) Compatible with other LTE-M carriers, see band support		
SUPPORTED BANDS	LTE Bands 2,4,5,12; Verizon LTE Band 13 (coming soon)		
DOWNLINK/UPLINK SPEEDS	Up to 375 kb/s		
DUPLEX MODE	Half-Duplex		
POWER REQUIREMENTS (AT 3.3VDC INPUT POWER)			
SUPPLY VOLTAGE	Standard Version: 3.3-4.3VDC; Extended Input Range*: 2.8 to 5.5VDC		
PEAK TRANSMIT CURRENT	Standard Version: 550mA w/ Bluetooth disabled; 610mA w/ Bluetooth enabled Extended Input Range: 800mA w/ Bluetooth disabled; 860mA w/ Bluetooth enabled		
AVG TRANSMIT CURRENT	235mA		
POWER SAVE MODE	Standard Version: 20uA Extended Input Range*: 60uA		
DEEP SLEEP	10uA		
REGULATORY AND CARRIER APPROVALS			
FCC (USA)	MCQ-XB3M1		
IC (CANADA)	1846A-XB3M1		
VERIZON END-DEVICE CERTIFIED	Pending		
AT&T END-DEVICE CERTIFIED	Complete		
PTCRB	Complete		

PART NUMBERS	DESCRIPTION
XB3-C-A2-UT-001	Digi XBee3 Cellular Smart Modem, LTE CAT M, North America
XK3-C-A2-UT-U	Digi XBee3 Cellular Smart Modem, LTE CAT M, Development Kit, AT&T

*Contact Digi for more information

DIGI SERVICE AND SUPPORT / You can purchase with confidence knowing that Digi is always available to serve you with expert technical support and our industry leading warranty. For detailed information visit www.digi.com/support.

© 1996-2018 Digi International Inc. All rights reserved.
All trademarks are the property of their respective owners.

91003677
B4/318

DIGI INTERNATIONAL WORLDWIDE HQ
877-912-3444 / 952-912-3444 / www.digi.com

DIGI INTERNATIONAL GERMANY
+49-89-540-428-0

DIGI INTERNATIONAL JAPAN
+81-3-5428-0261 / www.digi-intl.co.jp

DIGI INTERNATIONAL SINGAPORE
+65-6213-5380

DIGI INTERNATIONAL CHINA
+86-21-50492199 / www.digi.com.cn

