


## DIP Clips® for 8-14-16-20-24-40 Pin Clips And 8 Through 40 Pin DIP Removers

Pomona DIP Clip® test clips are designed for testing dual-in-line IC packages on PC boards. These devices incorporate many built-in features that assure a positive electrical connection as well as hands free testing.


- Contacts (.040" wide on lower end) are serrated for the best electrical contact.
- .025" X .028" serrated test points on upper end will accept wire wraps or mini test clips.
- Molded barriers between contacts allows live board connections without accidental shorting of contacts.
- Can also be used as an insertion tool for DIPs.
- Contacts are spring tempered Nickel Silver or Gold Plated Beryllium Copper alloy. Oxide penetrating clips have a roughened stainless steel surface treatment.
- Open back option allows probing on the chip leads while clip is attached.



Pomona's DIP Clip® test clips are perfect for emulation, field service, failure analysis, and for use with logic analyzers.

| Size Pins | Clip Width | Standard DIP Clip® | Open Back DIP Clip® | Contact Material and Plating | Oxide Penetrating DIP Clip® | Static Control DIP Remover |
|-----------|------------|--------------------|---------------------|------------------------------|-----------------------------|----------------------------|
| 8         | .43        | <b>5108</b>        | <b>5208</b>         | Be-Cu, Gold Plate            | <b>5649</b>                 | <b>5016</b>                |
| 14        | .72        | <b>5014</b>        | <b>5114</b>         | Nickel Silver                | <b>5650</b>                 | <b>5016</b>                |
|           |            | <b>5214</b>        | <b>5314</b>         | Be-Cu, Gold Plate            | <b>5650</b>                 | <b>5016</b>                |
| 16        | .83        | <b>3916A</b>       | <b>4236A</b>        | Nickel Silver                | <b>5692</b>                 | <b>5016</b>                |
|           |            | <b>5116</b>        | <b>5216</b>         | Be-Cu, Gold Plate            | <b>5692</b>                 | <b>5016</b>                |
| 20        | 1.03       | <b>5120</b>        | <b>5220</b>         | Be-Cu, Gold Plate            | <b>5693</b>                 | <b>5016</b>                |
| 24        | 1.22       | <b>4124A</b>       | <b>4324A</b>        | Nickel Silver                | <b>5694</b>                 | <b>5024</b>                |
|           |            | <b>5124</b>        | <b>5224</b>         | Be-Cu, Gold Plate            | <b>5694</b>                 | <b>5024</b>                |
| 40        | 2.02       | <b>4140A</b>       | <b>4340A</b>        | Nickel Silver                | <b>5695</b>                 | <b>5040</b>                |
|           |            | <b>5140</b>        | <b>5240</b>         | Be-Cu, Gold Plate            | <b>5695</b>                 | <b>5040</b>                |

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).  
All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA



### FEATURES:

- For use with 14 or 16 Dual-In-Line I.C. packages.

### MATERIALS:

Insulation: Glass filled nylon. Color: Red.

Hinge Pin: Stainless steel 302, passivated per QQ-P-35.

### RATINGS:

Operating Temperature: +102°C. (+216°F.) Max.

### ORDERING INFORMATION: Model 4386

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02$ " (.51 mm), .xxx =  $\pm .005$ " (.127 mm).  
All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA