



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
NKHF2M**-X	.05 LB/10 PCS (23.9 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.



MODEL FILENAME	MO2201BA_NKF2M_04.PRT	SIZE A							
DRAWING FILENAME	MO2201BA_DC_04A.PRT								
NETKEY™ 2 POSITION 1/3 FLAT INSERT CUSTOMER DRAWING									
 PANDUIT TM TINLEY PARK, ILL 60477	1.1. NUMBER N/A PRODUCT SPEC N/A WORK INSTRUCTION N/A SCALE NONE								
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .01(.3) (.XX) ± .03(.8) ANGLES ±									
DRAWN BY JsP		PART NO. NKHF2M**-X							
DATE 3-18-05		DRAWING NO. 02201-02							
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	MATERIAL: ABS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[NKHF2MIG-X](#) [NKHF2MWH-X](#) [NKHF2MIW-X](#) [NKHF2MEI-X](#) [NKHF2MBL-X](#)