

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

73943-2000

Status:

Active

Overview:

HDM® Backplane Connector System

Description:

HDM® Board-to-Board Backplane Header, Vertical, Solder Tail, Closed End, 72 Circuits

Documents:

3D Model

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Backplane Connectors

Series

73943

Application

Backplane

Comments

Solder Tail

Component Type

PCB Header

Overview

HDM® Backplane Connector System

Product Name

HDM®

Style

N/A

UPC

800754772464

Physical

Circuits (Loaded)

72

Circuits (maximum)

72

Color - Resin

Black, Natural

Durability (mating cycles max)

250

First Mate / Last Break

No

Flammability

94V-0

Guide to Mating Part

No

Keying to Mating Part

None

Material - Metal

Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Number of Columns

12

Number of Pairs

Open Pin Field

Number of Rows

6

Orientation

Vertical

PC Tail Length

2.50mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

2.50mm

Packaging Type

Tube

Pitch - Mating Interface

2.00mm

Pitch - Termination Interface

2.00mm

Plating min - Mating

0.762µm

Plating min - Termination

2.540µm

Stackable

Yes

Surface Mount Compatible (SMC)


Yes

Temperature Range - Operating

-55°C to +105°C

Termination Interface: Style

Through Hole



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

73943Series

Mates With

73632 HDM PLUS® Board-to-Board Daughtercard Receptacle. 73780 HDM® Board-to-Board Daughtercard Receptacle

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Backplane Insertion

0621001400

Signal Contact Tool

Extraction Tool

0621001000

Electrical

Current - Maximum per Contact	1A
Data Rate	1.0 Gbps
Voltage - Maximum	250V AC

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-73943-001
---------------	--------------

HDM and High Density Metric are trademarks of Amphenol Corporation

This document was generated on 10/01/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION