








3M™ Shrouded Board Mount Header 2 mm X 2 mm Pitch 159 Series, Standard Length and Extended Length




RECOMMENDED PCB HOLE PATTERN
TOLERANCE = 0.05 [.002]



POLARIZATION SLOT
THRU-HOLE VERTICAL HEADER
6-12 POSITIONS ONLY



SINGLE FRICTION LATCH
THRU-HOLE VERTICAL HEADER
6-12 POSITIONS ONLY



POLARIZATION SLOT AND
DUAL FRICTION LATCHES
THRU-HOLE VERTICAL HEADER
14-50 POSITIONS

PERFORMANCE	
CURRENT:	1.25 A, ALL LINES ENERGIZED 2.75 A, 6 LINES ENERGIZED 4.75 A, 1 LINE ENERGIZED
INSULATION RESISTANCE:	>1 X 10 ⁹ OHMS AT 500 VDC
VOLTAGE RATING:	150 VAC PER EIA-364-20
WITHSTANDING VOLTAGE:	500 VAC _{rms} AT SEA LEVEL
TEMPERATURE RATING:	-55° C TO +105° C
SOLDER PROCESS TEMPERATURE:	260° C MAX PER IPC/JEDEC J-STD-020D

REFERENCE TABLE ON SHEET 5
FOR AVAILABLE POSITIONS AND
SOLDER TAIL LENGTHS

METRIC [ENGLISH]



UL FILE NO: E68080




NOTES

- 1 MATERIAL:
BODY: HIGH TEMPERATURE
GLASS FILLED LCP, BLACK
UL94V-0
CONTACTS: COPPER ALLOY
- 2 PLATING:
2.03-3.81 μm [80-150 μin]
NICKEL UNDERPLATE.
0.38 μm [15 μin] OR
0.76 μm [30 μin] AVG GOLD
ON WIPING AREA.
5.08 μm [200 μin] MIN
MATTE TIN ON SOLDER TAILS.
- 3 STANDARD LENGTH HEADERS
MATE WITH 3M™ SOCKETS,
158 SERIES (REFERENCE 3M
DRAWING 78-5100-2358-9).
- 4 EXTENDED LENGTH HEADERS
MATE WITH 3M™ SOCKETS,
870 SERIES.
- 5 FOR PRODUCT
SPECIFICATIONS AND
WARRANTY INFORMATION SEE
3M 78-5102-0078-1.
- 6 SEE THE REGULATORY
INFORMATION APPENDIX (RIA)
IN THE "RoHS COMPLIANCE"
SECTION OF
WWW.3MCONNECTOR.COM FOR
COMPLIANCE INFORMATION
(RIA E1 & C1 APPLY).
- 7 IN THE EVENT OF CONFLICT
BETWEEN THIS DATA AND
THAT CONTAINED IN THE
PRODUCT SPECIFICATION,
THE PRODUCT SPECIFICATION
TAKES PRECEDENT.
- 8 PACKAGING:
VERTICAL THRU: TRAY
RIGHT ANGLE: TRAY
VERTICAL SMT: TAPE & REEL



F	52868	MAR 05,2014 ADD TAPE & REEL, MATE PT, VOLTAGE RATING	SJS	SAN
E	51692	DEC 16,2013 ADD UL SYMBOLS	SJS	SAN
D	41488	JUN 20,2012 REVISED CURRENT RATING IN PERFORMANCE TABLE	LDS	SAN
C	39876	APR 18,2012 REMOVED 32 POS FROM TABLE ON SHT 5	LDS	SAN
B	34080	MAY 18,2011 ADDED 6.19 DIM ON SHT 24, REVISED & MOVED TABLE TO SHT 5	LDS	SF
A	30741	OCT 28,2010 INITIAL RELEASE	LDS	SF
REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
DRFT	L. SCHMIDT	DATE JUL 29, 2010	MFG	DATE
CHKD		DATE	APPROV. S. FELDMAN	DATE AUG 09, 2010

DESIGN REFERENCE		NEXT ASSEMBLY		REV		ECO		ISSUE DATE AND DESCRIPTION		DRFT		CHKD	
ADDRESS		DRT		DATE		MFG		DATE		DATE		DATE	
CODES		L. SCHMIDT		JUL 29, 2010									
		CHKD		DATE		APPR		S FELDMAN		DATE		AUG 09, 2010	
DIVISION		DIVISION CODE											
DO NOT SCALE DRAWING		SCALE <u>6</u> <u>1</u>		TOLERANCES EXCEPT AS NOTED		 3M Center St. Paul, MN 55144		© 3M COPYRIGHT 2010 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.					
 THIRD ANGLE PROJECTION		INCHES .0 .00 .000 .0000 ±		MILLIMETERS .0 .00 .000 .000 ±									
INTERPRET PER ASME Y14.5 - 1994		MAX SURFACE ROUGHNESS 125 ☐ ALL SURFACES ☒ MARKED ONLY		.0 .00 .000 ± 0.13		CAGE NUMBER		SIZE DRAWING NO.		REV.			
				ANGLES ± 1°		D		78-5100-2359-7		F			
				MODEL		DET.		LISTS ☐ YES ☒ NO		SHT 1 OF 5			


3M™ Shrouded Board Mount Header 2 mm X 2 mm Pitch 159 Series, Standard Length 3 and Extended Length 4




RECOMMENDED PCB HOLE PATTERN
TOLERANCE = ±0.05 [.002]




SECTION B - B



POLARIZATION SLOT
RIGHT ANGLE HEADER
6-12 POSITIONS ONLY



POLARIZATION SLOT AND
DUAL FRICTION LATCHES
RIGHT ANGLE HEADER
14-50 POSITIONS



SINGLE FRICTION LATCH
RIGHT ANGLE HEADER
6-12 POSITIONS ONLY




METRIC [ENGLISH]

REFERENCE TABLE ON SHEET 5
FOR AVAILABLE POSITIONS AND
SOLDER TAIL LENGTHS



F	52868	MAR 05,2014	SJS	SAN
E	51692	DEC 16,2013	SJS	SAN
D	41488	JUN 20,2012	LDS	SAN
C	39876	APR 18,2012	LDS	SAN
B	34080	MAY 18,2011	LDS	SF
A	30741	OCT 28,2010	LDS	SF
REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
DRFT	CHKD	DATE	DATE	DATE
L. SCHMIDT		JUL 29,2010	MFG	
			APPR	
			S FELDMAN	AUG 09,2010

DESIGN REFERENCE	NEXT ASSEMBLY	REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
DO NOT SCALE DRAWING	SCALE 4/1	TOLERANCES EXCEPT AS NOTED	INCHES	0.00 ±	0.00 ±	0.00 ±
THIRD ANGLE PROJECTION	INTERPRET PER ASME Y14.5 - 1994	MILLIMETERS	0 ±	0 ±	0 ±	0 ±
MAX SURFACE ROUGHNESS	125/	ALL SURFACES	0.00 ±	0.00 ±	0.00 ±	0.00 ±
MARKED ONLY	ANGLES ±1°					
TITLE		3M SHROUDED BOARD MOUNT HEADER 2 MM X 2 MM PITCH 159 SERIES				
CAGE NUMBER		D 78-5100-2359-7				
MODEL		REV. F				
LISTS		YES NO SHT 2 OF 5				




3M™ Shrouded Board Mount Header 2 mm X 2 mm Pitch 159 Series, Standard Length 3 and Extended Length 4



RECOMMENDED PCB PAD PATTERN
TOLERANCE = ±0.08 [.003]



SECTION C - C




REFERENCE TABLE ON SHEET 5
FOR AVAILABLE POSITIONS

METRIC [ENGLISH]

DESIGN REFERENCE		NEXT ASSEMBLY		REV	ECO	ISSUE DATE AND DESCRIPTION		DRFT	CHKD
L. SCHMIDT		JUL 29, 2010		1		MFG		DATE	
DIVISION		DIVISION CODE		CHKD		APPROVAL		DATE	
DO NOT SCALE DRAWING		SCALE 4/1		TOLERANCES EXCEPT AS NOTED		INCHES		MILLIMETERS	
THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 1994		MAX SURFACE ROUGHNESS		ALL SURFACES		MARKED ONLY	
125		0.00 ± 0.13		0.00 ± 0.000		0.00 ± 0.000		ANGLES ± 1°	
CAGE NUMBER		SIZE		DRAWING NO.		REV.		MODEL	
125		D		78-5100-2359-7		F		SHT 3 OF 5	


3M™ Shrouded Board Mount Header 2 mm X 2 mm Pitch 159 Series, Standard Length 3

STANDARD LENGTH HEADERS
ARE AVAILABLE



3M™ Shrouded Board Mount Header 2 mm X 2 mm Pitch 159 Series, Extended Length 4

CALL 3M INTERCONNECT SOLUTIONS
AT 800-225-5373 FOR AVAILABILITY
OF EXTENDED LENGTH HEADERS



ORDERING INFORMATION

TIER 1 - BEST
1591XX-XXXX

TIER
1 = BEST 0.76 μ m
[30 μ in] GOLD

POSITION COUNT
(SEE TABLE)

PART CONFIGURATION
2 = VERTICAL SMT
5 = RIGHT ANGLE THRU HOLE
6 = VERTICAL THRU HOLE

BODY LENGTH
0 = STANDARD LENGTH
(MATES TO 158 SERIES)
1 = EXTENDED LENGTH
(MATES TO 870 SERIES)

CONTACT TAIL LENGTH
2 = 2.84 mm [.112]
3 = 3.94 mm [.155]

POLARIZATION/LATCHING
0 = POLARIZATION SLOT AND
DUAL FRICTION LATCHES
(14-50 POSITIONS ONLY)
1 = POLARIZATION SLOT
(6-12 POSITIONS ONLY)
2 = SINGLE FRICTION LATCH
(6-12 POSITIONS ONLY)

TIER 2 - BETTER
1592XX-XXXX

TIER
2 = BETTER 0.38 μ m
[15 μ in] GOLD

POSITION COUNT
(SEE TABLE)

PART CONFIGURATION
2 = VERTICAL SMT
5 = RIGHT ANGLE THRU HOLE
6 = VERTICAL THRU HOLE

BODY LENGTH
0 = STANDARD LENGTH
(MATES TO 158 SERIES)
1 = EXTENDED LENGTH
(MATES TO 870 SERIES)

CONTACT TAIL LENGTH
2 = 2.84 mm [.112]
3 = 3.94 mm [.155]

POLARIZATION/LATCHING
0 = POLARIZATION SLOT AND
DUAL FRICTION LATCHES
(14-50 POSITIONS ONLY)
1 = POLARIZATION SLOT
(6-12 POSITIONS ONLY)
2 = SINGLE FRICTION LATCH
(6-12 POSITIONS ONLY)

METRIC [ENGLISH]

F	52868	MAR 05, 2014	SJS	SAN
E	51692	DEC 16, 2013	SJS	SAN
D	41488	JUN 20, 2012	LDS	SAN
C	39876	APR 18, 2012	LDS	SAN
B	34080	MAY 18, 2011	LDS	SF
A	30741	OCT 28, 2010	LDS	SF
REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
DRFT	L. SCHMIDT	DATE JUL 29, 2010	DATE	DATE
CHKD		DATE	APPROV S FELDMAN	DATE AUG 09, 2010
DIVISION		DIVISION CODE		
DO NOT SCALE DRAWING	SCALE 4 1	TOLERANCES EXCEPT AS NOTED		
THIRD ANGLE PROJECTION		INCHES .00 .00 .000 .0000		
INTERPRET PER ASME Y14.5 - 1994		MILLIMETERS 0 .0 .00 .000		
MAX SURFACE ROUGHNESS 125		ALL SURFACES MARKED ONLY		
ANGLES $\pm$ 1°				
TITLE	3M SHROUDED BOARD MOUNT HEADER 2 MM X 2 MM PITCH 159 SERIES			
CAGE NUMBER	78-5100-2359-7	DRAWING NO.	REV.	
MODEL		DET	ISTS	YES NO SHT 4 OF 5

