

**MICRO SWITCH**FREEPORT ILLINOIS, U.S.A  
A DIVISION OF HONEYWELL INC.  
FED. MFG. CODE 91929**SWITCH - BASIC**

CATALOG LISTING

**V3-3057****CK-X3557**

REPLACES X83370-V3

RELEASE NO. PR-14328

**V3-3057****M**DRAWING  
NUMBERISSUE  
**X2**

## REVISIONS

A CO 74212

D H D  
20 JAN 93

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK


CHECK

**NOTES**

- 1 - TERMINALS ARE PLATED FOR SOLDERING  
2 - EPOXY APPLIED AROUND TERMINAL AREA AND JOINT BETWEEN CASE AND COVER. EPOXY ON TOP OF THE SWITCH TO BE WIPED OFF FLUSH WITH CASE & COVER

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE — — — 150 GRAM MAX

RELEASE FORCE — — — 15 GRAM MIN

DIFFERENTIAL TRAVEL — — — .002-.010


OVERTRAVEL — — — .050 MIN

FREE POSITION — — — .625 MAX

RELEASE TRAVEL — — — .010 MIN

**ELECTRICAL DATA**CONTACT ARRANGEMENT  
S P D T

L112

10A 1/3 HP 125 OR 250 VAC  
1/2A 125 VDC, 1/4A 250 VDC  
4A 125 VAC "L"**SCALE FULL**DO NOT  
SCALE PRINTUNLESS OTHERWISE SPECIFIED  
TOLERANCES ARE

ONE PLACE (.0) ± .030

TWO PLACE (.00) ± .015

THREE PLACE (.000) ± .005

ANGLES ±

RAW MATERIAL - COMMERCIAL STANDARD

DIMENSIONS ARE IN INCHES AND ARE  
TO BE MET BEFORE PROTECTIVE  
COATINGS ARE APPLIED

MICRO SWITCH STANDARDS APPLY

WEIGHT .016 LB

FC-52848-B  
DRAWN

KEW 14 NOV 85