

270 Series

Vitreous Enamel Power



Select 270 Type fixed resistors for applications requiring wattage ratings from 12 to 1000 watts. The 270 Type resistors are equipped with lug terminals suitable for soldering or sturdy bolt connection. When secure mounting is required, the hollow core of these resistors permit fastening with spring-type brackets, thru bolts or thru bolts with slotted-steel brackets.

Suitable for rugged applications, the 270 Type resistors feature all-welded construction and durable lead free vitreous enamel coating. Mounting brackets not included with resistors.

FEATURES

- Terminals suitable for soldering or bolt connection
- High wattage applications
- Rugged lead free vitreous enamel coating
- Flame resistant coating
- All-welded construction
- RoHS compliant available
- "Fast on" option – see terminal 538, <http://www.ohmite.com/techdata/terminals.pdf>

SERIES SPECIFICATIONS

Series	Wattage	Ohms	Core Code	Voltage	Std. Terminal
L12	12	0.1-51K	D	565	57
L25	25	0.15-100K	K	625	40
L50	50	0.38-260K	K	1625	40
L100	100	0.23-101K	M	2845	40
L175	175	0.13-101K	P	3595	46
L225	225	0.16-129K	P	4595	46
L500	500	0.38-218K	S	4970	45
L1000	1000	0.69-392K	S	8900	45

Non-Inductive versions available; Other sizes available; Also available in low cost Centohm or Silicone coating; Consult Ohmite.

* Maximum Voltage is based on Ohm's Law $[V=\sqrt{P \times R}]$ as limited by the resistance value of specified product

CHARACTERISTICS

Coating	Lead free vitreous enamel. Large models (500 watts and up) are supplied in Silicone Ceramic. Also available in low-cost Centohm coating; Consult factory.										
Core	Tubular ceramic.										
Terminals	Solder coated radial lug. RoHS solder composition is 96% Sn, 3.5% Ag, 0.5% Cu										
Derating	Linearly from 100% @ +25°C to 0% @ +350°C.										
Tolerance	±5% 1Ω and over (J); ±10% under 1Ω (K)										
Power rating	Based on 25°C free air rating.										
Overload	10 times rated wattage for 5 seconds.										
Temperature coefficient	1 to 20Ω: ±400 ppm/°C; Above 20Ω: ±260 ppm/°C										
Dielectric withstanding voltage	1000 VAC: 12 to 100 watt rating. 3000 VAC: 175 to 225 watt rating (Measured from terminal to mounting bracket)										
Max. amps	use the formula $\sqrt{P/R}$										
Power limitations for high resistance values	When resistance exceeds the resistance values listed, derate the Power Rating by 25% to improve reliability. <i>No power derating necessary for ratings higher than 100W.</i>										
	<table> <tr> <th>Power rating</th><th>Resistance value</th></tr> <tr> <td>12W</td><td>3,900Ω</td></tr> <tr> <td>25W</td><td>12,000Ω</td></tr> <tr> <td>50W</td><td>35,000Ω</td></tr> <tr> <td>100W</td><td>75,000Ω</td></tr> </table>	Power rating	Resistance value	12W	3,900Ω	25W	12,000Ω	50W	35,000Ω	100W	75,000Ω
Power rating	Resistance value										
12W	3,900Ω										
25W	12,000Ω										
50W	35,000Ω										
100W	75,000Ω										
Mounting Hardware	see http://www.ohmite.com/techdata/lug-mounting.php										


(continued)

270 Series

Vitreous Enamel Power

DIMENSIONS

in./mm



Series	Wattage	L		D		C	Core Code*	Std. Term.**
L12	12	1.75	44.4	0.313	7.94	0.188 / 4.76	D	57
L25	25	2.0	50.8	0.562	14.3	0.313 / 7.94	K	40
L50	50	4.0	101.6	0.562	14.3	0.313 / 7.94	K	40
L100	100	6.5	165.1	0.750	19.1	0.50 / 12.7	M	40
L175	175	8.5	215.9	1.125	28.6	0.75 / 19.1	P	46
L225	225	10.5	266.7	1.125	28.6	0.75 / 19.1	P	46
L500	500	12.0	304.8	2.50	63.5	1.75 / 44.5	S	45
L1000	1000	20.0	508.0	2.50	63.5	1.75 / 44.5	S	45

* <http://www.ohmite.com/techdata/200-210-270-custom.pdf>

** <http://www.ohmite.com/techdata/terminals.pdf>

ORDERING INFORMATION

Standard

F = Fast on (optional)	Non-inductive Blank = Standard N = Non-inductive	RoHS Compliant
L	25	J 100 E
Coating Blank = Vitreous C = Centohm S = Silicone	Series Wattage Tolerance J = 5% K = 10%	Ohms 1R0 = 1Ω 250 = 250Ω 1K0 = 1,000Ω 25K = 25,000Ω 25K5 = 25,500Ω

Made-to-order

Non-inductive Blank = Standard N = Non-inductive	Core Diameter See "Core and Terminal Selection"	RoHS Compliant
270	50	K 405 R 00 J E
Coating 270 = Vitreous 470 = Silicone Ceramic	Wattage Terminal Type See "Resistor Terminals for Tubular Cores"	Ohms R500 = 0.500Ω 1R00 = 1Ω 250R = 250Ω 1K00 = 1,000Ω 25K0 = 25,000Ω 25K5 = 25,500Ω

See website for custom core and terminal info

Standard part numbers for 270 series

Ohmic value		Wattage		Ohmic value		Wattage	
12 Watt		25		12 Watt		25	
0.51 ✓	L12JKR51E	180 ✓	L12J180E	180 ✓	L12J180E	25	L25J
1 ✓	L12J1R0E	270 ✓	L12J270E	270 ✓	L12J270E	50	L50J
3.3 ✓	L12J3R3E	330 ✓	L12J330E	330 ✓	L12J330E	100	L100J
4.7 ✓	L12J4R7E	390 ✓	L12J390E	390 ✓	L12J390E	175	L175J
10 ✓	L12J10RE	470 ✓	L12J470E	470 ✓	L12J470E	225	L225J
12 ✓	L12J12RE	560 ✓	L12J560E	560 ✓	L12J560E	500	L500J
15 ✓	L12J15RE	1000 ✓	L12J1K0E	1000 ✓	L12J1K0E	1000	L1000J
22 ✓	L12J22RE	1200 ✓	L12J1K2E	1200 ✓	L12J1K2E		
27 ✓	L12J27RE	1500 ✓	L12J1K5E	1500 ✓	L12J1K5E		
33 ✓	L12J33RE	2200 ✓	L12J2K2E	2200 ✓	L12J2K2E		
47 ✓	L12J47RE	2700 ✓	L12J2K7E	2700 ✓	L12J2K7E		
68 ✓	L12J68RE	4700 ✓	L12J4K7E	4700 ✓	L12J4K7E		
82 ✓	L12J82RE	10000 ✓	L12J10KE	10000 ✓	L12J10KE		
100 ✓	L12J100E	18000 ✓	L12J18KE	18000 ✓	L12J18KE		
150 ✓	L12J150E	22000 ✓	L12J22KE	22000 ✓	L12J22KE		
		51000 ✓	L12J51KE	51000 ✓	L12J51KE		

Ohmic value		Wattage		Ohmic value		Wattage	
12 Watt		25		12 Watt		25	
1 ✓	L1R0E	2,500 ✓	L2K5E	2,500 ✓	L2K5E	25	L25J
2 —	2R0E	3,000 ✓	L3K0E	3,000 ✓	L3K0E	50	L50J
3 —	3R0E	3,500 ✓	L3K5E	3,500 ✓	L3K5E	100	L100J
4 —	4R0E	4,000 ✓	L4K0E	4,000 ✓	L4K0E	175	L175J
5 —	5R0E	5,000 ✓	L5K0E	5,000 ✓	L5K0E	225	L225J
10 —	10RE	6,000 ✓	L6K0E	6,000 ✓	L6K0E	500	L500J
15 —	15RE	7,500 ✓	L7K5E	7,500 ✓	L7K5E	1000	L1000J
25 —	25RE	10,000 ✓	L10KE	10,000 ✓	L10KE		
50 —	50RE	12,000 ✓	L12KE	12,000 ✓	L12KE		
75 —	75RE	15,000 ✓	L15KE	15,000 ✓	L15KE		
100 —	100E	20,000 ✓	L20KE	20,000 ✓	L20KE		
125 —	125E	25,000 ✓	L25KE	25,000 ✓	L25KE		
150 —	150E	30,000 ✓	L30KE	30,000 ✓	L30KE		
200 —	200E	35,000 ✓	L35KE	35,000 ✓	L35KE		
250 —	250E	40,000 ✓	L40KE	40,000 ✓	L40KE		
500 —	500E	50,000 ✓	L50KE	50,000 ✓	L50KE		
750 —	750E	60,000 ✓	L60KE	60,000 ✓	L60KE		
800 —	800E	75,000 ✓	L75KE	75,000 ✓	L75KE		
1,000 —	1K0E	100,000 ✓	L100KE	100,000 ✓	L100KE		
1,500 —	1K5E	150,000 ✓	L150KE	150,000 ✓	L150KE		
2,000 —	2K0E	200,000 ✓	L200KE	200,000 ✓	L200KE		
		250,000 ✓	L250KE	250,000 ✓	L250KE		

✓ = Standard values; check availability using the worldwide inventory search at www.ohmite.com

Red outlined values supplied in Silicone-Ceramic coatings instead of vitreous enamel.