


Features

- ◆ Ultracompact DIP 16 package
- ◆ I/O isolation 3000 VACrms rated for 300 Vrms working voltage
- ◆ Medical safety to UL 60601-1 and IEC/EN 60601-1 3rd edition, 2 x MOOP
- ◆ Industrial safety to IEC/EN/UL 60950-1
- ◆ Operating temp. range -40°C to +71°C
- ◆ Short circuit protection
- ◆ 3-years product warranty



The THI 2M series is a new range of ultra-compact 2W DC/DC-converters providing a high I/O-isolation voltage of 3000 VAC. With a reinforced I/O-isolation system this product is an economical solution for many applications in instrumentation, industrial controls, medical equipment and everywhere where supplementary- or reinforced insulation is required to meet requested safety standards.

Full SMD-design with exclusive use of ceramic capacitors ensure a very high reliability and a long product lifetime.

Models

Order code	Input voltage range	Output voltage	Output current max.	Efficiency typ.
THI 2-0511M	5.0 VDC ± 10% (nominal 5 VDC)	5 VDC	400 mA	66 %
THI 2-0512M		12 VDC	165 mA	66 %
THI 2-0513M		15 VDC	133 mA	66 %
THI 2-0522M		±12 VDC	±83 mA	72 %
THI 2-0523M		±15 VDC	±66 mA	73 %
THI 2-1211M	12.0 VDC ± 10% (nominal 12 VDC)	5 VDC	400 mA	66 %
THI 2-1212M		12 VDC	165 mA	66 %
THI 2-1213M		15 VDC	133 mA	66 %
THI 2-1222M		±12 VDC	±83 mA	74 %
THI 2-1223M		±15 VDC	±66 mA	75 %
THI 2-2411M	24 VDC ± 10% (nominal 24 VDC)	5 VDC	400 mA	66 %
THI 2-2412M		12 VDC	165 mA	66 %
THI 2-2413M		15 VDC	133 mA	66 %
THI 2-2422M		±12 VDC	±83 mA	74 %
THI 2-2423M		±15 VDC	±66 mA	75 %

Input Specifications

Input current no load / full load	5 Vin models: 60 mA / 600 mA typ. 12 Vin models: 30 mA / 250 mA typ. 24 Vin models: 15 mA / 135 mA typ.
Reverse voltage protection	0.3 A max.
Recommended external input fuse (slow blow)	5 Vin models: 1.0 A 12 Vin models: 0.5 A 24 Vin models: 0.2 A
Surge voltage (1 sec. max.)	5 Vin models: 9 V max. 12 Vin models: 18 V max. 24 Vin models: 30 V max.
Input filter	internal capacitors

Output Specifications

Voltage set accuracy	±4 %
Voltage balance (dual output models)	1 % max.
Regulation	– Input variation – Load variation 20 – 100 % 1.2 % / 1 % change of Vin 10 % max. 12 % max. for 5 Vout models.
Ripple and noise (20 MHz Bandwidth)	150 mVpk-pk max
Temperature coefficient	±0.02 %/K
Short circuit protection	0.5 sec. max.
Minimum load	2 % of rated max. current
Capacitive load	single output models: 330 µF max. dual output models: 100 µF max. (each output)

General Specifications

Temperature ranges	– Operating – Storage – Casing	–40°C to +71°C –40°C to +125°C +90°C max.
Derating		2.5 %/K above 60°C
Humidity (non condensing)		95 % rel. H max.
Reliability, calculated MTBF (MIL-HDBK-217F, @ 25°C, ground benign)		>2.0 Mio h
Isolation voltage – Input/Output (50Hz, 60sec)	Medical applications in accordance to IEC/EN 60601-1: IT applications in accordance to IEC/EN 60950-1:	Reinforced, rated for 300 Vrms working voltage 3000 VAC, 2 x MOOP 4000 VAC
Isolation test voltage (1 sec.)		6'000 Vpk
Leakage current (at 240VAC, 60Hz)		2 µA max.
Isolation capacity	– Input/Output	20 pF max. (at 100KHz, 1V)
Isolation resistance	– Input/Output	>10 Gohm (at 500VDC)
Switching frequency		50 – 100 kHz (PFM)
Safety standards		IEC/EN 60950-1, UL 60950-1 CSA C22.2 No. 60950-1-03 IEC/EN 60601-1 3rd edition, 2 x MOOP, UL 60601-1, CSA C22.2 No. 601.1
Safety approvals	– CSA certificate for medical electrical equipment for information technology equipment – CB test certificate for medical electrical equipment for information technology equipment	www.tracopower.com/products/thi2m-csa60601.pdf www.tracopower.com/products/thi2m-csa60950.pdf www.tracopower.com/products/thi2m-cb60601.pdf www.tracopower.com/products/thi2m-cb60950.pdf

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

General Specifications


Casing material	non conductive plastic (UL 94V-0 rated)
Weight	5.1 g (0.18oz)
Soldering temperature	max. 265°C / 10 sec

Application note: www.tracopower.com/products/thi2m-application.pdf



- The component is not be used in an oxygen rich environment.
- The component is not to be used in conjunction with flammable anaesthetics and agents.
- The component has to be disposed appropriately. Please refer to local regulations (Waste Electrical and Electronic Equipment).
- A modification of the component is not allowed.

Outline Dimensions



Pin-Out

Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
7	No con.	No con.
8	No con.	Common
9	+Vout	+Vout
10	-Vout	-Vout
16	+Vin	+Vin

Dimensions in [mm], () = Inch
Pin diameter: 0.5 ± 0.05 (0.024 ± 0.002)
Tolerances: ± 0.25 (± 0.01)
Pin pitch tolerances: ± 0.05 (± 0.002)