






CODE No.	CONTACT	A	B	C	D	E	F	G
CL537-0721-0-86	10	4.7	2.0	2.8	3.2	4.1	2.8	5.6
CL537-0918-4-86	14	5.7	3.0	3.8	4.2	5.1	3.8	6.6
CL537-0723-5-86	20	7.2	4.5	5.3	5.7	6.6	5.3	8.1
CL537-0725-0-86	30	9.7	7.0	7.8	8.2	9.1	7.8	10.6
CL537-0732-6-86	32	10.2	7.5	8.3	8.7	9.6	8.3	11.1
CL537-0726-3-86	36	11.2	8.5	9.3	9.7	10.6	9.3	12.1
CL537-0727-6-86	40	12.2	9.5	10.3	10.7	11.6	10.3	13.1
CL537-0729-1-86	50	14.7	12.0	12.8	13.2	14.1	12.8	15.6
CL537-0731-3-86	60	17.2	14.5	15.3	15.7	16.6	15.3	18.1
CL537-0733-9-86	80	22.2	19.5	20.3	20.7	21.6	20.3	23.1

RECOMMEND METAL MASK PATTERN (10:1)



RECOMMENDED LAND PATTERN (10:1)



RECOMMENDED THICKNESS OF SOLDER PASTE : 120 μm

2	PHOSPHOR BRONZE	CONTACT AREA:GOLD PLATED 0.2μm min LEAD AREA:GOLD PLATED 0.015μm min OTHERS(UNDER PLATING):NICKEL PLATED 2μm min	7	PS	CLEAR (REINFORCEMENT COLLAR)
1	POLYAMIDE	UL94V-0, NATURAL (BEIGE)	6	PS	BLACK (PLASTIC REEL)
NO.	MATERIAL	FINISH, REMARKS	5	POLYESTER	CLEAR (COVER TAPE)
UNITS	mm	SCALE	4	PS	CLEAR (EMBOSSD CARRIER TAPE)
5 : 1		COUNT	3	BRASS	TIN PLATED 2μm min (UNDER PLATING):NICKEL 1μm min
		DESCRIPTION OF REVISIONS	NO.	MATERIAL	FINISH, REMARKS
		DIS-H-00002907			
		APPROVED : KH. IKEDA			
		CHECKED : TS. MIYAZAKI			
		DESIGNED : YH. MICHIDA			
		DRAWN : KR. AJITO			
		DATE			
		17.06.07			
		EDC3-163507-77			
		DF12(3.0)-*DP-0.5V(86)			
		CL537			

