






	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1																																																																																																	
M	CKT SIZE	① MAIN HOUSING	② TPA	③ SIGNAL HOUSING	④ POWER TERMINAL	⑤ SIGNAL TERMINAL	DIMENSION "A"	DIMENSION "B"	DIMENSION "C"	DIMENSION "D"											M																																																																																																
		MATERIAL: UNFILLED PBT	MATERIAL: FILLED PBT	MATERIAL: UNFILLED NYLON	MATERIAL: COPPER ALLOY FINISH: TIN OVER NICKEL W/ SELECT GOLD	MATERIAL: PHOS BRONZE FINISH: TIN OVER NICKEL W/ SELECT GOLD																																																																																																															
L	2P-12S	172510-3212	46708-3212	46709-0004	173693-****	70058-****	45.76	28.4	26.48	10.67											L																																																																																																
	2P-18S	172510-3218	46708-3218	46709-0006	173693-****	70058-****	50.84	33.5	31.80	15.75																																																																																																											
K	2P-24S	172510-3224	46708-3224	46709-0008	173693-****	70058-****	55.92	38.6	36.85	20.83											K																																																																																																
	4P-12S	172510-3412	46708-3412	46709-0004	173693-****	70058-****	60.76	43.4	41.48	10.67																																																																																																											
J	4P-18S	172510-3418	46708-3418	46709-0006	173693-****	70058-****	65.84	48.5	46.80	15.75																																																																																																											
	4P-24S	172510-3424	46708-3424	46709-0008	173693-****	70058-****	70.92	53.6	51.85	20.83											J																																																																																																
I	6P-12S	172510-3612	46708-3612	46709-0004	173693-****	70058-****	75.76	58.4	56.48	10.67																																																																																																											
	6P-18S	172510-3618	46708-3618	46709-0006	173693-****	70058-****	80.84	63.5	61.85	15.75																																																																																																											
	6P-24S	172510-3624	46708-3624	46709-0008	173693-****	70058-****	85.92	68.6	66.93	20.83	 EXPLODED VIEW MAIN HOUSING  TPA  SIGNAL HOUSING    NOTES: - SEE CHART FOR MATERIAL DETAILS - PART MATES TO MOLEX PLUG SERIES 172453 - ASSEMBLY SHOWN FOR REFERENCE ONLY. EACH ITEM HAS TO BE ORDERED SEPARATELY. - SEE SD-173693-001 FOR POWER TERMINAL DETAILS - SEE SD-70058-*** FOR SIGNAL TERMINAL DETAILS <table><tr><td rowspan="5">CHG TRML P/N EC NO: UCP2016-4071 DRAWN: JSCHAER 2016/04/18 CHKD: APPR: BPI SZCZOR 2016/10/03</td><td rowspan="6">DESCRIPTION REV</td><td>QUALITY SYMBOLS</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE 1.5:1</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td><td colspan="2">TITLE TEN60 WIRE TO BOARD POWER / SIGNAL MIX</td><td colspan="2">DOCUMENT NO. SD-172510-001</td><td>SHEET NO. 1 OF 1</td></tr><tr><td>▽=0</td><td>4 PLACES ±</td><td>mm</td><td>INCH</td><td>DRAWN BY JSCHAER</td><td>DATE 2014/02/17</td><td colspan="2" rowspan="5">APPROVED BY BPI SZCZOR</td><td colspan="2" rowspan="5">DATE 2016/10/03</td><td colspan="2" rowspan="5">SEE CHART</td><td colspan="2" rowspan="5">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr><tr><td>▽=0</td><td>3 PLACES ±</td><td>---</td><td>---</td><td>CHECKED BY</td><td>DATE</td></tr><tr><td>▽=0</td><td>2 PLACES ±</td><td>0.13</td><td>---</td><td colspan="10" rowspan="3">APPROVED BY BPI SZCZOR</td></tr><tr><td></td><td>1 PLACE ±</td><td>0.25</td><td>---</td></tr><tr><td colspan="2"></td><td colspan="19"></td></tr><tr><td colspan="2"></td><td colspan="19">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td></tr></table>										CHG TRML P/N EC NO: UCP2016-4071 DRAWN: JSCHAER 2016/04/18 CHKD: APPR: BPI SZCZOR 2016/10/03	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1.5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		TITLE TEN60 WIRE TO BOARD POWER / SIGNAL MIX		DOCUMENT NO. SD-172510-001		SHEET NO. 1 OF 1	▽=0	4 PLACES ±	mm	INCH	DRAWN BY JSCHAER	DATE 2014/02/17	APPROVED BY BPI SZCZOR		DATE 2016/10/03		SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		▽=0	3 PLACES ±	---	---	CHECKED BY	DATE	▽=0	2 PLACES ±	0.13	---	APPROVED BY BPI SZCZOR											1 PLACE ±	0.25	---																								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																			
CHG TRML P/N EC NO: UCP2016-4071 DRAWN: JSCHAER 2016/04/18 CHKD: APPR: BPI SZCZOR 2016/10/03	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1.5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION														TITLE TEN60 WIRE TO BOARD POWER / SIGNAL MIX		DOCUMENT NO. SD-172510-001		SHEET NO. 1 OF 1																																																																																										
		▽=0	4 PLACES ±	mm	INCH	DRAWN BY JSCHAER	DATE 2014/02/17	APPROVED BY BPI SZCZOR		DATE 2016/10/03													SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																												
		▽=0	3 PLACES ±	---	---	CHECKED BY	DATE																																																																																																														
		▽=0	2 PLACES ±	0.13	---	APPROVED BY BPI SZCZOR																																																																																																															
			1 PLACE ±	0.25	---																																																																																																																
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																																																																																																																			