

4		3		2		1		
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION.				ALL INTERNATIONAL RIGHTS RESERVED.				
LOC G		DIST 14		REVISIONS				
P		LTR		DESCRIPTION		DATE	DWN	APVD
		G1		REVISED PER ECR-09-019194		01SEP09	HMR	TM

1

STAMP AMP 22-18 APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC MIL-T-7928
COMMERCIAL WIRE RANGE IS 22-16

2 WIRE INSUL DIA, 2.67-3.56[.105-.140]

3 TONGUE MATL THK, 0.79±0.05[.031±.002]

Technical drawing of a terminal. Labels: BODY, SLEEVE COLOR, ORANGE, SERRATION. Dimensions: 5.00±0.08 DIA [.197±.003] (FOR #10 STUD), 7.14 [.281], 6.35 [.250] MIN, 15.52 [.611] MAX, 19.02 [.749] MAX. Feature 1 is indicated by a triangle with the number 1.

5000	ON TAPE, REEL	2-321894-1
1000	LOOSE PIECE	321894
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEM		MAX RECOMMENDED OPERATING TEMPERATURE: 649°C [1200°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN L OLMEDA 100CT94 CHK M ELLIS 100CT94 APVD S BORTNER 100CT94 PRODUCT SPEC — APPLICATION SPEC — WEIGHT —	Tyco Electronics Corporation Harrisburg, PA 17105-3608 NAME TERMINAL, RING TONGUE, STRATOTHERM, DIAMOND GRIP, WIRE SIZE, 22-16 AWG SIZE A3 CAGE CODE 00779 DRAWING NO C-321894 RESTRICTED TO —			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752							
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: —	DIMENSIONS: mm [INCHES] 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.20 [.008] 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH —				
FOR ORDER ENTRY	1-800-526-5142	CIRCULAR MIL AREA: 0.26mm²-1.65mm² [509-3260] STRANDED WIRE			MATERIAL BODY, NI PER ASTM B162 SLEEVE, NI SIL PER ASTM B122			