


Typical Applications

- CATV Distribution Amplifiers
- Cable Modems
- Broadband Gain Blocks
- Laser Diode Driver
- Return Channel Amplifier
- Base Stations

Product Description


The RF2317 is a general purpose, low cost high linearity RF amplifier IC. The device is manufactured on an advanced Gallium Arsenide Heterojunction Bipolar Transistor (HBT) process, and has been designed for use as an easily cascable 75Ω gain block. The gain flatness of better than ±0.4dB from 50MHz to 1000MHz, and the high linearity, make this part ideal for cable TV applications. Other applications include IF and RF amplification in wireless voice and data communication products operating in frequency bands up to 3GHz. The device is self-contained with 75Ω input and output impedances and requires only two external DC biasing elements to operate as specified.



Optimum Technology Matching® Applied

- ☐ Si BJT ☒ GaAs HBT ☐ GaAs MESFET
☐ Si Bi-CMOS

Package Style: SOP-16 QBW1



Functional Block Diagram

Features

- DC to 3.0GHz Operation
- Internally Matched Input and Output
- 15dB Small Signal Gain
- 4.9dB Noise Figure
- +26dBm Output Power
- Single 12V to 15Volt Power Supply

Ordering Information

- | | |
|-------------|----------------------------------|
| RF2317 | Linear CATV Amplifier |
| RF2317 PCBA | Fully Assembled Evaluation Board |

RF Micro Devices, Inc.
7625 Thorndike Road
Greensboro, NC 27409, USA

Tel (336) 664 1233
Fax (336) 664 0454
<http://www.rfmd.com>

Absolute Maximum Ratings

Parameter	Rating	Unit
Device Current	250	mA
Input RF Power	+18	dBm
Output Load VSWR	20:1	
Ambient Operating Temperature	-40 to +85	°C
Storage Temperature	-40 to +150	°C



Caution! ESD sensitive device.

RF Micro Devices believes the furnished information is correct and accurate at the time of this printing. However, RF Micro Devices reserves the right to make changes to its products without notice. RF Micro Devices does not assume responsibility for the use of the described product(s).

3

LINEAR CATV
AMPLIFIERS

Parameter	Specification			Unit	Condition
	Min.	Typ.	Max.		
Overall (50Ω)					T=25 °C, I _{CC} =180mA, R _C =11Ω, 50Ω System
Frequency Range		DC to 3000		MHz	3dB Bandwidth
Gain	14.0	14.5		dB	
Noise Figure		4.9		dB	From 100MHz to 1000MHz
Input VSWR		1.7			Appropriate values for the DC blocking capacitors and bias inductor are required to maintain this VSWR at the intended operating frequency range.
Output VSWR		2.2			Appropriate values for the DC blocking capacitors and bias inductor are required to maintain this VSWR at the intended operating frequency range.
Output IP ₃				dBm	At 100MHz
Output IP ₃		+42		dBm	At 500MHz
Output IP ₃				dBm	At 900MHz
Output IP ₂		+63		dBm	F ₁ =400MHz, F ₂ =500MHz, F _{OUT} =100MHz
Output P _{1dB}				dBm	At 100MHz
Output P _{1dB}		+26		dBm	At 500MHz
Output P _{1dB}				dBm	At 900MHz
Saturated Output Power				dBm	At 100MHz
Saturated Output Power		-27		dBm	At 500MHz
Saturated Output Power				dBm	At 900MHz
Reverse Isolation		20		dB	
Thermal					
Theta _{JC}		47		°C/W	I _{CC} =150mA, P _{DISS} =1.3W, T _{AMB} =85 °C
Maximum junction temperature		153		°C	
Mean Time Between Failures		8.6x10 ²		years	T _{AMB} =+85 °C
Mean Time Between Failures		1.8x10 ⁵		years	T _{AMB} =+25 °C
Theta _{JC}		54		°C/W	I _{CC} =180mA, P _{DISS} =1.7W, T _{AMB} =85 °C
Maximum junction temperature		185		°C	
Mean Time Between Failures		8.6x10 ²		years	T _{AMB} =+85 °C
Mean Time Between Failures		1.8x10 ⁵		years	T _{AMB} =+25 °C
Power Supply					
Device Voltage		8.3		V	On pin 13, I _{CC} =150mA
Device Voltage		8.7		V	On pin 13, I _{CC} =220mA
Operating Current Range	100		200	mA	Actual current determined by V _{CC} and R _S

Parameter	Specification			Unit	Condition
	Min.	Typ.	Max.		
Overall (75Ω)					T=25 °C, I _{CC} =180mA, R _C =11Ω, 75Ω System
Frequency Range		DC to 3000		MHz	3dB Bandwidth
Gain	14.5	15.0		dB	
Noise Figure		5.3		dB	From 100MHz to 1000MHz
Input VSWR		1.1:1			Appropriate values for the DC blocking capacitors and bias inductor are required to maintain this VSWR at the intended operating frequency range.
Output VSWR		1.5:1			Appropriate values for the DC blocking capacitors and bias inductor are required to maintain this VSWR at the intended operating frequency range.
Output IP ₃				dBm	At 100MHz
Output IP ₃		+42		dBm	At 500MHz
Output IP ₃				dBm	At 900MHz
Output IP ₂		+63		dBm	F ₁ =400MHz, F ₂ =500MHz, F _{OUT} =100MHz
Output P _{1dB}				dBm	At 100MHz
Output P _{1dB}		+26		dBm	At 500MHz
Output P _{1dB}				dBm	At 900MHz
Saturated Output Power				dBm	At 100MHz
Saturated Output Power		+27		dBm	At 500MHz
Saturated Output Power				dBm	At 900MHz
Reverse Isolation		20		dB	
CSO		-68		dBc	At 55.25MHz, 77 Channels, 44dBmV/ch
CSO		-52		dBc	At 325.25MHz, 77 Channels, 44dBmV/ch
CSO		-53		dBc	At 547.25MHz, 77 Channels, 44dBmV/ch
CTB		-60		dBc	At 55.25MHz, 77 Channels, 44dBmV/ch
CTB		-55		dBc	At 325.25MHz, 77 Channels, 44dBmV/ch
CTB		-57		dBc	At 547.25MHz, 77 Channels, 44dBmV/ch
DIN 45004B		62		dBmV	At 600 MHz
DIN 45004B		60.5		dBmV	At 900 MHz


RF2317

3

LINEAR CATV
AMPLIFIERS

Pin	Function	Description	Interface Schematic
1	NC	This pin is internally not connected.	
2	GND	Ground connection. Keep traces physically short and connect immediately to ground plane for best performance. Each ground pin should have a via to the ground plane.	
3	GND	Same as pin 2.	
4	RF IN	RF input pin. This pin is NOT internally DC blocked. A DC blocking capacitor, suitable for the frequency of operation, should be used in most applications. DC coupling of the input is not allowed, because this will override the internal feedback loop and cause temperature instability. The bias of the device can be controlled by this pin. Adding an optional 1k resistor to ground on this pin reduces the bias level, which can be compensated by a higher supply voltage to maintain the appropriate bias level. The net effect of this is an increased output power capability, as well as higher linearity for signals with high crest factors.	
5	NC	This pin is internally not connected.	
6	GND	Same as pin 2.	
7	GND	Same as pin 2.	
8	NC	This pin is internally not connected.	
9	NC	This pin is internally not connected.	
10	GND	Same as pin 2.	
11	GND	Same as pin 2.	
12	NC	This pin is internally not connected.	
13	RF OUT	RF output and bias pin. Because DC is present on this pin, a DC blocking capacitor, suitable for the frequency of operation, should be used in most applications. For biasing, an RF choke in series with a resistor is needed. The DC voltage on this pin is typically 8.3V with a current of 150mA. See device voltage versus device current plot. In lower power applications the value of R_C can be increased to lower the current and V_D on this pin.	
14	GND	Same as pin 2.	
15	GND	Same as pin 2.	
16	NC	This pin is internally not connected.	

Application Schematic




3

LINEAR CATV
AMPLIFIERS

Evaluation Board Schematic

(Download [Bill of Materials](http://www.rfmd.com) from www.rfmd.com.)



Evaluation Board Layout 2" x 2"

3

LINEAR CATV
AMPLIFIERS

