



DM537405000NC	COAXIAL CONTACTS STRAIGHT	1.00	1.75	2.32	3.20	22.40	RG 178 BU
DM537405008NC	COAXIAL CONTACTS STRAIGHT	1.00	1.75	2.32	3.20	23.60	RG 178 BU
DM537405002NC	COAXIAL CONTACTS STRAIGHT	2.75	4.00	5.09	5.95	26.30	RG 180 BU
Ref contact	Designation	$\phi A^{+0.10}_0$	$\phi B^{+0.10}_{-0.10}$	$\phi C^{+0.10}_0$	$\phi D^{+0.10}_0$	E	Ref cable



NOTE: RoHS INFORMATION

- These products meet European union Directives and other country regulations as described in GS-22-008. (RoHS Compliant products)
- Packaging spec: see GS-14-920

Part
number

SEE TABLE

ELECTRICAL CHARACTERISTICS

dielectric with standing voltage 2800V eff.
break down voltage 3200V eff.
insulation resistance 10^6 M OHMS
contact resistance ≤ 5 m OHMS


MECHANICAL CHARACTERISTICS

mating force per set of contact 3 N
 mating endurance 200
 temperature -55° to +125 °C

TOOLING

coaxial contact extraction tool 8630-07A

rev	ecn no	dr	date
B	-	JAR	2000/02/02
C	LS05-0026	MPE	2005/07/08
D	LS06-0095	LGO	2006/07/19
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		mm 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	PESSON	1996/07/01	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 5			
Eng	PESSON	1996/07/01			0.XX	±0.1					
Chr	LEGARE	1996/07/01			0.XX* ±2*	±0.1					
Appr	LEGARE	1996/07/01	Product family				D-SUB	Spec ref	-		
			MALE COAX CONTACT STRAIGHT SOLDER VERSION					dwg no C01-8639-0627		Rev D	
catalog no			-					CUSTOMER	sheet 1 of 1		