




NOTES:

1. MATERIALS OF CONSTRUCTION:
BODY = BRASS (ASTM-B16 H02, C36000), GOLD PLATED (.000003 MIN) OVER NICKEL (.000100 MIN) THICK
CONTACT PIN = PHOSPHOR BRONZE, GOLD PLATED (.000050 MIN THICK) OVER NICKEL (.000100 MIN) THICK
INSULATORS = PTFE PER ASTM D 1710 OR EQUIV.
COVER = PE, NATURAL
2. CONNECTOR SUPPLIED WITH POLYETHELENE CAP TO PROTECT CONTACT.
3. ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC - 18.0 GHz
4. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO+165° C
5. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL, 901-10124, AND DATE CODE"



SCALE 2.000

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES ±.015 (0,381 mm) ±.005 (0,127 mm) ± 1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL	DRAWN C. McGRATH	DATE 10/20/03	TITLE SMA PANEL RECEPT JACK				Amphenol RF Danbury, CT, USA Tainan, Taiwan Shenzhen, China www.amphenolrf.com			
	REFERENCE EAR 1145 GEN# 901-10109-ASSY	ENGINEER O. BARTHELMES	DATE 10/20/03								
		APPROVED	DATE								
		CAD FILE I:\SMA\ 901-10124		CODE ID 74868	DWG SIZE B	DRAWING NO. 901-10124		REV B			