

Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Standard Analog Video Cable

RG-59/U Type

Jameco Part Number 232653 (9259-010-100)



Description	Part No.	UL NEC/ C(UL) CEC Type	Standard Lengths		Standard Unit Weight		Conductor (stranding) Diameter Nom. DCR	Nominal Core OD		Shielding Materials Nom. DCR	Nominal OD		Nom. Imp. (Ω)	Nom. Vel. of Prop.	Nominal Capacitance		Nominal Attenuation		
			Ft.	m	Lbs.	kg		Inch	mm		Inch	mm			pF/Ft.	pF/m	MHz	dB/ 100 Ft.	dB/ 100m

22 AWG Solid Bare Copper-covered Steel • Bare Copper Braid Shield

Polyethylene Insulation • Black PVC Jacket																			
UL AWM	8263	NEC:	U-500	U-152.4	19.5	8.9	23 AWG	.146	3.71	BC Braid	.242	6.15	75	66%	20.5	67.3	1	.6	2.0
Style 1354		CMX	U-1000	U-304.8	39.0	17.7	(solid)			95% Shield							10	1.1	3.6
(30V 60°C)		CEC:	1000	304.8	38.0	17.3	.023"			Coverage							50	2.4	7.9
		CMX					BCCS			2.6Ω/M'							100	3.4	11.2
							49.0Ω/M'			8.5Ω/km							200	4.9	16.1
							160.7Ω/km										400	7.0	23.0
																	700	9.7	31.8
																	900	11.1	36.4
																	1000	12.0	39.4

Non-contaminating Black PVC Jacket.

UL AWM	9244	NEC:	U-500	U-152.4	18.0	8.2	22 AWG	.146	3.71	BC Braid	.242	6.15	75	66%	19.4	63.6	1	.6	2.0
Style 1354		CMX	U-1000	U-304.8	36.0	16.4	(solid)			85% Shield							10	1.1	3.6
(30V 80°C)		CEC:	1000	304.8	36.0	16.4	.025"			Coverage							50	2.4	7.9
		CMX	3280	1000.0	118.1	53.8	BCCS			4.5Ω/M'							100	3.4	11.2
							50.0Ω/M'			14.8Ω/km							200	4.9	16.1
							164.0Ω/km										400	7.0	23.0
																	700	9.7	31.8
																	900	11.1	36.4
																	1000	12.0	39.4

Foam Polyethylene Insulation • Black PVC Jacket

75°C	8221		U-500	U-152.4	18.5	8.4	22 AWG	.146	3.71	BC Braid	.242	6.15	80	78%	16.3	53.5	1	.4	1.4
			500	152.4	18.5	8.4	(solid)			95% Shield							10	.9	3.0
			U-1000	U-304.8	36.0	16.4	.025"			Coverage							50	2.0	6.6
			1000	304.8	36.0	16.4	BCCS			2.6Ω/M'							100	2.9	9.5
							50.0Ω/M'			8.5Ω/km							200	4.1	13.4
							164.0Ω/km										400	5.9	19.4
																	700	7.8	25.6
																	900	8.8	28.9
																	1000	9.9	32.5

22 AWG Stranded (7x30) .030" Bare Copper • 95% Bare Copper Braid Shield

Foam Polyethylene Insulation • Black PVC Jacket																			
UL AWM	9659	NEC:	U-500	U-152.4	18.0	8.2	22 AWG	.146	3.71	BC Braid	.242	6.15	75	78%	17.3	56.7	1	.3	1.0
Style 1354		CMX	U-1000	U-304.8	36.0	16.4	(7x30)			95% Shield							10	.9	3.0
(30V 60°C)		CEC:	1000	304.8	36.0	16.4	.030"			Coverage							50	2.1	6.9
VW-1		CMX					BC			2.6Ω/M							100	3.0	9.8
							15.0Ω/M'			8.5Ω/km							200	4.5	14.8
							49.2Ω/km										400	6.6	21.6
																	700	8.9	29.2
																	900	10.1	33.1
																	1000	10.9	35.8

Non-contaminating PVC Jacket. For CCTV applications.

UL AWM	9259	NEC:	100	30.5	4.6	2.1	22 AWG	.146	3.71	BC Braid	.241	6.12	75	78%	17.3	56.7	1	.3	1.0
Style 1354		CM	U-500	U-152.4	18.5	8.4	(7x30)			95% Shield							10	.9	3.0
(30V 80°C)		CEC:	500	152.4	20.5	9.3	.030"			Coverage							50	2.1	6.9
		CM	U-1000	U-304.8	36.0	16.4	BC			2.6Ω/M							100	3.0	9.8
			1000	304.8	36.0	16.4	15.0Ω/M'			8.5Ω/km							200	4.5	14.8
							49.2Ω/km										400	6.6	21.7
																	700	8.9	29.2
																	900	10.1	33.1
																	1000	10.9	35.8

For CCTV applications.

Plenum • Foam FEP Insulation • Black FEP Jacket

200°C	89259	NEC:	100	30.5	5.1	2.3	22 AWG	.135	3.43	BC Braid	.193	4.90	75	78%	17.3	56.7	1	.3	1.0
		CMP	500†	152.4	18.0	8.2	(7x30)			95% Shield							10	.9	3.0
		CEC:	1000†	304.8	34.0	15.5	.030"			Coverage							50	2.1	6.9
		CMP FT6					BC			2.6Ω/M							100	3.0	9.8
							15.0Ω/M'			8.5Ω/km							200	4.5	14.8
							49.2Ω/km										400	6.6	21.6
																	700	9.0	29.5
																	900	10.1	33.1
																	1000	11.0	36.1

Suitable for Outdoor and Direct Burial applications.

Plenum • Foam FEP Insulation • Natural Flamarrest® Jacket

75°C	82259	NEC:	U-1000†	U-304.8	31.0	14.1	22 AWG	.135	3.43	BC Braid	.193	4.90	75	78%	17.3	56.7	1	.3	1.0
		CMP	1000†	304.8	33.0	15.0	(7x30)			95% Shield							10	.9	3.0
		CEC:					.030"			Coverage							50	2.1	6.9
		CMP FT6					BC			2.6Ω/M							100	3.0	9.8
							15.0Ω/M'			8.5Ω/km							200	4.5	14.8
							49.2Ω/km										400	6.6	21.6
																	700	9.0	29.5
																	900	10.1	33.1
																	1000	11.0	36.1

BC = Bare Copper • BCCS = Bare Copper-covered Steel • DCR = DC Resistance

Contact the Belden Customer Service Department for a Comprehensive Connector Cross Reference. 1-800-BELDEN-1. Request quotations of RG/U cables not listed.

†Spools and/or UnReel® cartons are one piece, but length may vary ±10% from length shown.

