

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [70287-1116](#)
Status: **Active**
Overview: [C-Grid® Products](#)
Description: 2.54mm Pitch C-Grid® Header, Breakaway, Dual Row, Vertical, with Retention Pin, 40 Circuits, 6.10mm Mating Pin Length, 0.38µm Gold (Au) Selective Plating

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)

[Product Specification PS-70280 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family PCB Headers
Series [70287](#)
Application Board-to-Board, Signal, Wire-to-Board
Overview [C-Grid® Products](#)
Product Name C-Grid®
UPC 822350866088

Physical

Breakaway Yes
Circuits (Loaded) 40
Circuits (maximum) 40
Color - Resin Black
Durability (mating cycles max) 25
First Mate / Last Break No
Flammability 94V-0
Glow-Wire Compliant No
Guide to Mating Part No
Keying to Mating Part N/A
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 2.669/g
Number of Rows 2
Orientation Vertical
PC Tail Length 3.18mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.57mm
Packaging Type Bag
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Plating min - Mating 0.381µm
Plating min - Termination 2.032µm
Polarized to Mating Part No
Polarized to PCB No
Shrouded No
Stackable Yes
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating -40°C to +120°C



Series

image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[70287Series](#)

Mates With
7859 Shunt, C-Grid Receptacles, SL™
Crimp, FFC and IDT Housing

Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	3A
Voltage - Maximum	250V DC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-70280
Sales Drawing	SD-70287-004

This document was generated on 08/08/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION