




AND113R/RP Standard LED

Standard Bright LED LAMPS

Weight: 0.30 g Unit: mm



AND113R/RP Standard LED T-1 3/4 Package (5 mm)

Features

- Low power requirement
- RoHS Compliant
- Flush-mount
- All plastic molded lens
- Color: GaP-Red

Optical Characteristics ($T_a = 25^\circ\text{C}$)

Color		Lens Desc.	Axial Luminous Intensity (mcd)		Test Condition (I_F -mA)	Viewing Angle $2\theta_{1/2}$ (deg)
LED	Lens		Min.	Typ.		
Red	Red	Clear	5	18	10	30

Absolute Maximum Ratings ($T_a = 25^\circ\text{C}$)

Characteristics	Symbol	Rating (Yellow)	Unit
Forward Current (DC)	I_F	25	mA
Reverse Voltage	V_R	5	V
Power Dissipation	P_D	120	mW
Operating Temperature	T_{Opr}	-40 to +85	$^\circ\text{C}$
Storage Temperature Range	T_{Stg}	-40 to +85	$^\circ\text{C}$

Electro-Optical Characteristics ($T_a = 25^\circ\text{C}$)

Characteristics	Symbol	Test Condition	Yellow			Unit
			Min.	Typ.	Max.	
Forward Voltage	V_F	$I_F = 20\text{mA}$	—	2.0	2.5	V
Reverse Current	I_R	$V_R = 5\text{V}$	—	—	10	μA
Peak Emission Wavelength	λ_p	$I_F = 15\text{mA}$	—	700	—	nm
Spectral Line Half Width	λ	$I_F = 15\text{mA}$	—	45	—	nm

Precaution

Please be careful of the following:

1. Soldering temperature: 260 $^\circ\text{C}$ max; Soldering time: 5 sec. max; Soldering portion of lead: up to 1.6 mm from the body of the device.
2. The lead can be formed up to 5 mm from the body of the device without forming stress. Soldering should be performed after the lead forming.




Product specifications contained herein may be changed without prior notice.

It is therefore advisable to contact Purdy Electronics before proceeding with the design of equipment incorporating this product.



AND113R/RP Standard LED

Standard Bright LED LAMPS



This graph shows relative luminous vs. forward current. □
At three points ($I_F = 10, 15, 20\text{mA}$) each relation is normalized.)

