


6 mm Square Thin Type SMD Light Touch Switches 6mm Square Middle Travel SMD Light Touch Switch

Type: **EVQP0**
EVQQ2
EVPBF



■ Features


- External dimensions : 6.5 mm×6.0 mm, Height 1.8 mm (Excluding the push plate)
- External dimensions : 6.0 mm×6.0 mm, Height 2.5 mm (Excluding the push plate, Middle Travel)
- With or without ground terminal, height, operating force
- Overstroke travel
- Middlestroke travel type

■ Recommended Applications


- Operating switches for other electronic equipment
- Operation switches for PC mouse
- Car audio systems
- Game

■ Explanation of Part Numbers

6 mm Square Thin Type SMD Light Touch Switches



6mm Square Middle Travel SMD Light Touch Switch





■ Specifications

Travel Type		Short Push Travel	Overstroke Travel	Middlestroke Travel
Type		Snap action/Push-on type SPST		
Electrical	Rating	10 μ A 2 Vdc to 20 mA 15 Vdc (Resistive load)		
	Contact Resistance	100 m Ω max.		500 m Ω max.
	Insulation Resistance	100 M Ω min. (at 100 Vdc)		
	Dielectric Withstanding Voltage	250 Vac for 1 minute		
	Bouncing	10 ms max. (ON, OFF)		
Mechanical	Operating Force	0.5 N, 1.0 N, 1.3 N, 1.6 N, 2.6 N, 3.5 N	0.6 N, 1.0 N	2.0 N
	Travel	0.25 mm (0.2 mm : 0.5N, 1.0N)	0.3 mm	0.25 mm
Endurance	Operating Life	0.5 N : 2000000 cycles min. 1.0 N, 1.3 N, 1.6 N : 1000000 cycles min. 2.6 N : 200000 cycles min. 3.5 N : 100000 cycles min.	0.6 N : 2000000 cycles min. 1.0 N : 1000000 cycles min.	1000000 cycles min.
Operating Temperature		-40 °C to +85 °C		
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)		
Minimum Quantity/Packing Unit		H=2.0 mm 4000 pcs. Embossed Taping (Reel Pack)	H=3.5mm 3000 pcs. Embossed Taping (Reel Pack)	
		H=2.5 mm, 3.1 mm 2000 pcs. Embossed Taping (Reel Pack)		
Quantity/Carton		H=2.0 mm 20000 pcs.		
		H=2.5 mm, 3.1 mm 10000 pcs.		

Note: Non washable

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)


No. 1					
EVQP0	(General dimension tolerance : ± 0.2) () dimensions are reference dimensions.				
Overstroke travel : 0.3 mm With J-bent terminals					
					
Part Numbers	Operating Force	Height	Push Plate Color	Ground Terminal	Operating Life
EVQP0N02B	0.6 N	2.5 mm	Blue	Without	2000000 cycles
EVQP0P02B	0.6 N	2.5 mm	Blue	With	2000000 cycles
EVQP0Q02Q	1.0 N	2.5 mm	Gray	Without	1000000 cycles
EVQP0S02Q	1.0 N	2.5 mm	Gray	With	1000000 cycles

■ Dimensions in mm (not to scale)


No. 2

EVQQ2

Short travel 0.25 mm
With J-bent terminals



(General dimension tolerance : ± 0.2)
() dimensions are reference dimensions.



Circuit Diagram

PWB land pattern for reference

Height
H
2.0 $\pm$ 0.2
2.5 $\pm$ 0.2
3.1 $\pm$ 0.2

Part Numbers	Operating Force	H=Height	Push Plate Color	Ground Terminal	Operating Life
EVQQ2B01W	0.5 N	2.0 mm	White	Without	2000000 cycles
EVQQ2B02W	0.5 N	2.5 mm	White	Without	2000000 cycles
EVQQ2B03W	0.5 N	3.1 mm	White	Without	2000000 cycles
EVQQ2D01W	0.5 N	2.0 mm	White	With	2000000 cycles
EVQQ2D02W	0.5 N	2.5 mm	White	With	2000000 cycles
EVQQ2D03W	0.5 N	3.1 mm	White	With	2000000 cycles
EVQQ2F01W	1.0 N	2.0 mm	White	Without	1000000 cycles
EVQQ2F02W	1.0 N	2.5 mm	White	Without	1000000 cycles
EVQQ2F03W	1.0 N	3.1 mm	White	Without	1000000 cycles
EVQQ2H01W	1.0 N	2.0 mm	White	With	1000000 cycles
EVQQ2H02W	1.0 N	2.5 mm	White	With	1000000 cycles
EVQQ2H03W	1.0 N	3.1 mm	White	With	1000000 cycles
EVQQ2K01W	1.3 N	2.0 mm	White	Without	1000000 cycles
EVQQ2K02W	1.3 N	2.5 mm	White	Without	1000000 cycles
EVQQ2K03W	1.3 N	3.1 mm	White	Without	1000000 cycles
EVQQ2M01W	1.3 N	2.0 mm	White	With	1000000 cycles
EVQQ2M02W	1.3 N	2.5 mm	White	With	1000000 cycles
EVQQ2M03W	1.3 N	3.1 mm	White	With	1000000 cycles
EVQQ2P01W	1.6 N	2.0 mm	White	Without	1000000 cycles
EVQQ2P02W	1.6 N	2.5 mm	White	Without	1000000 cycles
EVQQ2P03W	1.6 N	3.1 mm	White	Without	1000000 cycles
EVQQ2S01W	1.6 N	2.0 mm	White	With	1000000 cycles
EVQQ2S02W	1.6 N	2.5 mm	White	With	1000000 cycles
EVQQ2S03W	1.6 N	3.1 mm	White	With	1000000 cycles
EVQQ2U01W	2.6 N	2.0 mm	White	Without	200000 cycles
EVQQ2U02W	2.6 N	2.5 mm	White	Without	200000 cycles
EVQQ2U03W	2.6 N	3.1 mm	White	Without	200000 cycles
EVQQ2W01W	2.6 N	2.0 mm	White	With	200000 cycles
EVQQ2W02W	2.6 N	2.5 mm	White	With	200000 cycles
EVQQ2W03W	2.6 N	3.1 mm	White	With	200000 cycles
EVQQ2Y01W	3.5 N	2.0 mm	White	Without	100000 cycles
EVQQ2Y02W	3.5 N	2.5 mm	White	Without	100000 cycles
EVQQ2Y03W	3.5 N	3.1 mm	White	Without	100000 cycles
EVQQ2201W	3.5 N	2.0 mm	White	With	100000 cycles
EVQQ2202W	3.5 N	2.5 mm	White	With	100000 cycles
EVQQ2203W	3.5 N	3.1 mm	White	With	100000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ 形状寸法 (mm)



No. 3

EVPBF


Middlestroke Travel 0.25 mm
With J-bent terminals



(General dimension tolerance : ± 0.2)
() dimensions are reference dimensions.



Circuit Diagram



PWB land pattern for reference


 : Recommended land pattern area.

 : No soldering area.


- Any land pattern or via holes shall not be provided at  area.
- If it's necessary to design land pattern or via holes at  area, please apply resist to them to protect their metal part completely.
- If their metal parts are not protected completely, short circuit failure may occur by solder ball.
- Beside, there should be convexoconcave by designing additional pattern, it may cause with tilt, influence on solder-ability or flux intrusion after reflow soldering.
- Therefore, please study any influence of additional land pattern or via holes at  area in advance.

Part Numbers	Operating Force	Height	Push Plate Color	Ground Terminal	Operating Life
EVPBFAC1A000	2.0 N	3.5 mm	Gray	Without	1000000 cycles

■ Recommended Reflow Soldering Conditions




● Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	P ₁	P ₂	P ₀	D ₀ Dia	t ₁	t ₂
EVQQ2	2.0	6.7±0.2	7.4±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 ^{+0.1} ₀	0.30±0.05	2.2±0.2
	2.5/3.1											3.2±0.2
EVQP0	2.5											2.8±0.2
EVPBF	3.5											3.7±0.1


● Standard Reel Dimensions in mm (not to scale)



Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.5	φ21.0±1.0	2.0±0.5

Item	W	T	t	r
Rate (mm)	13.5±1.0	17.5±1.0	—	—

■ Recommended Shape of Test Pole



■ Recommended Operating Conditions

