


Connectors in 3.50 mm pitch Series BL/SL 3.50

BL 3.50/./90 & 270



Female plug with clamping-yoke screw system for connecting wires with 90° and 270° angled orientation in 3.5 mm pitch. The female plugs are also available with a flange (F). They include space for labelling and can be coded.

Product data

IEC: 320 V / 12 A / 0.2 - 1.5 mm²
UL: 300 V / 8 A / AWG 28 - 14


For additional articles and information, refer to catalog.weidmuller.com

- Note:**
- Additional colours on request
 - Gold-plated contact surfaces on request
 - Rated current related to rated cross-section and min. No. of poles.
 - Max. O.D. of conductor: 2.9 mm
 - Wire end ferrule without plastic collar to DIN 46228/1
 - Wire end ferrule with plastic collar to DIN 46228/4
 - P on drg. = pitch
 - Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

BL 3.50/./90



Dimensioned drawing



Technical data

In compliance with IEC 60664-1 / IEC 61984

Clamping range, max.	mm ²	0.08...1.5
Solid core H05(07) V-U	mm ²	0.2...1.5
Stranded H07 V-R		
Flexible H05(07) V-K	mm ²	0.2...1.5
Flexible with ferrule	mm ²	0.2...1.5
Ferrule with plastic collar	mm ²	0.2...1.5
Stripping length	mm	6
Screwdriver blade	mm	0.4 x 2.5
According to norm		DIN 5264
Tightening torque range	Nm	0.2...0.25
Rated current, max.	A	12 10
At ambient temperature	20°C 40°C	
For conductor cross-section	mm ²	1.5
Overvoltage category	III III II	
Pollution severity	3 2 2	
Rated voltage	V	160 160 320
Rated impulse voltage	kV	2.5 2.5 2.5
UL / CUL (Use Group)	B C D	
Rated voltage	V	300 300
Rated current	A	8 8
AWG conductor	AWG	28-14
CSA (Use Group)	B C D	
Rated voltage	V	300 300
Rated current	A	10 10
AWG conductor	AWG	28-14
General data		
Type of insulation material		PBT
Flammability class UL 94		V-0
Contact base material		Copper alloy
Material of contact surface		tinned
Pin dimensions = d	mm	
Solder eyelet Ø = D	mm	
Solder eyelet Ø tolerance	mm	

Accessories


Note: Refer to the Accessories chapter for additional accessories.

Coding	Order No.
BL SL 3.5 KO OR	1693430000
BL SL 3.5 KO SW	1610100000
Screwdriver	
SD 0,4x2,5x75	9009030000
SDI 0,4x2,5x75	9008370000

Ordering data

Solder pin length			orange		black	
Colour						
Pitch	3.50 mm					
Pol.	L1	(inch)	Qty.	Order No.	Order No.	
2	3.50	0.138	100	1638550000	1638780000	
3	7.00	0.276	100	1638560000	1638790000	
4	10.50	0.413	100	1638570000	1638800000	
5	14.00	0.551	50	1638580000	1638810000	
6	17.50	0.689	50	1638590000	1638820000	
7	21.00	0.827	50	1638600000	1638830000	
8	24.50	0.965	50	1638610000	1638840000	
9	28.00	1.102	50	1638620000	1638850000	
10	31.50	1.240	50	1638630000	1638860000	
11	35.00	1.378	50	1638640000	1638870000	
12	38.50	1.516	50	1638650000	1638880000	
13	42.00	1.654	50	1638660000	1638890000	
14	45.50	1.791	50	1638670000	1638900000	
15	49.00	1.929	50	1638680000	1638910000	
16	52.50	2.067	50	1638690000	1638920000	
17	56.00	2.205	20	1638700000	1638930000	
18	59.50	2.343	20	1638710000	1638940000	
19	63.00	2.480	20	1638720000	1638950000	
20	66.50	2.618	20	1638730000	1638960000	
21	70.00	2.756	20	1638740000	1638970000	
22	73.50	2.894	20	1638750000	1638980000	
23	77.00	3.031	20	1638760000	1638990000	
24	80.50	3.169	20	1638770000	1639000000	


Representative derating curve



BL 3.50/./90F



Dimensioned drawing




Ordering data

Solder pin length					
Colour			orange		black
Pitch			3.50 mm		
Pol.	L1	(inch)	Qty.	Order No.	Order No.
2	3.50	0.138	100	1639010000	1639240000
3	7.00	0.276	100	1639020000	1639250000
4	10.50	0.413	100	1639030000	1639260000
5	14.00	0.551	50	1639040000	1639270000
6	17.50	0.689	50	1639050000	1639280000
7	21.00	0.827	50	1639060000	1639290000
8	24.50	0.965	50	1639070000	1639300000
9	28.00	1.102	50	1639080000	1639310000
10	31.50	1.240	50	1639090000	1639320000
11	35.00	1.378	50	1639100000	1639330000
12	38.50	1.516	50	1639110000	1639340000
13	42.00	1.654	50	1639120000	1639350000
14	45.50	1.791	50	1639130000	1639360000
15	49.00	1.929	50	1639140000	1639370000
16	52.50	2.067	50	1639150000	1639380000
17	56.00	2.205	20	1639160000	1639390000
18	59.50	2.343	20	1639170000	1639400000
19	63.00	2.480	20	1639180000	1639410000
20	66.50	2.618	20	1639190000	1639420000
21	70.00	2.756	20	1639200000	1639430000
22	73.50	2.894	20	1639210000	1639440000
23	77.00	3.031	20	1639220000	1639450000
24	80.50	3.169	20	1639230000	1639460000

BL 3.50/./270



Dimensioned drawing




Ordering data

Solder pin length					
Colour			orange		black
Pitch			3.50 mm		
Pol.	L1	(inch)	Qty.	Order No.	Order No.
2	3.50	0.138	100	1639470000	1639700000
3	7.00	0.276	100	1639480000	1639710000
4	10.50	0.413	100	1639490000	1639720000
5	14.00	0.551	50	1639500000	1639730000
6	17.50	0.689	50	1639510000	1639740000
7	21.00	0.827	50	1639520000	1639750000
8	24.50	0.965	50	1639530000	1639760000
9	28.00	1.102	50	1639540000	1639770000
10	31.50	1.240	50	1639550000	1639780000
11	35.00	1.378	50	1639560000	1639790000
12	38.50	1.516	50	1639570000	1639800000
13	42.00	1.654	50	1639580000	1639810000
14	45.50	1.791	50	1639590000	1639820000
15	49.00	1.929	50	1639600000	1639830000
16	52.50	2.067	50	1639610000	1639840000
17	56.00	2.205	20	1639620000	1639850000
18	59.50	2.343	20	1639630000	1639860000
19	63.00	2.480	20	1639640000	1639870000
20	66.50	2.618	20	1639650000	1639880000
21	70.00	2.756	20	1639660000	1639890000
22	73.50	2.894	20	1639670000	1639900000
23	77.00	3.031	20	1639680000	1639910000
24	80.50	3.169	20	1639690000	1639920000

BL 3.50/./270F



Dimensioned drawing



Ordering data

Solder pin length					
Colour		orange		black	
Pitch 3.50 mm					
Pol.	L1	(inch)	Qty.	Order No.	Order No.
2	3.50	0.138	100	1639930000	1640160000
3	7.00	0.276	100	1639940000	1640170000
4	10.50	0.413	100	1639950000	1640180000
5	14.00	0.551	50	1639960000	1640190000
6	17.50	0.689	50	1639970000	1640200000
7	21.00	0.827	50	1639980000	1640210000
8	24.50	0.965	50	1639990000	1640220000
9	28.00	1.102	50	1640000000	1640230000
10	31.50	1.240	50	1640010000	1640240000
11	35.00	1.378	50	1640020000	1640250000
12	38.50	1.516	50	1640030000	1640260000
13	42.00	1.654	50	1640040000	1640270000
14	45.50	1.791	50	1640050000	1640280000
15	49.00	1.929	50	1640060000	1640290000
16	52.50	2.067	50	1640070000	1640300000
17	56.00	2.205	20	1640080000	1640310000
18	59.50	2.343	20	1640090000	1640320000
19	63.00	2.480	20	1640100000	1640330000
20	66.50	2.618	20	1640110000	1640340000
21	70.00	2.756	20	1640120000	1640350000
22	73.50	2.894	20	1640130000	1640360000
23	77.00	3.031	20	1640140000	1640370000
24	80.50	3.169	20	1640150000	1640380000