


**C1005X5R0J104K050BA** (TDK item description : C1005X5R0J104KT\*\*\*\*)

Applications	 Commercial Grade
Feature	<b>General</b> General (Up to 50V)
Series	C1005 [EIA CC0402]



Size	
Length(L)	1.00mm +/-0.05mm
Width(W)	0.50mm +/-0.05mm
Thickness(T)	0.50mm +/-0.05mm
Terminal Width(B)	0.10mm Min.
Terminal Spacing(G)	0.30mm Min.
Recommended Land Pattern(PA)	0.30 to 0.50mm
Recommended Land Pattern(PB)	0.35 to 0.45mm
Recommended Land Pattern(PC)	0.40 to 0.60mm
Recommended Slit Pattern(SD)	

Electrical Characteristics	
Capacitance	100nF +/-10%
Rated Voltage	6.3Vdc
Temperature Characteristic	X5R(+/-15%)
Dissipation Factor	5% Max.
Insulation Resistance	1000MΩ Min.

Other	
Soldering Method	Reflow
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	10000Pcs Min.


•This PDF document was created based on the data listed on the TDK Corporation website.  
 •All specifications are subject to change without notice.

# C1005X5R0J104K050BA


**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)




**C1005X5R0J104K050BA**



**C1005X5R0J104K050BA**




**C1005X5R0J104K050BA**



**C1005X5R0J104K050BA**



**C1005X5R0J104K050BA(DC Bias = 0V)** **C1005X5R0J104K050BA(DC Bias = 3.15V)**



**C1005X5R0J104K050BA(100kHz)** **C1005X5R0J104K050BA(500kHz)**  
**C1005X5R0J104K050BA(1MHz)**

•This PDF document was created based on the data listed on the TDK Corporation website.  
 •All specifications are subject to change without notice.