

General Purpose Transistor (PNP)

MMBT2907A



Features

Epitaxial Planar Die Construction
Complementary NPN Type Available (MMBT2222A)
Ideal for Medium Power Amplification and Switching



Mechanical Data

Case: SOT-23 Plastic Package
Weight: approx. 0.008g



Maximum Ratings & Thermal Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Rating	Symbol	2907	2907A	Unit
Collector–Emitter Voltage	V _{CEO}	–40	–60	Vdc
Collector–Base Voltage	V _{CBO}	–60		Vdc
Emitter–Base Voltage	V _{EBO}	–5.0		Vdc
Collector Current — Continuous	I _C	–600		mAdc

Characteristic	Symbol	Max	Unit
Total Device Dissipation FR–5 Board ⁽¹⁾ T _A = 25°C Derate above 25°C	P _D	225 1.8	mW mW/°C
Thermal Resistance, Junction to Ambient	R _{θJA}	556	°C/W
Total Device Dissipation Alumina Substrate, ⁽²⁾ T _A = 25°C Derate above 25°C	P _D	300 2.4	mW mW/°C
Thermal Resistance, Junction to Ambient	R _{θJA}	417	°C/W
Junction and Storage Temperature	T _J , T _{stg}	–55 to +150	°C

General Purpose Transistor (PNP)

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Characteristic	Symbol	Min	Max	Unit
OFF CHARACTERISTICS				
Collector–Emitter Breakdown Voltage ⁽³⁾ ($I_C = -10\text{ mAdc}$, $I_B = 0$)	$V_{(BR)CEO}$	-40 -60	— —	Vdc
Collector–Base Breakdown Voltage ($I_C = -10\text{ }\mu\text{Adc}$, $I_E = 0$)	$V_{(BR)CBO}$	-60	—	Vdc
Emitter–Base Breakdown Voltage ($I_E = -10\text{ }\mu\text{Adc}$, $I_C = 0$)	$V_{(BR)EBO}$	-5.0	—	Vdc
Collector Cutoff Current ($V_{CE} = -30\text{ Vdc}$, $V_{BE(off)} = -0.5\text{ Vdc}$)	I_{CEX}	—	-50	nAdc
Collector Cutoff Current ($V_{CB} = -50\text{ Vdc}$, $I_E = 0$)	I_{CBO}	— —	-0.020 -0.010	μAdc
($V_{CB} = -50\text{ Vdc}$, $I_E = 0$, $T_A = 125^\circ\text{C}$)		— —	-20 -10	
Base Current ($V_{CE} = -30\text{ Vdc}$, $V_{EB(off)} = -0.5\text{ Vdc}$)	I_B	—	-50	nAdc

ON CHARACTERISTICS

DC Current Gain ($I_C = -0.1\text{ mAdc}$, $V_{CE} = -10\text{ Vdc}$)	MMBT2907 MMBT2907A	h_{FE}	35 75	— —	—
($I_C = -1.0\text{ mAdc}$, $V_{CE} = -10\text{ Vdc}$)	MMBT2907 MMBT2907A		50 100	— —	
($I_C = -10\text{ mAdc}$, $V_{CE} = -10\text{ Vdc}$)	MMBT2907 MMBT2907A		75 100	— —	
($I_C = -150\text{ mAdc}$, $V_{CE} = -10\text{ Vdc}$) (3)	MMBT2907 MMBT2907A		— 100	— 300	
($I_C = -500\text{ mAdc}$, $V_{CE} = -10\text{ Vdc}$) (3)	MMBT2907 MMBT2907A		30 50	— —	
Collector–Emitter Saturation Voltage (3) ($I_C = -150\text{ mAdc}$, $I_B = -15\text{ mAdc}$) ($I_C = -500\text{ mAdc}$, $I_B = -50\text{ mAdc}$)		$V_{CE(sat)}$	— —	-0.4 -1.6	Vdc
Base–Emitter Saturation Voltage (3) ($I_C = -150\text{ mAdc}$, $I_B = -15\text{ mAdc}$) ($I_C = -500\text{ mAdc}$, $I_B = -50\text{ mAdc}$)		$V_{BE(sat)}$	— —	-1.3 -2.6	Vdc

1.FR-5 = 1.0 X 0.75 X 0.062 in.

2.Alumina = 0.4 X 0.3 X 0.024 in. 99.5% alumina.

SMALL-SIGNAL CHARACTERISTICS

Current-Gain — Bandwidth Product (3),(4) ($I_C = -50\text{ mAdc}$, $V_{CE} = -20\text{ Vdc}$, $f = 100\text{ MHz}$)	f_T	200	—	MHz
Output Capacitance ($V_{CB} = -10\text{ Vdc}$, $I_E = 0$, $f = 1.0\text{ MHz}$)	C_{obo}	—	8.0	pF
Input Capacitance ($V_{EB} = -2.0\text{ Vdc}$, $I_C = 0$, $f = 1.0\text{ MHz}$)	C_{ibo}	—	30	pF

SWITCHING CHARACTERISTICS

Turn-On Time	$(V_{CC} = -30\text{ Vdc}$, $I_C = -150\text{ mAdc}$, $I_{B1} = -15\text{ mAdc}$)	t_{on}	—	45	ns
Delay Time		t_d	—	10	
Rise Time		t_r	—	40	
Turn-Off Time	$(V_{CC} = -6.0\text{ Vdc}$, $I_C = -150\text{ mAdc}$, $I_{B1} = I_{B2} = -15\text{ mAdc}$)	t_{off}	—	100	ns
Storage Time		t_s	—	80	
Fall Time		t_f	—	30	

3. Pulse Test: Pulse Width $\leq 300\text{ }\mu\text{s}$, Duty Cycle $\leq 2.0\%$.
4. f_T is defined as the frequency at which $|h_{fe}|$ extrapolates to unity.




Figure 1. Delay and Rise Time Test Circuit




Figure 2. Storage and Fall Time Test Circuit

TYPICAL CHARACTERISTICS




Figure 3. DC Current Gain




Figure 4. Collector Saturation Region




Figure 5. Turn-On Time




Figure 6. Turn-Off Time

TYPICAL SMALL-SIGNAL CHARACTERISTICS

NOISE FIGURE

$V_{CE} = 10 \text{ Vdc}$, $T_A = 25^\circ\text{C}$




Figure 7. Frequency Effects




Figure 8. Source Resistance Effects




Figure 9. Capacitances




Figure 10. Current-Gain — Bandwidth Product




Figure 11. "On" Voltage




Figure 12. Temperature Coefficients