

Related Products



USB to MotherBoard 4-Pin Slot



USB Panel Mount B to Socket



USB Panel Mount Type A Cable



USB Type-A Dust Covers



USB Wall Plate - Single

More Information

[Custom Wall Plates & Panel-Mount Cables](#)

[DataPro's USB Guide and FAQ](#)

[DataPro's USB 3 Guide and FAQ](#)

[Technical Info Home](#)



USB Panel-Mount to 5-pin Socket

Categories:

> [USB 2.0 Cables](#), [USB Panel-Mount Cables](#), [Panel-Mount USB-A Cables](#)


Add USB ports to your computer case, custom hardware, or OEM system, quickly and easily! This mounting cable provides a female USB port wherever it's installed, and the PCB pins at the other end terminate directly on a motherboard or other controller.



DataPro

1590-01C	USB Panel Mount A to Socket	1 ft	2035 in stock	+ Add to cart
1590-02C	USB Panel-Mount A to Socket	2 ft	105 in stock	+ Add to cart
1590-03C	USB Panel-Mount A to Socket	3 ft	622 in stock	+ Add to cart
1590-00C	USB Panel Mount A to Socket		Custom build at + per foot.	+ Add to cart

The DataPro 1590 USB cable is a jumper cable that provides a panel-mounting USB port to any device with PCB headers, such as any modern motherboard or a custom OEM device.



Available with an unpolarized connector!
This cable can be built with an unpolarized 2.54mm header connector. [Contact](#) us for details.

Technical Documents

☐ I agree to the [Terms of Service](#).



DOWNLOAD




DOWNLOAD

This cable features a 5-pin PCB connector (header) at 0.100 pitch, with separate signal and wire grounds. We also carry a [Panelmount USB to 4-pin cable](#) for combined grounds, for terminating on a 4-pin board.

This external connector includes two mounting screws for secure attachment to a chassis, frontpanel, or backplane. It is a panel-mount USB A-type female with size 4-40 screws, and the nuts are inset in the molded hood so they won't get lost. No threading is required on the mounting panel.

This product supports USB 2.0 high-speed data transfer rates.

Cutout Dimensions (in mm)



[Click here for PDF version](#)

Features:

- USB 1.1/2.0 High-Speed Compatible
- CL2 rated for in-wall use
- Embedded 4-40 nuts with mounting screws included

Specifications:

- Home
- Custom Wall Plates
- Custom Panels
- Custom Enclosures
- Custom Rack Mount Solutions
- Custom Cables
- Machining Services
- Pelican Case Panels
- Storm Case Panels
- Nanuk Case Panels
- Seahorse Case Panels

- Stock Wall Plates
- Enclosures & Cases
- Panel-Mount Cables
- Panel-Mount Couplers
- Dust Covers

USB Cables

- USB 3.0 and 3.1 Products
- USB 2.0 Cables
- USB-C Cables
- USB Hubs & Cards
- USB Adaptors

- FireWire Cables
- Video Cables
- Video Electronics
- Keyboard & Mouse
- Audio Cables
- Networking
- Fiber Optic
- Wireless Products
- SCSI
- Serial & Parallel
- Manual Switches
- Other Data Cables
- Power Cables
- Server Racks
- Clearance & Specials

- Contact Us
- Support
- Order Status
- Tech Info
 - USB Info
 - USB 3 Info
 - USB-C Info
 - HDMI Info
 - DisplayPort Info
 - Thunderbolt Info
 - DVI Info

(more articles)

- Max speed 480Mbit/s
- Allowable panel depth: 4.5mm (full mating)
- Recommended screw installation: hand tighten, 2.0 in-lbs maximum torque



[FAQ](#) | [Terms & Conditions](#) | [Privacy Policy](#) | [Cookie Statement](#)
© 1986-2018 DataPro International Inc., Seattle, WA