

Power Diodes

Controlled Avalanche




Features:

- For surface mounted application
- Metal to silicon rectifier, majority carrier conduction
- Low forward voltage drop
- Easy pick and place
- High surge current capability
- Epitaxial construction
- High temperature soldering : 250°C / 10 seconds at terminals

Mechanical Data

Cases : Moulded plastic
 Terminals : Solder plated
 Polarity : Indicated by cathode band

SMA/DO-214AC



Dimensions : Inches (Millimetres)

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%

Type Number	SS14	SS16	SS110	Unit
Maximum Recurrent Peak Reverse Voltage	40	60	100	V
Maximum RMS Voltage	28	42	70	
Maximum DC Blocking Voltage	40	60	100	



Power Diodes

Controlled Avalanche





Type Number	SS14	SS16	SS110	Unit
Maximum average forward rectified current at T _L (See Figure 1)	1			A
Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load (JEDEC method)	30			
Maximum Instantaneous forward voltage (Note) at 1 A	0.5	0.75	0.8	V
Maximum DC reverse current at TA = 25°C at rated DC blocking voltage at TA = 100°C	0.5		0.05	mA
	10	5	0.5	
Typical thermal resistance (Note 2) RθJL RθJA	28 88			°C / W
Operating temperature range T _J	-65 to +125	-65 to +150		°C
Storage temperature range T _{STG}	-65 to +150			

Notes:

1. Pulse test with $PW = 300 \mu$ seconds, 1% duty cycle
2. Measured on PC Board with 0.2×0.2 inches (5×5 mm) copper pad areas

Ratings and Characteristic Curves



Power Diodes

Controlled Avalanche



Rating and Characteristic Curves

Figure 3 Typical Forward Characteristics




Figure 4 Typical Reverse Characteristics





Figure 5 Typical Junction Capacitance



Specification Table

I_F (AV) (A)	T_C (°C)	V_{RRM} (V)	V_{FM} maximum (V)	I_{RM} maximum (mA)	Package	Part Number
1	105	40	0.5	0.5	DO-214AC (SMA)	SS14
		60	0.75			SS16
		100	0.8	0.05		SS110

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

