

THIS DRAWING IS UNPUBLISHED.
QUESTO DISEGNO NON DEVE ESSERE DIVULGATO O RIPRODOTTO

RELEASED FOR PUBLICATION
E' CONSENTITA LA DIVULGAZIONE

2002

© COPYRIGHT 2002

BY -

ALL RIGHTS RESERVED.
TUTTI I DIRITTI SONO RISERVATI

CONNECTOR OVERALL DIMENSIONS WITH COVER KIT AND LEVER ASSEMBLED
(DIMENSIONI DI INGOMBRO CONNETTORE CON KIT COPERCHIO E LEVA MONTATI)

80.0

5.7

74.4

20.0

↑

"A"

8x2.5=20.0

4x3.5=14.0

3.0

7.7

3.0

3.0

0.5

3.0

VIEW FROM A

CONTACT INSERT SIDE VIEW
(VISTA LATO INSERIMENTO CONTATTI)

15

30

45

60

1

16

31

46

➔ CABLE EXIT
USCITA CAVI

CAVITIES POSITIONS
(POSIZIONE IN CAVITA')

CONTACT P/N (P/N CONTATTO)	POSITION (POSIZIONE)
968220-1 & 968221-1	6 to 14; 21 to 29; 36 to 44; 51 to 59
1452158-1 & 1241608-1	1 to 5; 15 to 20; 30 to 35; 45 to 50; 60

-	1	PA6.6 GF30	YELLOW	/	C.P.A. Disp. controllo aggancio leva	5
1	1	PA6.6 GF13	BLACK	/	COVER / Coperchio	4
1	1	PA6.6 GF30	BLACK	/	LEVER / Leva	3
1	1	PA6.6 GF30	VIOLET	/	SECONDARY LOCK 60 POSN. Disp. Ritenz. secondaria, 60 pos.	2
1	1	PA6.6 GF25/PBT+ASA-GF20 PA6.6 GF13 + GF33 SILICON	BLACK/LIGHT BROWN:HOUSING YELLOW:PERIPHERAL SEAL RED-BROWN:FAMILY SEAL	/	CARRIER HSG. / Corpo connettore	1
QTY.	QTY.	RAW MATERIALS Materiali	COLOURS Colori	REV	DESCRIPTION Descrizione	ITEM Pos.
284742-2 (NOTE 6)	284742-1 (NOTE 5)	PART-NO. Codice				
E	E	REV				

LOC

DIST

1


-

REVISIONS
REVISIONI

P	LTR REV	DESCRIPTION DESCRIZIONE	DATE DATA	DWN DIS.	APVD APP.
	E2	REVISED PER ECO-11-005033	24MAR2011	RK	HMR
	E3	ECR-12-016488		M.P.	M.G.

P/N 284742-1 AS SHOWN
FIAT VERSION

HOUSING AS SUPPLIED
(CORPO CONNETTORE COME FORNITO)



NOTE:

1) CONNECTOR IS SUITABLE TO BE MATED WITH COUNTERPART P/N 284617-1
(IL CONNETTORE SI ACCOPPIA CON LA CONTROPARTE P/N 284617-1)

2) CONNECTOR CAVITIES ARE SUITABLE FOR CONTACTS:
(LE CAVITA' DEL CONNETTORE SONO ADATTE PER CONTATTI:)

- 0.64 MQS Clean Body contact WSR 0.35±0.50 mm² P/N 1703296-1 (FIAT restricted version)
(Minimum isolation diameter: 1.2 mm; Maximum isolation diameter: 1.6 mm)
- 0.64 MQS Clean Body contact WSR 0.35 mm² P/N 968220-1
(Minimum isolation diameter: 1.2 mm; Maximum isolation diameter: 1.3 mm)
- 0.64 MQS Clean Body contact WSR 0.75 mm² P/N 1703298-1 (FIAT restricted version)
(Minimum isolation diameter: 1.7 mm; Maximum isolation diameter: 1.9 mm)
- 0.64 MQS Clean Body contact WSR 0.50±0.75 mm² P/N 968221-1
(Minimum isolation diameter: 1.4 mm; Maximum isolation diameter: 1.9 mm)
- 1.5 mm Clean Boby contact WSR 0.50 mm² P/N 1452158-1
(Minimum isolation diameter: 1.4 mm; Maximum isolation diameter: 1.6 mm)
- 1.5 mm Clean Boby contact WSR 0.75±1.50 mm² P/N 1241608-1
(Minimum isolation diameter: 1.7 mm; Maximum isolation diameter: 2.4 mm)

3) TO CLOSE UNUSED CAVITIES:
(PER CHIUDERE LE CAVITA' NON UTILIZZATE)

- P/N 284583-1 for MQS Clean Body contacts
- P/N 1394872-1 for 1.5 mm Clean Body contact

4) ITEMS 2 AND 3 ARE SUPPLIED NOT ASSEMBLED IN THE SAME PACKAGE.
(I PARTICOLARI 2 E 3 SONO FORNITI NON ASSEMBLATI NELLA STESSA CONFEZIONE.)

5) ITEMS 4 AND 5 ARE SUPPLIED PRE-ASSEMBLED, IN THE SAME PACKAGE.
(I PARTICOLARI 4 E 5 SONO FORNITI PRE-ASSEMBLATI NELLA STESSA CONFEZIONE)

6) ITEMS 4 IS SUPPLIED NOT ASSEMBLED IN THE SAME PACKAGE
ITEM 5 IS NOT SUPPLIED
(L'ITEM 4 E' FORNITO NON ASSEMBLATO NELLA STESSA CONFEZIONE, L'ITEM 5 NON E' FORNITO.)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
DIMENSIONI:
(MM)

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
TOLLERANZE: SE NON
DIVERSAMENTE SPECIFICATO

0 PLC/DEC: ±0.3
1 PLC/DEC: ±0.3
2 PLC/DEC: ±0.3
3 PLC/DEC: ±
4 PLC/DEC: ±
ANGLES/ANGOLI ±30°

MATERIAL
MATERIALE

-

FINISH
FINITURA

-

DWN/DIS.
D. BISETTI
CHK/CONT.
O. CANUTO
APVD/APP.
A. GENIA

03OCT01
03OCT01
03OCT01

PRODUCT SPEC
SPEC. DI PRODOTTO
108-20235
APPLICATION SPEC
SPEC. DI APPLICAZIONE
I.S. 411-20067

WEIGHT
PESO
-

CUSTOMER DRAWING

TE Connectivity

CONNECTOR HOUSING, 60 POS.
MQS, 1.5mm Clean Body Contacts
+ COVER AND C.P.A. KIT

SIZE
A2

CAGE CODE
00779

DRAWING NO.
C=284742

RESTRICTED TO
-

SCALE
SCALA

1:1

SHEET
FOGLIO

OF
DI

REV
E3

1471-9 (3/11)