





FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLE




mat'l. code SEE NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC			
ltr	ecm no	dr	date	tolerances unless otherwise specified				INCH/MM	title				
E	V40227	PDP	1/11/94	angles	linear	.XX ±.01/.3			3 ROW R/A HEADER				
F	V90522	HTB	2/26/99			.XXX ±.005/.13			SOLDER TO BOARD, 0 G.P.				
G	V00262	JWS	1/25/00			.XXXX ±.0020/.051			scale 1:1				
H	V02768	LSS	11/21/00	dr	D. SHEAFFER	6/05/91			dwg no		sheet 1 of 3	size	
J	V05-0756	DAI	10/07/05	enr	S. CLARK	6/05/91			50119		A3		
K	V05-1040	HTB	11/14/05	chr	S. CLARK	6/05/91							
L	M06-0255	MNR	7/06/06	appd	S. CLARK	6/05/91			type		Product	Customer	Drawing
sheet	revision	L	L	L									
index	sheet	1	2	3									


form: A3

1 2 3 4 5 6


PRODUCT NUMBER
SEE TABLE



SECTION U-U



SECTION X-X



RECOMMENDED PCB LAYOUT
(ALL HOLES LOCATED ON .100/2.54 GRID
UNLESS OTHERWISE SPECIFIED)

mat'l. code SEE NOTE 3		surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecr	no	dr	date	title
L					3 ROW R/A HEADER SOLDER TO BOARD, 0 G.P.
					dwg no
					50119
					type
					Product Customer Drawing
sheet index	revision sheet				

PRODUCT NUMBER	NUMBER OF POSITIONS SEE NOTE 2	TAIL LENGTH REF.	TERMINAL PLATING
50119 - 1YYYH	YYY	.180/4.57	30μ"/.76μ GOLD
50119 - 1YYYJ	YYY	.120/3.05	30μ"/.76μ GOLD
50119 - 3YYYH	YYY	.180/4.57	50μ"/1.27μ GOLD
50119 - 3YYYJ	YYY	.120/3.05	50μ"/1.27μ GOLD
50119 - 5YYYH	YYY	.180/4.57	30μ"/.76μ GXT
50119 - 5YYYHLF	YYY	.180/4.57	30μ"/.76μ GXT
50119 - 5YYYJ	YYY	.120/3.05	30μ"/.76μ GXT
50119 - 5YYYJLF	YYY	.120/3.05	30μ"/.76μ GXT

NOTES:

1. PRODUCT NUMBERING CODE:

50119 - X YYY Z LF

LEAD FREE (OPTIONAL)
TAIL LENGTH SEE TABLE
NO. OF POSITIONS SEE NOTE 2
PLATING SEE TABLE
BASE NUMBER

PRODUCT NUMBERING CODE FOR
SELECT LOAD PART NUMBERS:

50119 - XXYYY LF

LEAD FREE (OPTIONAL)
SEQUENCE NUMBER
ALWAYS 'XX'
BASE NUMBER

2. THIS PRODUCT IS CONFIGURED IN SIZES OF 6 THRU 80 COLUMNS IN INCREMENTS OF ONE.
i.e.: 6,7,8,9,.....78,79,80.

3. HOUSING MATERIAL: GLASS AND MINERAL FILLED
HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER
UL94V-0. COLOR: BLACK.
PIN MATERIAL: PHOS. BRONZE

4. MANUFACTURE'S NAME, P/N, AND LOT CODE TO APPEAR ON
THIS SURFACE PER BUS-12-108.

5. LENGTH FORMULAS:

DIM "A" = .100/2.54 x NO. OF COLUMNS + .75/19.1

DIM "B" = .100/2.54 x NO. OF COLUMNS + .450/11.43

DIM "C" = .100/2.54 x NO. OF COLUMNS - .100/2.54

6. THIS PRODUCT (WITH "LF" SUFFIX) MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
7. THIS HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE
FOR 10-30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE
REFLOW OVEN.

mat'l. code SEE NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection INCH/MM		product family HPC	
ltr ecn no dr date				tolerances unless otherwise specified						title	
L				angles		linear		INCH/MM		3 ROW R/A HEADER	
										SOLDER TO BOARD, 0 G.P.	
				0°±2'				scale 1:1		dwg no	
				dr		D. SHEAFFER		6/05/91		sheet 3 of 3 size	
				enr		S. CLARK		6/05/91		50119 A3	
				chr		S. CLARK		6/05/91		type	
				appd		S. CLARK		6/05/91		Product Customer Drawing	
sheet index		revision sheet									