


DESCRIPTION: .370" STAMPED FEMALE R/A D-SUB CONNECTOR



192-025-Y13RYY1

SERIES _____

NUMBER OF CONTACTS _____

GENDER _____

1 = MALE

2 = FEMALE (NO GROUND INDENTS)

PC MOUNT _____

3 = NICKEL SHELL _____

HARDWARE OPTIONS: _____

16 = .120 MATING HOLE WITH INSIDE GROUND STRAP

17 = 4-40 INSERT WITH INSIDE GROUND STRAP

18 = 4-40 STANDOFF WITH INSIDE GROUND STRAP

53 = 4-40 INSERT WITH FORK BOARD LOCKS

56 = 4-40 STANDOFF WITH FORK BOARD LOCKS

PLATING: _____

1 = GOLD FLASH

MATERIALS:

INSULATOR: NYLON 9T, UL94V-0 - 260°C PROCESS TEMP
CHEMICAL RESISTANCE, COLOR BLACK


SHELL: STEEL, NICKEL TIN PLATED

CONTACT: MALE: BRASS; FEMALE: PHOSPHOR BRONZE
GOLD FLASH - MATING AREA
TIN PLATING ON TAIL ENDS

RoHS COMPLIANT

ELECTRICAL:

CURRENT RATING: 5 AMPERES
DIELECTRIC WITHSTANDING VOLTAGE: 1000VAC rms AT SEA LEVEL
INSULATION RESISTANCE: 5000 MEGOHMS MIN.
CONTACT RESISTANCE: 10 MILLIOHMS MAX.
WORKING TEMPERATURE: -55° TO +125° C



(9, 15, 25, 37 POSITIONS)

NUMBER OF CONTACTS	"A" Inch (mm)	"B" Inch (mm)	"C" Inch (mm)	"D" Inch (mm)
9	1.214 (30.84)	.984 (24.99)	.432 (10.97)	.109 (2.76)
15	1.545 (39.24)	1.312 (33.32)	.756 (19.20)	.109 (2.76)
25	2.088 (53.04)	1.852 (47.04)	1.304 (33.12)	.109 (2.76)
37	2.730 (69.34)	2.500 (63.50)	1.956 (49.68)	.109 (2.76)



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
PAM JENKINS

CHECKED:

SCALE:

DATE:
9-15-05

DATE:

SHEET
1 OF
1

REV
3

NorComp

DWG NO.
192-YYY-213RYY1