


Glass Passivated Junction Rectifier

Major Ratings and Characteristics

I _{F(AV)}	1.0 A
V _{RRM}	200 V to 800 V
I _{FSM}	50 A
I _R	5.0 μ A
V _F	1.2 V
T _j max.	175 °C



* Glass-plastic encapsulation technique is covered by Patent No. 3,996,602, and brazed-lead assembly by Patent No. 3,930,306

Features

- Superecifier structure for High Reliability application
- Cavity-free glass-passivated junction
- Low forward voltage drop
- Low leakage current
- High forward surge capability
- Meets environmental standard MIL-S-19500
- Solder Dip 260 °C, 40 seconds



Mechanical Data

Case: DO-204AC, molded epoxy over glass body
Epoxy meets UL-94V-0 Flammability rating

Terminals: Matte tin plated leads, solderable per J-STD-002B and JESD22-B102D
E3 suffix for commercial grade, HE3 suffix for high reliability grade (AEC Q101 qualified)

Polarity: Color band denotes cathode end

Typical Applications

For use in general purpose rectification of power supplies, inverters, converters and freewheeling diodes application

Maximum Ratings

(T_A = 25 °C unless otherwise noted)

Parameter	Symbol	1N5059GP	1N5060GP	1N5061GP	1N5062GP	Unit
* Maximum repetitive peak reverse voltage	V _{RRM}	200	400	600	800	V
Maximum RMS voltage	V _{RMS}	140	280	420	560	V
* Maximum DC blocking voltage	V _{DC}	200	400	600	800	V
* Maximum average forward rectified current 0.375" (9.5 mm) lead length at T _A = 75 °C	I _{F(AV)}	1.0				A
* Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	50				A
* Maximum full load reverse current, full cycle average 0.375" (9.5 mm) lead length at T _A = 25 °C	I _{R(AV)}	5.0 150				μ A
Operating junction and storage temperature range	T _J , T _{STG}	- 65 to + 175				°C

1N5059GP thru 1N5062GP



Vishay General Semiconductor

Electrical Characteristics

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Test condition	Symbol	1N5059GP	1N5060GP	1N5061GP	1N5062GP	Unit
* Max. instantaneous forward voltage	at 1.0 A, $T_A = 75^\circ\text{C}$	V_F		1.2			V
* Maximum DC reverse current at rated DC blocking voltage	$T_A = 25^\circ\text{C}$ $T_A = 175^\circ\text{C}$	I_R		5.0	300		μA
Typical reverse recovery time	at $I_F = 0.5\text{ A}$, $I_R = 1.0\text{ A}$, $I_{rr} = 0.25\text{ A}$	t_{rr}		2.0			μs
Typical junction capacitance	at 4.0 V, 1 MHz	C_J		15			pF

Thermal Characteristics

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	1N5059GP	1N5060GP	1N5061GP	1N5062GP	Unit
Typical thermal resistance(1)	$R_{\theta JA}$ $R_{\theta JL}$		45	20		$^\circ\text{C/W}$

Notes:

(1) Thermal resistance from junction to ambient at 0.375" (9.5 mm) lead length, P.C.B. mounted

*JEDEC registered values

Ratings and Characteristics Curves

($T_A = 25^\circ\text{C}$ unless otherwise noted)




Figure 1. Forward Current Derating Curve




Figure 2. Maximum Non-repetitive Peak Forward Surge Current




Figure 3. Typical Instantaneous Forward Characteristics




Figure 5. Typical Junction Capacitance




Figure 4. Typical Reverse Characteristics





Figure 6. Typical Transient Thermal Impedance

Package outline dimensions in inches (millimeters)





Legal Disclaimer Notice

Vishay

Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.