

SK1-11

General Information

Extended Product Type:	SK1-11
Product ID:	1SAM201903R1001
EAN:	4013614320392
Catalog Description:	SK1-11 Signal Contact
Long Description:	SK1-11 Signal contact



Categories

Products » Low Voltage Products and Systems » Control Products » Manual Motor Starters » Manual Motor Starters Accessories

Ordering

Extended Product Type:	SK1-11
Product ID:	1SAM201903R1001
EAN:	4013614320392
Minimum Order Quantity:	2 piece
Customs Tariff Number:	85365080

Container Information

Package Level 1 Width:	15.0 mm
Package Level 1 Length:	80.0 mm
Package Level 1 Height:	93.0 mm
Package Level 1 Gross Weight:	0.080 kg
Package Level 1 Units:	2 piece

Dimensions

Product Net Width:	9.0 mm
Product Net Height:	90.0 mm
Product Net Depth:	78.5 mm
Product Net Weight:	0.035 kg

Technical

Rated Operational Voltage (U_e):	690 V AC 600 V DC
Rated Impulse Withstand Voltage (U_{imp}):	Auxiliary Circuit 6 kV
Rated Insulation Voltage (U_i):	690 V
Connecting Capacity-Auxiliary Circuit:	Rigid 1/2x 1 ... 1.5 mm ² Flexible with Ferrule 1/2x 0.75 ... 1.5 mm ² Flexible with Insulated Ferrule 1/2x 0.75 ... 1.5 mm ² Flexible 1/2x 0.75 ... 1.5 mm ²
Tightening Torques:	Auxiliary Circuit 0.8 ... 1.2 N·m
Wire Stripping Length:	Auxiliary Circuit 8 mm
Recommended Screw Driver:	Pozidriv 2 / M3
Standards:	IEC / EN 60947-1, IEC/EN 60947-5-1
Number of Auxiliary Contacts NO:	1
Product Name:	Signal Contact
Suitable For:	MS116 MS132
Suitable for Product Class:	Manual Motor Starters

Environmental

Ambient Air Temperature: Operation -20 ...+55 °C
Storage -20 ... +70 °C
Storage -50 ... +80 °C

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA

Maximum Operating Voltage UL/CSA: Main Circuit 600 V
Connecting Capacity-Auxiliary Circuit UL/CSA: Stranded 1/2x 16 ... 14 AWG
Auxiliary Circuit Flexible 1/2x 16 ... 14 AWG
Tightening Torques UL/CSA: Auxiliary Circuit 7 in·lb
Contact Rating UL/CSA: B600
Q600

Certificates and Declarations (Document Number)

ABS Certificate: 1SAA963001-0101
BV Certificate: 1SAA963000-0202
CB Certificate: 1SAA963001-2002
CCC Certificate: 1SAA963003-3801
DNV Certificate: 1SAA963001-0302
Declaration of Conformity - CE: 1SAD938512-0060
1SAD938500-0183
1SAD938504-0125
GL Certificate: 1SAA963000-0401
GOST Certificate: 1SAA937000-2703
LR Certificate: 1SAA963000-0503
1SAA963001-0501
RINA Certificate: 1SAA963000-0801
RoHS Information: 1SAA963001-4405
UL Certificate: 1SAA918000-1606
cUL Certificate: 1SAA918000-1703

Classifications

E-nummer: E3112011
Object Classification Code: Q