





LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			J5	REVISED PER ECR-12-013486	06JAN13	KH	KR



- 1 MATL: #2 HARD BRASS OR NICKEL PLATE STEEL.
- 2 NO BURRS PERMISSIBLE AT HOLE.
- 3 TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL
TEMPERATURE IS OVER 225° F.
- 4  MUST BE FLAT WITHIN 0.076 [0.003] OVER THIS LENGTH.
- 5 HOLE MUST BE SYMMETRICAL ABOUT TAB  WITHIN 0.076 [0.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



GOLD / NICKEL 	BRASS	 63196-5
---	BRASS	63196-4
GOLD / NICKEL 	BRASS	 63196-3
PRE-TIN	BRASS	63196-2
TIN	BRASS	63196-1
FINISH	MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 2/28/87 CHK G YETTER 3/9/87 APVD R KUZO 3/9/87 PRODUCT SPEC — APPLICATION SPEC —		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.25 .010 4 PLC ± — ANGLES ± —		RECEPTACLE, POSITIVE LOCK, .187 SERIES —	
MATERIAL		FINISH		SIZE	RESTRICTED TO
SEE TABLE		SEE TABLE		CAGE CODE A2 00779	DRAWING NO C-63196
		WEIGHT —		—	
CUSTOMER DRAWING				SCALE 5:1	SHEET 1 of 1
				REV	.15