





THIS DRAWING IS UNPUBLISHED
RELEASED FOR PUBLICATION
2015
COPYRIGHT 1999 BY TE CONNECTIVITY
ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	REVISED PER E.O. PI7000	08DEC2000	SP	RDR
			D	REVISED PER E.O. PI9555	11JUL2007	JA	RDR
			E	REVISED PER E.O. P20396	25JUN2010	JA	RDR
			F	REVISED PER ECO-15-007761	28MAY2015	RL	DM



TE INTERNAL PN	DEUTSCH PN	PLATING
1060-14-0122	1060-14-0122	NICKEL
1060-14-0144	1060-14-0144	SELECTIVE GOLD
1060-14-0177	1060-14-0177	TIN

- 3 MATERIAL: .012 [0.30] THICK COPPER ALLOY
2. WIRE RANGE: 18 AWG TO 14 AWG [0.75-2.0 mm²]
INSULATION RANGE: Ø.095-.150 [Ø2.41-3.81]
- 1 APPLIED ONLY TO SELECTIVE GOLD 1060-14-0144.
INDICATED DIMENSION SHOWS GOLD PLATED AREA.

NOTES: UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 04NOV1999 MICHAEL BLOOM	TE Connectivity		
DIMENSIONS: INCHES[mm]		CHK 04DEC2000 VLADIMIR TOMSA			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 08DEC2000 ROBIN REED	NAME STAMPED CONTACT PIN SIZE 16		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [0.64] 4 PLC ± ANGLES ±		PRODUCT SPEC 0425-015-0000	SIZE A3		
MATERIAL 3		APPLICATION SPEC 114-151000	CAGE CODE 4AFU8		
FINISH SEE TABLE		WEIGHT 0.34 g	DRAWING NO C-1060-14-01XX		
		Customer Drawing	RESTRICTED TO -		
			SCALE 6:1		
			SHEET 1		
			OF 1		
			REV F		