






SCALE 1:1

- △ MATERIAL:
HARNESS - 35% GLASS FILLED PA66, BLACK
ALT MAT'L - 30% GLASS FILLED sPS, BLACK
- SPACER - 40% GLASS FILLED PPS, RED
ALT MAT'L - 30% GLASS FILLED sPS, RED
- COVER - 35% GLASS FILLED PA66, BLACK
ALT MAT'L - 30% GLASS FILLED LCP, BLACK
- CAM LEVER - 35% GLASS FILLED NYLON, GRAY
GROMMET - SILICONE, BROWN
PERIMETER SEAL - SILICONE, GREEN
2. CAM LEVER AND SPACER ARE SHIPPED IN PRE-LATCH POSITION.
3. SEE PINOUT CHART FOR CLOSED CIRCUIT CONFIGURATIONS.
4. CAVITIES WITH A NUMERIC SYMBOL INDICATES CLOSED TERMINAL LOCATIONS.
BLANK CAVITIES INDICATE OPEN TERMINAL HOLE LOCATIONS.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
H6		REVISED PER ECO-11-018497	09SEP2011	DLD	DCM
H7		REVISED PER ECO-14-015177	15OCT2014	DLD	DCM
H8		REVISED PER ECO-15-011500	07AUG2015	DLD	DCM
H9		REVISED PER ECO-18-005723	16APR2018	JMS	CM




CHART FOR CLOSED CIRCUIT CONFIGURATIONS SHEET 2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL	15OCT2003	TE Connectivity	
		CHK D. STRAUSSER	15OCT2003		
DIMENSIONS:		APVD D. STRAUSSER	15OCT2003	NAME	
mm		PRODUCT SPEC		PCM	
		APPLICATION SPEC		HARNESS ASSEMBLY, 30-WAY CONNECTOR	
		WEIGHT		RESTRICTED TO	
MATERIAL		CUSTOMER DRAWING		A100779C=1438083	
				SCALE 3:1 SHEET 1 OF 2 REV H9	

PIN-OUT CHART KEYING OPTION "B" PIN-OUT CHART KEYING OPTION "A" 4805 (3/13)