



SAW Components

Data Sheet B4143

Data Sheet

An abstract, grayscale graphic featuring a globe with a grid pattern, overlaid with a large, stylized, and slightly blurred "EPCOS" logo. The logo is rendered in a light gray, almost white, color, giving it a three-dimensional appearance as if it's floating or attached to the globe. The background is dark and textured with swirling patterns.

EPCOS



SAW Components

B4143

Low-Loss Filter for Mobile Communication

1880,0 MHz

Data Sheet




Ceramic package DCC6C

Features

- Low-loss RF filter for mobile telephone PCS systems, transmit path
- Usable passband 60 MHz
- No matching network required for operation at 50 Ω
- Ceramic Package for Surface Mounted Technology (SMT)

Terminals


- Ni, gold-plated



Dimensions in mm, approx. weight 0,037 g

Pin configuration

2	Input
3	Input - ground
5	Output
4	Output - ground
1,6	To be grounded



Type	Ordering code	Marking and Package according to	Packing according to
B4143	B39192-B4143-U410	C61157-A7-A67	F61074-V8088-Z000

Electrostatic Sensitive Device (ESD)

Maximum ratings

Operable temperature range	T	- 30 /+ 85	$^{\circ}\text{C}$	source and load impedance 50 Ω peak power of TDMA signal, duty cycle 1 : 3 continuous wave
Storage temperature range	T_{stg}	- 40 /+ 85	$^{\circ}\text{C}$	
DC voltage	V_{DC}	0	V	
Input power max. 1850...1910 MHz	P_{IN}	13	dBm	
		10	dBm	



SAW Components

B4143

Low-Loss Filter for Mobile Communication

1880,0 MHz

Data Sheet



Characteristics

Operating temperature range: $T = 25 \pm 2^\circ \text{C}$
Terminating source impedance: $Z_S = 50 \Omega$
Terminating load impedance: $Z_L = 50 \Omega$

			min.	typ.	max.	
Center frequency	f_c		—	1880,0	—	MHz
Maximum insertion attenuation	$\alpha_{\max}$					
	1850,0 ... 1910,0 MHz		—	3,2	4,0	dB
Amplitude ripple (p-p)	$\Delta\alpha$					
	1850,0 ... 1910,0 MHz		—	1,7	2,5	dB
Input VSWR						
	1850,0 ... 1910,0 MHz		—	2,0	2,2	
Output VSWR						
	1850,0 ... 1910,0 MHz		—	2,0	2,2	
Attenuation	α					
	10,0 ... 1570,0 MHz		23,0	26,0	—	dB
	1570,0 ... 1720,0 MHz		33,0	35,0	—	dB
	1930,0 ... 1935,0 MHz		15,0	24,0	—	dB
	1935,0 ... 1990,0 MHz		20,0	27,0	—	dB
	2032,0 ... 2125,0 MHz		35,0	36,5	—	dB
	2125,0 ... 2340,0 MHz		35,0	37,0	—	dB
	2340,0 ... 3000,0 MHz		30,0	39,0	—	dB
	3000,0 ... 3500,0 MHz		15,0	24,0	—	dB



SAW Components

B4143

Low-Loss Filter for Mobile Communication

1880,0 MHz

Data Sheet



Characteristics

Operating temperature range: $T = -10$ to $+70$ °C
Terminating source impedance: $Z_S = 50 \Omega$
Terminating load impedance: $Z_L = 50 \Omega$

			min.	typ.	max.	
Center frequency	f_c		—	1880,0	—	MHz
Maximum insertion attenuation	$\alpha_{\max}$					
	1850,0 ...1910,0 MHz		—	3,5	4,6	dB
Amplitude ripple (p-p)	$\Delta\alpha$					
	1850,0 ...1910,0 MHz		—	2,0	3,1	dB
Input VSWR						
	1850,0 ...1910,0 MHz		—	2,0	2,2	
Output VSWR						
	1850,0 ...1910,0 MHz		—	2,0	2,2	
Attenuation	α					
	10,0 ...1448,0 MHz		23,0	26,0	—	dB
	1448,0 ...1570,0 MHz		30,0	32,0	—	dB
	1570,0 ...1720,0 MHz		33,0	35,0	—	dB
	1930,0 ...1935,0 MHz		14,5	22,0	—	dB
	1935,0 ...1990,0 MHz		20,0	25,0	—	dB
	2032,0 ...2125,0 MHz		35,0	36,5	—	dB
	2125,0 ...2340,0 MHz		35,0	37,0	—	dB
	2340,0 ...3000,0 MHz		30,0	39,0	—	dB
	3000,0 ...3500,0 MHz		15,0	24,0	—	dB



SAW Components

B4143

Low-Loss Filter for Mobile Communication

1880,0 MHz

Data Sheet



Characteristics

Operating temperature range: $T = -30$ to $+85\text{ }^{\circ}\text{C}$
Terminating source impedance: $Z_S = 50\text{ }\Omega$
Terminating load impedance: $Z_L = 50\text{ }\Omega$

			min.	typ.	max.	
Center frequency	f_c		—	1880,0	—	MHz
Maximum insertion attenuation	$\alpha_{\max}$					
	1850,0 ...1910,0 MHz		—	3,5	5,0	dB
Amplitude ripple (p-p)	$\Delta\alpha$					
	1850,0 ...1910,0 MHz		—	2,0	3,5	dB
Input VSWR						
	1850,0 ...1910,0 MHz		—	2,0	2,2	
Output VSWR						
	1850,0 ...1910,0 MHz		—	2,0	2,2	
Attenuation	α					
	10,0 ...1570,0 MHz		23,0	26,0	—	dB
	1570,0 ...1720,0 MHz		33,0	35,0	—	dB
	1930,0 ...1935,0 MHz		13,0	22,0	—	dB
	1935,0 ...1990,0 MHz		20,0	25,0	—	dB
	2032,0 ...2125,0 MHz		35,0	36,5	—	dB
	2125,0 ...2340,0 MHz		35,0	37,0	—	dB
	2340,0 ...3000,0 MHz		30,0	39,0	—	dB
	3000,0 ...3500,0 MHz		15,0	24,0	—	dB



SAW Components

B4143


Low-Loss Filter for Mobile Communication

1880,0 MHz


Data Sheet



Transfer function (25°C spec)



Transfer function (wideband)





SAW Components

B4143



Low-Loss Filter for Mobile Communication

1880,0 MHz

Data Sheet



Reflection function





SAW Components	B4143
Low-Loss Filter for Mobile Communication	1880,0 MHz
Data Sheet	SMD

Published by EPCOS AG
Surface Acoustic Wave Components Division, OFW E MF
P.O. Box 80 17 09, D-81617 München

© EPCOS AG 1999. All Rights Reserved.

As far as patents or other rights of third parties are concerned, liability is only assumed for components per se, not for applications, processes and circuits implemented within components or assemblies.

The information describes the type of component and shall not be considered as assured characteristics.

Terms of delivery and rights to change design reserved.

For questions on technology, prices and delivery please contact the sales offices of EPCOS AG or the international representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our sales offices.