



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO LAIRD TECHNOLOGIES.
IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN LAIRD TECHNOLOGIES
PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM LAIRD TECHNOLOGIES.



* NOTE:
FOR SINGLE FINGER PARTS
TAKE 77-15 FROM STOCK.



② NOT TO SCALE: RECOMMENDED MOUNTING HOLE PATTERN
R.020 MAX/TYP

DWG. NO.
0077-0011

MATERIAL:	.005±.0002 X 1.031±.003	
	BeCu ALLOY 25 1/4 HARD	
HEAT TREATED:	TO DPH 373 MINIMUM	
	USING A 500 GRAM LOAD	
THICKNESS AFTER:	CLEANING AND	
	BEFORE PLATING: .0046 MIN.	
FINISH:	AS REQUIRED	
	CAD MAINTAINED DRAWING. MANUAL CHANGES UNAUTHORIZED.	

TOLERANCES NOT SHOWN	
DECIMAL 2 PL'S	± .020
DECIMAL 3 PL'S	± .005
ANGULAR	± ---
THIRD ANGLE PROJECTION	
UNITS:	INCH [MM]
SCALE:	2:1

	DRAWN BY:	DATE:
	RCC	08/22/90
DELAWARE WATER GAP PENNSYLVANIA	CHECKED BY:	DATE:
	ES	08/23/90
LAIRD STANDARD	APPROVED BY:	DATE:
	ES	08/23/90
REF. DWG NO. SLOT MOUNT GASKET		
DWG. NO.	0077-0011	② SUB 09

DWG. NO.	0077-0011
ECN-5532 ADD STOCK IN 25 FT. COILS. ADD MOUNTING DIMS. P.N. WAS 0097-B-0927 RCC 9-27-90 ES 9-27-90	02
ECN-5948 DWG NO. WAS 9097-B-11 RCC 3-20-91 EWS 3-22-91	03
ECN-6542 ADD TO QP#1-250 FT. COILS. EWS 12-2-91	04
ECN-6774 ADDED A NOTE .282 ±.0005 PITCH WAS .282±.001 PITCH MN 5-6-92 EWS 5-6-92	05
ECD-E156 MATERIAL WIDTH CHNGE 1.031 WAS 1.125 DCS 4-13-98 EWS 4-13-98	06
ECD-E1666 26.58 #/K WAS 29.02 RKM 5-15-00 EWS 5-15-00	07
ECD-E2038 ADDED +8°/-2° TOL. TO LEG FORM. RKM 12-7-00 EWS 12-7-00	08
ECD-E2985 CHANGED DIM SCHEME OF MOUNTING HOLE PATTERN SDH 05/31/02 EWS 05/31/02	09