


## • HXO-S Series 3.2X2.5X1.2 mm



The HXO-S series is an ultra miniature package clock oscillator with size of 3.2X2.5X1.2mm. It is mainly used in portable PC and telecommunication devices and equipment.

### FEATURES


- 3.2X2.5X1.2 Miniature Package
- Tri-State Enable/Disable
- TTL/HCMOS compatible
- Tape and Reel
- IR Re-flow
- 5.0V,3.3V,2.8V and 1.8V option

### Electrical Specifications

| Parameter                   |                  | Condition                              | HXO-SF                                    | HXO-SC     | HXO-SD     | HXO-SE     |
|-----------------------------|------------------|----------------------------------------|-------------------------------------------|------------|------------|------------|
| Frequency Range             | F <sub>O</sub>   |                                        | 1MHz~54MHz                                |            |            |            |
| Frequency Stability*        |                  | All Condition*                         | ± 25ppm, ± 50ppm, ± 100ppm                |            |            |            |
| Operating Temperature Range | T <sub>OPR</sub> |                                        | -20℃~+70℃ (-40℃~+85℃ option)              |            |            |            |
| Storage Temperature Range   | T <sub>STG</sub> |                                        | -55℃~+125℃                                |            |            |            |
| Power supply Voltage        | V <sub>DD</sub>  |                                        | 5.0V+/-10%                                | 3.3V+/-10% | 2.8V+/-10% | 1.8V+/-10% |
| Supply Current              | I <sub>DD</sub>  | 1MHz to 9.999MHz                       | 15mA Max                                  | 8mA Max    | 7mA Max    | 6mA Max    |
|                             |                  | 10MHz to 34.999MHz                     | 20mA Max                                  | 10mA Max   | 8mA Max    | 7mA Max    |
|                             |                  | 35MHz to 49.999MHz                     | 35mA Max                                  | 25mA Max   | 20mA Max   | 15mA Max   |
|                             |                  | 50MHz to 54.000MHz                     | 40mA Max                                  | 35mA Max   | 30mA Max   | 25mA Max   |
| Output Symmetry             | Sym              | At 1/2V <sub>DD</sub>                  | 40/60%(45/55% Option)                     |            |            |            |
| Rise time                   | T <sub>r</sub>   | 10%V <sub>DD</sub> ~90%V <sub>DD</sub> | 5 nS Max                                  | 5 nS Max   | 6 nS Max   | 7 nS Max   |
| Fall Time                   | T <sub>f</sub>   | 90%V <sub>DD</sub> ~10%V <sub>DD</sub> | 5 nS Max                                  | 5 nS Max   | 6 nS Max   | 7 nS Max   |
| Output Voltage              | V <sub>OH</sub>  |                                        | 90% V <sub>DD</sub> Min                   |            |            |            |
|                             | V <sub>OL</sub>  |                                        | 10% V <sub>DD</sub> Max                   |            |            |            |
| Output Load                 | HCMOS Load       |                                        | 15pF Typ.                                 |            |            |            |
| Start Time                  | T <sub>s</sub>   |                                        | 10mS Max                                  |            |            |            |
| Stand-by Function           |                  |                                        | Yes                                       |            |            |            |
| Aging(First Year)           |                  | 25℃±3℃                                 | ±2ppm Max                                 |            |            |            |
| Pin 1,tri-state function    |                  |                                        | Pin 1=H or open....Output active at pin 3 |            |            |            |
|                             |                  |                                        | Pin 1=L.....high impedance at pin 3       |            |            |            |
| Packing Unit                |                  | 3000pcs/reel                           |                                           |            |            |            |

\*Include: 25°C tolerance, operating temperature range, input voltage change, aging, load change, shock and vibration

### Mechanical Dimensions(mm)



\*\*Note: A 0.01uF bypass capacitor should be placed between V<sub>DD</sub>(Pin4) and GND(Pin2) to Minimize power supply line noise

#### TAIWAN:

HOSONIC ELECTRONIC CO., LTD.  
23-1 LANE 84. CHUN YING ST. SHULIN CHEN.  
TAIPEI 23804. TAIWAN  
WEB SITE:<http://www.hosonic.com>

☎: 886-2-86875200  
☎: 886-2-26816456  
✉: sharon@hosonic.com.tw

#### CHINA:

HANGZHOU HOSONIC ELECTRONIC CO., LTD.  
NO.242 LIANGBO ROAD. LIANGZHU TOWN.  
YUHANG DISTRICT, HANGZHOU, ZHEJIANG, CHINA  
WEB SITE:<http://www.hosonic.com.cn>

☎: 86-571-88778189  
☎: 86-571-88778857  
✉: mike@hosonic.com

Specifications are subject to change without notice