







PROMINENT COLORED FRONT LABEL,
ATTENUATION IN BLACK LETTERS

1. Mates to SFP components which comply to standard MSA dimension specifications.
2. Support for: Data rates to 10 Gbps
3. Robust zinc die cast body, bright nickel plated. Mounts belly-to-belly using 0.093"+ boards.
4. Raised wedges assure electrical contact with surrounding EMI cage assembly.
5. Spring loaded latch releases with simple squeeze, and pull action.
6. 100 ohm impedance.
7. Supports serial ID functionality.
8. 3.3V supply.
9. Hot pluggable.

PART NUMBER	LABEL COLOR	PART DESCRIPTION
747650904	TAN	SERIAL ID, WITH 5.0 dB ATTENUATION
747650906	LIGHT BLUE	SERIAL ID, WITH 0.0 dB ATTENUATION


ENTER DESCRIPTION EC NO: USY2009-0124 DRWN: JERWIN 2008/09/25 CHKD: BRUSSELL 2008/10/07 APPR: BRUSSELL 2008/10/08	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY JERWIN	DATE 2007/11/07	SFP+ 10G LOOPBACK ADAPTER				
		4 PLACES	± ---	± ---	CHECKED BY BRUSSELL	DATE 2007/11/07					
		3 PLACES	± ---	± .005	APPROVED BY BRUSSELL	DATE 2007/11/07					
		2 PLACES	± 0.13	± ---	MATERIAL NO. SEE CHART	DOCUMENT NO. SD-74765-0904					
		1 PLACE	± ---	± ---	MOLEX INCORPORATED						
		ANGULAR ±1/2°									
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									




△ ATTENUATION LEVEL FOR 74765-0904 SHOWN AS EXAMPLE.

ENTER DESCRIPTION EC NO: USY2009-0124 DRWN: JERWIN 2008/09/25 CH'KD: BRUSSELL 2008/10/07 APPR: BRUSSELL 2008/10/08			DESCRIPTION	REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
							mm	INCH	DRAWN BY	DATE	TITLE SFP+ 10G LOOPBACK ADAPTER					
						4 PLACES	± ---	± ---	JERWIN	2007/11/07						
						3 PLACES	± ---	± .005	CHECKED BY	DATE	MOLEX INCORPORATED					
						2 PLACES	± 0.13	± ---	BRUSSELL	2007/11/07						
						1 PLACE	± ---	± ---	APPROVED BY	DATE	SD-74765-0904					
						ANGULAR ±1/2°			BRUSSELL	2007/11/07						
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		DOCUMENT NO.				SHEET NO.	
									SEE CHART		SD-74765-0904				2 OF 3	
									SIZE A	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

Top View
Cutaway



Bottom
View



Gnd T	20	1	Gnd T
TD-	19	2	Tx Fault
TD+	18	3	Tx Disable
Gnd T	17	4	MOD-DEF(2)
VccT	16	5	MOD-DEF(1)
VccR	15	6	MOD-DEF(0)
Gnd R	14	7	Rate Select
RD+	13	8	LOS
RD-	12	9	Gnd R
Gnd R	11	10	Gnd R

ENTER DESCRIPTION EC NO: USY2009-0124 DRWN: JERWIN 2008/09/25 CHKD: BRUSSELL 2008/10/07 APPR: BRUSSELL 2008/10/08		DESCRIPTION	QUALITY SYMBOLS ▽=0 ◻=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
					mm	INCH	DRAWN BY JERWIN	DATE 2007/11/07	TITLE SFP+ 10G LOOPBACK ADAPTER				
				4 PLACES	± ---	± ---	CHECKED BY BRUSSELL	DATE 2007/11/07					
				3 PLACES	± ---	± .005	APPROVED BY BRUSSELL	DATE 2007/11/07	MOLEX MOLEX INCORPORATED				
2 PLACES	± 0.13	± ---	MATERIAL NO. SEE CHART		DOCUMENT NO. SD-74765-0904		SHEET NO. 3 OF 3						
1 PLACE	± ---	± ---	ANGULAR ±1/2°										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													
REV			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										