



LOCK TANG BEAM
(2-PL)
(SEE NOTE 7)

.005 MAX CUT-OFF
0.14 TAB



.723 ± .006
18.35 ± 0.15

.165 ± .005
4.19 ± 0.13




TPA LOCK TABS

NOTES:

1. MATERIAL: .012/(0.30) THICK HSM COPPER.
2. FINISH: SELECT SILVER (.000100/0.00254 MIN) & SELECT MATTE TIN (.000100/0.00254 MIN) OVER NICKEL OVERALL.
3. PRODUCT SPECIFICATION: PS-171825-001.
4. PACKAGING: PK-171825-001 (PENDING).
5. MATES WITH: 171826 MALE CRIMP TMLS, 172042 AND 172043 HDRS. FOR USE IN 172672/44441 RCPT HSGS.
6. SINGLE CRIMP TO UL1015, 10 OR 12AWG STRANDED COPPER WIRE, OR SINGLE CRIMP TO 4MM² CU-R4TPE 19x0.53mm STRANDED COPPER WIRE OR 5MM² CU-H1PVC 65X0.32mm STRANDED COPPER WIRE. TINNED WIRE RECOMMENDED.
7. NO PORTION OF ONE LOCK TANG BEAM SHALL TOUCH ANY PORTION OF THE OTHER LOCK TANG BEAM.

REF.
.520
13.21
PROGRESSION



NOTE 6 UPDATED EC NO: UCP2016-1350 DRWN:SNAGARAVENKA 2017/07/20 CHKD:JDOX 2017/07/20 APPR:FSMITH 2017/08/01	REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 10:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	
						DRAWN BY GES		DATE 2013/04/02	TITLE SUPER-SABRE FEMALE CRIMP TERMINAL			
						CHECKED BY BANDERSON		DATE 2013/04/02				
						APPROVED BY FSMITH		DATE 2013/10/09				
						MATERIAL NO. 1718250100		DOCUMENT NO. SD-171825-001				SHEET NO. 1 OF 1
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
				mm		INCH						
				4 PLACES ± --- ± ---								
				3 PLACES ± --- ± .010								
				2 PLACES ± 0.25 ± .014								
1 PLACE ± 0.35 ± ---												
0 PLACE ± --- ± ---												
		ANGULAR ±1/2°										