


3.0A Standard Rectifier

Features

- Low Forward Voltage Drop
- High Current Capability
- High Surge Current Capability
- High Reliability
- High Temperature Soldering Guaranteed 260°C/10 seconds
/.375" (9.5mm) lead length, 5lbs (2.3kg) tension
- RoHS compliant



DO-201AD



Mechanical Data

Case:	Molded Plastic
Epoxy:	Meets UL 94V-0 flammability rating
Terminals:	Axial leads, solderable per MIL-STD-202, Method 208
Polarity:	Cathode indicated by color band
Weight:	0.042 Ounce, 1.2 gram

Maximum Ratings ($T_{Ambient}=25^{\circ}\text{C}$ unless noted otherwise)

Symbol	Description	1N5400	1N5401	1N5402	1N5403	1N5404	1N5405	1N5406	1N5407	1N5408	Unit
V_{RRM}	Maximum Repetitive Peak Reverse Voltage	50	100	200	300	400	400	600	800	1000	V
V_{RMS}	Maximum RMS Voltage	35	70	140	210	280	280	420	560	700	V
V_{DC}	Maximum DC Blocking Voltage	50	100	200	300	400	400	600	800	1000	V
I_{O(AV)}	Maximum Average Forward Rectified Current @Ta=75° C	3.0									A
I_{FSM}	Peak Forward Surge Current (Note1)	200									A
T_J	Operating Junction Temperature Range	-55 to +125									° C
T_{STG}	Storage Temperature Range	-55 to +150									° C

3.0A Standard Rectifier

1N5400 - 1N5408

Electrical Characteristics ($T_{Ambient}=25^{\circ}\text{C}$ unless noted otherwise)

Symbol	Description	1N5400	1N5401	1N5402	1N5403	1N5404	1N5405	1N5406	1N5407	1N5408	Unit
V_F	Maximum Forward Voltage @ $I_F=3.0\text{A}$	1.0									V
I_R	Maximum DC Reverse Current at Rated DC Blocking Voltage	$T_A=25^{\circ}\text{C}$ 5.0									μA
		$T_A=100^{\circ}\text{C}$ 50									μA
C_J	Typical Junction Capacitance (Note2)	30									pf
$R_{\theta-JA}$	Maximum Thermal Resistance (Note3)	20									$^{\circ}\text{C/W}$

- Note:**
1. 8.3ms single half sine-wave superimposed on rated load (JEDEC method)
 2. Measured at 1MHz and applied reverse voltage of 4.0Volts D.C.
 3. Thermal resistance from junction to ambient at .375" (9.5mm) lead length.

Typical Characteristics Curves

Fig.1- Forward Current Derating Curve





Fig.2-Max. Non-Repetitive Forward Surge Current



3.0A Standard Rectifier

1N5400 - 1N5408

Fig.3-Typical Instantaneous Forward Characteristics




Fig.4- Typical Reverse Characteristics






Fig.5-Typical junction capacitance



3.0A Standard Rectifier

1N5400 - 1N5408

Dimensions in inches (mm)



3.0A Standard Rectifier

1N5400 - 1N5408

How to contact us:

US HEADQUARTERS

28040 WEST HARRISON PARKWAY, VALENCIA, CA 91355-4162

Tel: (800) TAITRON (800) 824-8766 (661) 257-6060

Fax: (800) TAITFAX (800) 824-8329 (661) 257-6415

Email: taitron@taitroncomponents.com

Http://www.taitroncomponents.com

TAITRON COMPONENTS MEXICO, S.A .DE C.V.

BOULEVARD CENTRAL 5000 INTERIOR 5 PARQUE INDUSTRIAL ATITALAQUIA, HIDALGO C.P.

42970 MEXICO

Tel: +52-55-5560-1519

Fax: +52-55-5560-2190

TAITRON COMPONETS INCORPORATED E REPRESENTAÇÕES DO BRASIL LTDA

RUA DOMINGOS DE MORAIS, 2777, 2.ANDAR, SALA 24 SAÚDE - SÃO PAULO-SP 04035-001 BRAZIL

Tel: +55-11-5574-7949

Fax: +55-11-5572-0052

TAITRON COMPONETS INCORPORATED, SHANGHAI REPRESENTATIVE OFFICE

CROSS REGION PLAZA, 899 LINGLING ROAD, SUITE 18C, SHANGHAI, 200030, CHINA

Tel: +86-21-5424-9942

Fax: +86-21-5424-9931