




LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
AD	39				H	REV PER 0010-1175-95	12-30-96	JH
					J	REV PER 063C-0062-00	11FEB00	MZ



- 1

POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS).
- 2

SHEAR LINES DEFINE LOOSE PIECE PART.
- 3


"H" RECEPTACLE CENTERS MAY VARY DEPENDING ON REQUIREMENTS. MINIMUM NOMINAL CENTER SPACING BETWEEN ADJACENT RECEPTACLES IS 3.81±0.08[.150±.003].
- 4

GOLD FLASH OVER 0.00127[.000050] NICKEL ENTIRE TERMINAL, 0.00076[.000030] GOLD ON CONTACT AREA ONLY.
- 5


0.00200 [.000079] MIN TIN.
- 6

0.00038[.000015] GOLD ON CONTACT AREA, 0.00254-0.00508[.000100-.000200] BRIGHT TIN-LEAD ON TERMINATION AREA, ALL OVER 0.00127[.000050] NICKEL ENTIRE TERMINAL.
- 7

0.00076[.000030] GOLD ON CONTACT AREA, 0.00254-0.00508[.000100-.000200] BRIGHT TIN-LEAD ON TERMINATION AREA, ALL OVER 0.00127[.000050] NICKEL ENTIRE TERMINAL.





SECTION A-A



SECTION B-B

OBSOLETE	MINATURE	87105-4	7	87003-6
	-	-	-	-
OBSOLETE	MINATURE	87105-3	6	87003-4
	-	-	-	-
	MINATURE	87105-2	5	87003-2
	MINATURE	87105-1	4	87003-1
	REELED FOR APPLICATOR	LOOSE PIECE PART NO	FINISH	PART NUMBER



TYPICAL APPLICATION

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

				PART NO		
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± 0.13[.005] ANGLES ± -	DR 7-18-94 E.BRANDBERG		AMP AMP Incorporated Harrisburg, PA 17105-3608			
	CHK 7-18-94 J. HERRINGTON					
	APPD 7-18-94 J. HERRINGTON					
MATERIAL PHOS BRONZE	APPD 7-18-94 D. DUPLER		NAME RECEPTACLE, MOD I, STANDARD PRESSURE, TYPE B			
	PRODUCT SPEC -					
FINISH - SEE TABLE	APPLICATION SPEC -		SIZE C	CAGE CODE 00779	DRAWING NO C=87003	
	WEIGHT -		SCALE 8:1		SHEET 1 OF 1	