

Primary Power Receptacles

UL and CSA Approved, International Standard CCE-22

Shell: Black glass reinforced thermoplastic polyester. UL flammability rating 94 V-O, yellow card #E45575. Pins: Silver-plated brass. Terminals: Electrotinned brass except EAC-333, silver-plated brass.

EAC-333. 3-pin male receptacle with right angle housing for PC board mount. Rear of panel mounting. PC terminals project 0.125" to extend through PC board. Ground pin is integral with the ground solder lug on rear of receptacle. Two additional 0.136" holes for fastening to panel or chassis. **EAC-309.** 3-pin male receptacle with standard lug terminals. Mounts from front or rear of panel with two #5 screws or 0.125" rivets (not supplied). **EAC-311.** 3-pin male receptacle with FASTON terminals. Mounts from front or rear of panel with two #4 screws or 0.094" rivets (not supplied). **EAC-305.** 3-contact female receptacle front mount with two #4 screws or 0.094" rivets (not supplied). **EAC-405.** 3-contact female receptacle with standard solder lug terminals. Snap-in panel mounting. **EAC-409.** 3-pin male receptacle with standard solder lug terminals. Snap-in panel mounting. **EAC-411.** 3-pin male receptacle with FASTON terminals. Snap-in panel mounting.

| Stock No. | Mr.'s Type | Rating | Mating Power Cord | EACH | |
|-----------|-------------|---------------|--------------------|------|-------|
| | | | | 1-9 | 10-24 |
| 932-0093 | EAC-333 | 10 A, 250 VAC | 523, 535, 545, 537 | 2.09 | 1.79 |
| 932-0099 | EAC-309 | 10 A, 250 VAC | 523, 535, 545, 537 | 1.42 | 1.20 |
| 932-0101 | EAC-311 | 10 A, 250 VAC | 545, 537 | 1.41 | 1.20 |
| 932-0097 | EAC-305 | 10 A, 250 VAC | 551, 552 | 1.95 | 1.67 |
| 932-0108 | EAC-405040* | 10 A, 250 VAC | 551, 552 | 2.44 | 2.11 |
| 932-0110 | EAC-409040* | 10 A, 250 VAC | 523, 535, 545, 537 | 2.09 | 1.78 |
| 932-0112 | EAC-411040* | 10 A, 250 VAC | 545, 537 | 3.03 | 2.59 |

*Panel mounts are for .040 panel thickness. Snap-in for other panel thickness also available.



EAC-333



EAC-309



EAC-311



EAC-305



EAC-409



EAC-411

8


DIN Plugs and Sockets



With 30° Locking Ring



Extended Barrel



Shielded Barrel

DIN is the name given to this high-quality family of versatile miniature audio connectors. Features include solder lug or PC terminations, as well as bright nickel-plated or colorful plastic snap-on shells. Designed for audio circuitry, they are also ideal for test equipment, computers and other types of low level circuits. Precision manufactured. The parts listed are a small representation of a large and growing family. Call the closest sales office for parts not shown.

Right Angle Receptacles for PC Mounting Shielded

| Stock No. | Mr.'s Type | Description | EACH | |
|-----------|------------|--|------|-------|
| | | | 1-9 | 10-24 |
| 932-0183 | 57PC5FS | Mates with 3 or 5 pins, 5 contacts at 180° | 2.17 | 1.74 |
| 932-0198 | 62PC8FS | Mates with 8 pins, 8 contacts at 270° | 3.16 | 2.75 |

Unshielded

| | | | | |
|----------|--------|--|------|------|
| 932-0200 | 57PC5F | Mates with 3 or 5 pins, 5 contacts at 180° | 2.10 | 1.58 |
| 932-0201 | 61PC5F | Mates with 5 pins, 5 contacts at 240° | 2.09 | 1.78 |
| 932-0202 | 62PC8F | Mates with 8 pins, 8 contacts at 270° | 3.09 | 2.68 |

Straight Cord Plugs


| | | | | |
|----------|--------|---------------------------------------|------|------|
| 932-0153 | 05CL3M | With 30° locking ring, 3 pins at 180° | 5.63 | 4.38 |
| 932-0154 | 05CL5M | With 30° locking ring, 5 pins at 180° | 5.80 | 5.22 |
| 932-0166 | 12CL5M | With 30° locking ring, 5 pins at 240° | 5.45 | 4.81 |
| 932-0156 | 05GM3M | Shielded barrel, 3 pins at 180° | 3.15 | 2.74 |
| 932-0157 | 05GM5M | Shielded barrel, 5 pins at 180° | 3.36 | 2.91 |
| 932-0165 | 12GM5M | Shielded barrel, 5 pins at 240° | 3.86 | 3.34 |
| 932-0167 | 12GM6M | Shielded barrel, 6 pins at 240° | 4.08 | 3.53 |
| 932-0168 | 15GM7M | Shielded barrel, 7 pins at 270° | 4.27 | 3.71 |
| 932-0178 | 15GM8M | Shielded barrel, 8 pins at 270° | 4.50 | 3.90 |
| 932-0162 | 05BL3M | Extended barrel, 3 pins at 180° | 2.72 | 2.36 |
| 932-0155 | 05BL5M | Extended barrel, 5 pins at 180° | 4.21 | 3.64 |
| 932-0164 | 12BL5M | Extended barrel, 5 pins at 240° | 4.08 | 3.53 |
| 932-0163 | 12BL6M | Extended barrel, 6 pins at 240° | 4.24 | 3.68 |
| 932-0169 | 15BL8M | Extended barrel, 8 pins at 270° | 3.96 | 3.42 |

Straight Receptacles

| | | | | |
|----------|---------|--|------|------|
| 932-8860 | 57HB3F | For locking ring plugs, 3 contacts at 180° | 2.01 | 1.75 |
| 932-0185 | 57HA5F | For locking ring plugs, 5 contacts at 180° | 2.53 | 2.19 |
| 932-0186 | 57HB5F* | For locking ring plugs, 5 contacts at 180° | 2.86 | 2.47 |
| 932-0188 | 61HA5F | For locking ring plugs, 5 contacts at 240° | 2.85 | 2.46 |
| 932-0187 | 57CB3F | For shielded and extended barrel plugs, 3 contacts at 180° | 1.85 | 1.47 |
| 932-0181 | 57CB8F | For shielded and extended barrel plugs, 5 contacts at 180° | 2.02 | 1.81 |
| 932-0195 | 61CA5F | For shielded and extended barrel plugs, 5 contacts at 240° | 2.21 | 1.93 |
| 932-0196 | 61CB6F | For shielded and extended barrel plugs, 6 contacts at 240° | 2.72 | 2.35 |
| 932-0197 | 62CB7F | For shielded and extended barrel plugs, 7 contacts at 270° | 2.63 | 2.28 |
| 932-0199 | 62GB8F | For shielded and extended barrel plugs, 8 contacts at 270° | 3.38 | 2.93 |

*Flared solder terminals.

Phone Jacks and Plugs



Type 3501FP for front panel mount in 0.25" (6.35 mm) holes in panels up to 0.125" thick. Type 3501FR for rear panel mount in 0.375" hole in panels up to 0.203" thick. Type 3502 has unique cable clamp with 0.406" O.D. shielded removable handle. Type 3503 extension jack has shielded removable handle 0.406" O.D. with cable clamp. Series 3558 are phone plugs with cable clamp and "snap-on" color-coded plastic handles in red, black, and white.

| Stock No. | Mr.'s Type | No. of Conductors | Description | EACH | | |
|-----------|------------|-------------------|---------------------|------|-------|-------|
| | | | | 1-9 | 10-24 | 25-99 |
| 932-1011 | 3501F | 2 | Phone jack | 1.59 | 1.38 | 1.25 |
| 932-3502 | 3501FP | 2 | Front of panel jack | 1.18 | .94 | .79 |
| 932-3503 | 3501FR | 2 | Rear panel jack | 1.33 | 1.15 | 1.04 |
| 932-1029 | 3502 | 2 | Shielded plug | 1.46 | 1.21 | 1.10 |
| 932-1012 | 3503 | 2 | Extension plug | 2.33 | 1.86 | 1.58 |
| 932-1098 | 35581 | 2 | Red plug | 1.36 | 1.17 | 1.05 |
| 932-1099 | 35582 | 2 | Black plug | 1.36 | 1.06 | .92 |
| 932-1097 | 35585 | 2 | White plug | 1.63 | 1.41 | 1.29 |
| 932-1026 | 3502A | 2 | Shielded plug | 1.82 | 1.59 | 1.44 |

Dual Video Jacks

The HD Series is a new video jack designed to meet the SMPTE 292M specification for high definition signal patching. A rugged diecast housing optimizes RFI shielding, while increasing optimal frequency response. The SD Series features the same rugged diecast housing, but offers a narrower bandwidth, up to 750 MHz.

| Stock No. | Mr.'s Type | Description | EACH | |
|-----------|------------|-------------|------|-------|
| | | | 1-9 | 10-24 |