








USED ON													—		
TOOL NUMBER  -1 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 						CONTACT DESCRIPTION (loose piece color code)	APPLIC. SPECIF.	
							LOOSE PIECE 			STRIP FORM 					
91505-1	0.2 - 0.6 [24-20]	1.14 - 1.78 [.045-.070]	YES	NO	3.96 ± 0.38 [.156 ± .015]	1.01 ± 0.05 [.039 ± .002]	66103-[] 66400-[] 164163-[]	66105-[] 163086-[]	66399-[] 163088-[] 170246-[] 170248-[] 66702-[]	66102-[] 66332-[] 164160-[]	66104-[] 163085-[]	66331-[] 163087-[] 170245-[] 170247-[] 66671-[] 66672-[]	Type III+ (yellow)	114-10004	
91505-3	0.8 - 1.4 [18-16]	2.03 - 2.54 [.080-.100]				1.30 ± 0.05 [.051 ± .002]	66099-[] 164164-[] 66589-[]	66101-[] 163082-[] 164839-[] 170244-[] 66590-[]	163084-[] 164840-[] 170242-[]	66098-[] 164161-[] 66579-[]	66100-[] 163081-[] 163766-[] 170243-[] 66580-[]	163083-[] 163767-[] 170241-[]	Type III+ (blue and violet)	114-10004	
												Type VI	114-10007		
91515-1	0.05 - 0.38 [30-22]	1.02-1.91 [.040-.075]	NO	NO	3.50-4.75 [.140-.187]	0.79 ± 0.05 [.031 ± .002]	61173-[]	61174-[]		350078-[]	350079-[]		COMMERCIAL M-N-L	114-1012	
	91515-3	0.08 - 0.24 [28-24]					0.89-1.40 [.035-.055]	66107-[] 163092-[] 66595-[]	66109-[] 164163-[] 66596-[]	163090-[] 170250-[] 170252-[]	66106-[] 163091-[] 66585-[]	66108-[] 164160-[] 66586-[]	163089-[] 170249-[] 170251-[]	Type III+ (red)	114-10004
		0.2 - 0.6 [24-20] 0.05 - 0.15 [30-26]				1.14-1.78 [.045-.070]	1.003 ± 0.051 [.0395 ± .002]	66103-[] 163088-[] 66428-[] 66593-[]	66105-[] 164162-[] 66429-[] 66594-[]	163086-[] 170246-[] 170248-[]	66102-[] 163087-[] 66424-[] 66583-[]	66104-[] 164159-[] 66425-[] 66584-[]	163085-[] 170245-[] 170247-[]	Type III+ (yellow & brown)	114-10004
												Type VI	114-10007		
91519-1	0.8 - 1.4 [18-16]	2.03-2.54 [.080-.100]	YES	NO	3.96 ± 0.38 [.156 ± .015]	1.30 ± 0.05 [.051 ± .002]	66360-[] 66361-[]			66358-[] 66359-[]			Type III+	114-10004	
91519-3	1.9 - 2.1 [14]					1.73 ± 0.05 [.068 ± .002]									
91521-1	0.8 - 1.4 [18-16]	2.79-3.81 [.110-.150]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.30 ± 0.05 [.051 ± .002]	66601-[] 66602-[]			66598-[] 66597-[]			Type III+	114-10004	
91521-3	1.9 - 2.1 [14]					1.73 ± 0.05 [.068 ± .002]	213603-2 213603-4			213603-1 213603-3					
91523-1	0.2 - 0.6 [24-20]	2.03-2.54 [.080-.100]	NO	NO	3.56-4.75 [.140-.187]	0.99 ± 0.05 [.039 ± .002]	66400-[] 66399-[]			66332-[] 66331-[]			Type III+ (yellow)	114-10004	
	91523-3					0.8 - 1.4 [18-16]	1.30 ± 0.05 .051 ± .002]	163082-[] 163084-[] 66589-[]	164164-[] 66099-[] 66590-[]	66101-[] 170242-[]	163081-[] 163083-[]	164161-[] 66098-[] 66579-[]	66100-[] 170241-[]	Type III+ (blue)	114-10004
															Type VI
91542-1	0.2 - 0.35 [24-22]	1.52-3.43 [.060-.135]	YES	NO	3.96 ± 0.38 [.156 ± .015]	0.89 ± 0.08 [.035 ± .003]	66565-[] 66566-[]			66563-[] 66564-[]			Type III+ (yellow)	114-10004	
91542-3	2X 0.2 OR 0.56 [2X 24 OR 20]					0.99 ± 0.08 [.039 ± .003]									
91550-1	0.8 - 1.4 [18-16]	2.03-3.43 [.080-.135]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.30 ± 0.05 [.051 ± .002]	66587-[] 66588-[]			66577-[] 66578-[]			Type VI	114-10007	
	91550-3					1.9 - 2.1 [14]	1.73 ± 0.05 [.068 ± .002]								

⚠ LIST OF APPLIED CONTACT PART NUMBERS
MAY NOT BE COMPLETE AND IS SUBJECT
TO CHANGE. FOR CURRENT INFORMATION
ON TERMINAL PART NUMBERS, CONTACT
THE TOOLING ASSISTANCE CENTER :
1-800-722-1111.

2. AMP and CERTI-CRIMP are trademarks.

③ -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.










CERTI-CRIMP II DATA SHEET

[illegible]

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED IN THE DRAWING. IT IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT PERMISSION IN WRITING FROM TE CONNECTIVITY.

DWG NO. 1583004

THIS DRAWING IS A CONTROLLED DOCUMENT.

USED ON												
TOOL NUMBER  -1 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 				CONTACT DESCRIPTION (loose piece color code)	APPLIC. SPECIF.
							LOOSE PIECE 		STRIP FORM 			
91564-1 91564-3	0.20-0.56 [24-20]	1.02-2.03 [.040-.080]	NO	NO	3.55-4.75 [.140-.187]	1.00 ± 0.05 [.039 ± .002]	66103-[] 66593-[] 66596-[]	66102-[] 66583-[] 66586-[]	Type III+ (yellow) (red)	114-10004		
	0.05-0.15 [30-26]	1.02-1.52 [.040-.060]					66105-[] 170246-[] 66594-[]	66104-[] 170245-[] 66584-[]				
	0.12-0.22 [26-24]	0.89-1.40 [.035-.055]					66429-[] 170248-[] 66595-[] 66428-[]	66425-[] 170247-[] 66585-[] 66424-[]				
2844982-1	0.30 [22]	1.27-2.79 [.050-.110]	NO	NO	4.37 [.172]	0.94 ± 0.05 [.037 ± .002]	66591-[]		66581-[]		TYPE VI INSULATION GRIP CONTACTS	114-10007
	0.60-0.80 [20-18]	1.27-2.79 [.050-.110]					66592-[]		66582-[]			

- ⚠ LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.
2. AMP and CERTI-CRIMP are trademarks.
- ⚠ -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.
4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

DWG: 21FEB2012		MATERIAL: -	HEAT TREAT: -
CHK: 22FEB2012		B.A. WOLFE	
APVD: 22FEB2012		B.A. WOLFE	
NAME: CERTI-CRIMP II TOOL DATA SHEET			
SCALE: -			
SIZE: A1			
DRAWING NO: 1583004			
SHEET: 2 of 2			
REV: D1			

P	LTR	REVISION RECORD	DATE	DWN	APVD
-	SEE SHEET 1	-	-	-	-

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC	± .	0 PLC	± .
1 PLC	± .	1 PLC	± .
2 PLC	± .	2 PLC	± .
3 PLC	± .	3 PLC	± .
4 PLC	± .	4 PLC	± .

ANGLES: ±	-
SURFACE TEXTURE	✓