

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

V2





REFERENCE FOR OVERALL PITCH DIMENSION CORRECTED

09MAR2017

SS

PS

PART NUMBER BOX PACKAGING	PART NUMBER REEL PACKAGING	NO OF POS "n"	DIMENSION "A" MAX
7-215083-4	215083-4	4	8,6
7-215083-6	215083-6	6	11,1
7-215083-8	215083-8	8	13,6
8-215083-0	1-215083-0	10	16,2
8-215083-2	1-215083-2	12	18,7
8-215083-4	1-215083-4	14	21,3
8-215083-6	1-215083-6	16	23,8
8-215083-8	1-215083-8	18	26,3
9-215083-0	2-215083-0	20	28,9
9-215083-4	2-215083-4	24	34,0



NOTES;

1. SHOWN IS A 10 POSITION CONNECTOR


2. FOR FLAT RIBBON CABLE REQUIREMENTS.
SEE APPLICATION SPEC 114-19016.

3. CONNECTOR-HEIGHT AFTER CABLE TERMINATION 5.1 mm AVERAGE.
DEPENDING ON PROCESSING, SEE APPLICATION SPEC 114-19016.

250 CONNECTORS PER BOX
BOX PACKAGING

2500 CONNECTORS PER REEL
REEL PACKAGING

--	GLASS FILLED POLYESTER (RED)	HOUSING	3
TIN OVER NICKEL PLATING	PHOSPHOR BRONZE	MALE CONTACT	2
--	GLASS FILLED POLYESTER (RED)	COVER	1
FINISH	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P.V.Tongerren	-	TE Connectivity					
DIMENSIONS: mm		CHK H SPELDE	24-08-01						
		APVD H SPELDE	24-08-01						
		NAME Micro-MaTch MALE-ON-WIRE CONNECTOR -							
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-19052	APPLICATION SPEC 114-19016	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO -		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		WEIGHT -		A3	00779	C-215083			
MATERIAL SEE TABLE		FINISH SEE TABLE							
Customer Drawing				SCALE	5:1	SHEET	1 OF 1	REV	V2