

VM15LCD 15" monitor
VM17LCD 17" monitor
VM19LCD 19" monitor

Features

- Displays up to 16.7 million colors
- Convenient front controls for on-screen programming
- Stereo speakers
- Input signal detection provides easy connection
- Regulated 12VDC 4A (UL & CSA listed power supply included)
- 1 year warranty



Specifications

	VM15LCD	VM17LCD	VM19LCD
Screen	15" TFT	17" TFT	19" TFT
Resolution	1024 (H) x 768 (V) SXGA	1280 (H) x 1024 (V) SXGA	1280 (H) x 1024 (V) SXGA
Aspect Ratio	4:3	4:3	4:3
Viewing Angle	170° (H) 160° (V)	170° (H) 160° (V)	170° (H) 160° (V)
Viewing Lines	500 TV lines	500 TV lines	500 TV lines
Contrast Ratio	800:1	800:1	800:1
Response time	6ms	6ms	6ms
3D Comb Filter w/De-interlace	2D	2D	2D
3D Noise Reduction	3D	3D	3D
Brightness	270cd/m2	270cd/m2	270cd/m2
Speakers	2 each (2.5 watts)	2 each (2.5 watts)	2 each (2.5 watts)
Composite Inputs/Outputs	BNC x 1 / BNC x 1	BNC x 1 / BNC x 1	BNC x 1 / BNC x 1
VGA	VGA x 1	VGA x 1	VGA x 1
DVI	DVI x 1	DVI x 1	DVI x 1
Audio Inputs	Stereo PC / Audio R & L	Stereo PC / Audio R & L	Stereo PC / Audio R & L
Audio Adjustment	Yes	Yes	Yes
Wall Hanging	VESA standard	VESA standard	VESA standard
Vesa Size	100 x 100mm	100 x 100mm	100 x 100mm
Stand and Bezel	Plastic	Plastic	Plastic
OSD Control	Yes	Yes	Yes
OSD Language	English, Spanish, French, German, Portuguese, Russian, Italian and Simplified Chinese		
Operating Temperature	32° F - 122° F	32° F - 122°	32° F - 122° F
Power Consumption	20W	30W	40W
Power Supply	12VDC/4A (included)	12VDC/4A (included)	12VDC/4A (included)
Screen Dimensions	14.5" (W) x 12.25" (H) x 2.5" (D)	15.25" (W) x 13" (H) x 2.5" (D)	16.5" (W) x 14" (H) x 2.5" (D)
Dimensions with Base	14.5" (W) x 13.75" (H) x 6" (D)	15.25" (W) x 14.5" (H) x 6" (D)	16.5" (W) x 15.5" (H) x 6" (D)
Weight	7.3 lbs.	10.8 lbs.	12.1 lbs.

Power cord, adapter, user's guide and audio cable included in the box with all monitors.
Safety includes Energy Star, FCC-DOC, CE, RoHS

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation. Rev. 10/18/11

For more information contact Speco Technologies
200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com