



| LOC | DIST | REVISIONS |     |                           |           |     |      |
|-----|------|-----------|-----|---------------------------|-----------|-----|------|
|     |      | P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
| GP  | 00   |           | K   | REVISED PER ECO-11-012231 | 12SEP2011 | CJV | CWR  |



1. FOR MINI APPLICATOR.
2. FOR HAND TOOL USE ONLY.
3. WIRE RANGE OF 22-28, INSULATION RANGE OF .030-.040.
4. GOLD PLATING PER MIL-G-45204, NICKEL PLATING PER QQ-N-290, TIN PLATING PER MIL-T-10727.
5. GOLD PLATED IN LOCALIZED GOLD PLATED AREA, 000030 MIN GOLD IN MATED AREA, .000100 MIN TIN IN WIRE & INSULATION BARRELS, BOTH OVER .000050 MIN NICKEL.
6. GOLD FLASH IN LOCALIZED GOLD PLATE AREA, .000100 MIN TIN IN WIRE & INSULATION BARRELS, BOTH OVER .000030 MIN NICKEL.
7. .000050 MIN GOLD OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
8. GOLD PLATED IN LOCALIZED GOLD PLATED AREA, 000015 MIN GOLD IN MATED AREA, .000100 MIN TIN IN WIRE & INSULATION BARRELS, BOTH OVER .000050 MIN NICKEL.
9. GOLD PLATING ON THE CARRIER STRIP IS NOT REQUIRED.

|                        |                     |            |   |   |   |             |            |
|------------------------|---------------------|------------|---|---|---|-------------|------------|
| SUPERSEDED BY 748333-2 |                     | STANDARD   | 8 | 9 | 1 | STRIP       | 1-748333-5 |
| OBSOLETE               |                     | SMALL PACK | 5 |   | 2 | LOOSE PIECE | 1-748333-4 |
|                        |                     | STANDARD   | 7 | 9 | 1 | STRIP       | 748333-9   |
| OBSOLETE               | AMP BRAZIL USE ONLY | STANDARD   | - |   | 1 | STRIP       | 748333-8   |
| OBSOLETE               |                     | STANDARD   | 6 |   | 2 | LOOSE PIECE | 748333-7   |
| OBSOLETE               |                     | STANDARD   | 6 |   | 1 | STRIP       | 748333-5   |
| OBSOLETE               |                     | STANDARD   | 5 |   | 2 | LOOSE PIECE | 748333-4   |
| OBSOLETE               |                     | STANDARD   | 5 |   | 1 | STRIP       | 748333-2   |

| PACKAGING TYPE                         |  | FINISH                 | USE                                                                    | TYPE      | PART NUMBER  |
|----------------------------------------|--|------------------------|------------------------------------------------------------------------|-----------|--------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN C.RICHARD 09/25/86 | TE Connectivity                                                        |           |              |
| DIMENSIONS: INCHES                     |  | CHK S.WELDON 09/26/86  | NAME                                                                   |           |              |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | APVD -                 | PRODUCT SPEC                                                           |           |              |
| 0 PLC ± -                              |  | APPLICATION SPEC       | PIN CONTACT, SIZE 22 DF, 22-28 AWG, W/.030-.040 DIA INSULATION SUPPORT |           |              |
| 1 PLC ± -                              |  | APVD -                 | SIZE                                                                   | CAGE CODE | DRAWING NO   |
| 2 PLC ± -                              |  | APVD -                 | A2                                                                     | 00779     | C-748333     |
| 3 PLC ± .005                           |  | APVD -                 | SCALE                                                                  | 10:1      | SHEET 1 of 1 |
| 4 PLC ± -                              |  | APVD -                 | REV                                                                    | K         |              |
| ANGLES ± -                             |  | APVD -                 | CUSTOMER DRAWING                                                       |           |              |
| FINISH                                 |  | WEIGHT -               | RESTRICTED TO                                                          |           |              |
| MATERIAL BRASS PER MIL-C-50            |  | SEE TABLE, NOTE 4      |                                                                        |           |              |