

AUTOMOTIVE, TRUCK, BUS, & OFF-ROAD HOUSINGS



✓ Active

TE CONNECTIVITY (TE) MQS PIN HSG 2POS

AMP | MQS

1-1534155-1
TE Internal Number: 1-1534155-1

EU RoHS Compliant
EU ELV Compliant

Connector Style Housing for male terminals

Mating Tab Width .63 mm [.025 in]

Connector System Wire-to-Wire

Number of Positions 2

Sealable No

 **PRODUCT DRAWING**
English

 **3D PDF**

DOCUMENTATION

Product Drawings

PIN HOUSING, 2 POSN., MQS Stiftgeh., 2 Pol., MQS

PDF (TIFF AVAILABLE)

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

3D

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Housing for male terminals

Connector System Wire-to-Wire

Sealable No

Hybrid Connector No

Primary Locking Feature On the terminal

Strain Relief No

Configuration Features

Number of Positions 2

Number of Rows 1

Electrical Characteristics

Nominal Voltage Architecture (V) 12

Operating Voltage (VDC) 12

Body Features

Color Black

Cable Exit Angle 180°

Body Material PBT GF

Contact Features

Mating Tab Width .63 mm [.025 in]

Mechanical Attachment

Mounting Feature No

Terminal Position Assurance Yes

Polarized Yes

Dimensions

Width 28.8 mm [1.134 in]

Height 11.2 mm [.441 in]

Usage Conditions

Operating Temperature Range -40 – 80 °C [-40 – 176 °F]

Operation/Application

Circuit Application Signal

Industry Standards

Degree of Protection Other

UL Flammability Rating UL 94-HB

Packaging Features

Packaging Method Package

Other

Connector Position Assurance Capable No

Serviceable Yes

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
