

TAA Compliant SmartPro Tower UPS System - Intelligent line-interactive network power management system

MODEL NUMBER: **SMART2200SLTAA**



Description

The SMART2200SLTAA is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. 2200VA line-interactive tower UPS system for server, networking and telecommunications equipment. Upright tower form factor. Offers sine wave 120V nominal output in both AC and battery modes. Switches to battery-derived AC output during power failures and extreme voltage variations. Line-interactive automatic voltage regulation (AVR) provides voltage boost/cut during brownouts/overvoltages to maintain regulated 120V nominal output over an input voltage range of 83-145V. Includes NEMA 5-20P input plug and 7 UPS-supported (6 x 5-15/20R & 1 L5-20R) output receptacles. Network-grade AC surge and noise suppression. Network management interfaces support simultaneous communications via USB port, DB9 serial port and SNMPWEBCARD slot. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Supports simultaneous detailed monitoring of equipment load levels, self-test data and utility power conditions via all three network interfaces. Includes PowerAlert power management software and complete cabling. Three-stage metered current monitoring and battery charge status LEDs. Utility power and voltage regulation, and battery warning LEDs. Audible alarm. Self-test. Field-replaceable, hot-swappable internal batteries. Attractive all-black color scheme. \$250,000 [connected equipment insurance](#); (U.S., Canada, and Puerto Rico only).

Features

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- SmartPro line-interactive UPS system is ideal for voice, data, medical and industrial networking applications
- Line-interactive voltage regulation maintains selectable 120V nominal output during brownouts as low as 83V and overvoltages to 145V
- Enables continuous operation through blackouts, voltage fluctuations and surges
- Line-interactive automatic voltage regulation (AVR) provides 12% and 24% voltage boost during brownouts and a 12% voltage cut during overvoltages
- Standard internal battery set offers 13 min. runtime at half load (800W) and 5 min. at full load (1600W)
- Space-saving upright tower format
- Network interfaces support simultaneous communications via built-in USB port, DB9 serial port and SNMPWEBCARD slot
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Included PowerAlert power management software supports safe unattended shutdown, monitoring and control via local connected servers, plus any

Highlights

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- 2.2kVA / 2200VA line interactive tower UPS; Sine wave output
- 120V nominal output during brownouts to 83 and overvoltages to 145V
- USB, RS232, EPO and slot for optional SNMP/Web card
- Front panel status LEDs with detailed load and battery capacity display
- NEMA 5-20P input; 6 NEMA 5-15/20R & 1 L5-20R outlets

Package Includes

- SMART2200SLTAA TAA Compliant UPS System
- PowerAlert Software and cabling
- Owner's manual with warranty information

number of additional servers over IP

- UPS interface supports on-battery, low-battery, power-restored, AC-voltage, DC-voltage, output current monitoring, battery charge current, battery capacity, timed inverter shutoff, activate self-test and output power control
- NEMA 5-20P input plug/6 x NEMA 5-15R and 1 x NEMA L5-20R output receptacles
- Front panel LEDs provide current monitoring, voltage regulation, battery charge level, and battery warning information
- UPS ships fully assembled in full compliance with DOT regulations; no time-consuming connection of internal batteries by user required
- \$250,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only)

Specifications

General Info	
Product Group	UPS SYSTEMS
OUTPUT	
Output Volt Amp Capacity (VA)	2200
Output kVA Capacity (kVA)	2.2
Output Watt Capacity (Watts)	1600
Output kW Capacity (kW)	1.6
Power Factor	0.7
Nominal Output Voltage(s) Supported	120V
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-18% / +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
UPS Output Receptacles	6 5-15/20R outlet(s); 1 L5-20R outlet(s)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
INPUT	
Rated input current (Maximum Load)	14.8A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-20P
Input Circuit Breakers	20A
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3
Recommended Electrical Service	20A 120V

Input Phase	Single-Phase
BATTERY	
Full Load Runtime (min.)	5 min. (1600w)
Half Load Runtime (min.)	13 min. (800w)
DC System Voltage (VDC)	48
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90%
Internal UPS Replacement Battery Cartridge	RBC54
Battery Access	Battery access door
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83V to overvoltages to 145V
Overvoltage Correction	Input voltages between 127 and 145 are reduced by 12%
Undervoltage Correction	Input voltages between 96 and 108V are boosted by 12%
Severe Undervoltage Correction	Input voltages between 83 and 95V are boosted by 24%
LEDS ALARMS & SWITCHES	
LED Indicators	9 LEDs indicate line power, battery power, AVR, overload and replace battery status - with a 3-LED level meter for load and battery charge level
Audible Alarm	Audible alarm indicates power failure and overload conditions
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	570
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Installation Form Factors Supported with Included Accessories	Tower
Primary Form Factor	Tower
UPS Power Module Dimensions (hwd, in.)	10.5 x 8.9 x 12.5

UPS Power Module Dimensions (hwd, cm)	26.7 x 22.5 x 31.8
UPS Power Module Weight (lbs.)	57
UPS Power Module Weight (kg)	25.9
UPS Shipping Dimensions (hwd / in.)	14.5 x 13.8 x 18
UPS Shipping Dimensions (hwd / cm)	36.8 x 34.9 x 45.7
Shipping Weight (kg)	0
Cooling Method	Fan
UPS Housing Material	Steel
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	286.3
Battery Mode BTU / Hr. (Full Load)	885.6
AC Mode Efficiency Rating (100% Load)	95%
Audible Noise	Audible Noise < 50 dBA at Front Side 1 Meter
COMMUNICATIONS	
Communications Interface	USB; DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	Included
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	83
High Voltage Transfer to Battery Power (Setpoint)	145
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries

Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI); ROHS (Restriction of Hazardous Substances); TAA Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.