




Features

- Wirewound and Hybritron® elements
- High rotational life
- Optional 0.15 % linearity
- Optional A/R lug
- RoHS compliant*
- Suitable for use under side load
- Designed for HMI and MMI applications
- Dual gang option
- Servo mount option

3548 - 5-Turn Precision Potentiometer

Electrical Characteristics ¹	Wirewound Element	Hybritron® Element
Standard Resistance Range.....	500 to 50K ohms.....	1K to 10K ohms
Total Resistance Tolerance.....	±3 %.....	±10 %
Independent Linearity.....	±0.25 %.....	±0.25 %
Independent Linearity (Maximum Practical).....	±0.15 %.....	±0.15 %
Effective Electrical Angle.....	1800 ° +10 °, -0 °.....	1800 ° +10 °, -0 °
Absolute Minimum Resistance/End Voltage.....	1 ohm or 0.1 % maximum (whichever is greater)	0.4 % maximum
Noise/Output Smoothness.....	100 ohms maximum.....	0.15 % maximum
Max. Wiper Current @ 5K ohms.....	20 mA.....	10 mA
Dielectric Withstanding Voltage (MIL-STD-202, Method 301)		
Sea Level.....	1,000 VAC minimum.....	1,000 VAC minimum
Insulation Resistance (500 VDC).....	1,000 megohms minimum.....	1,000 megohms minimum
Resolution.....	See How to Order chart.....	Essentially infinite
Power Rating (Voltage Limited By Power Dissipation)		
+70 °C.....	1.5 watts.....	1.5 watts
+125 °C.....	0 watt.....	0 watt

Environmental Characteristics ¹		
Operating Temperature Range		
Dynamic.....	-40 °C to +125 °C.....	-40 °C to +125 °C
Static.....	-55 °C to +125 °C.....	-55 °C to +125 °C
Temperature Coefficient (Over Static Temperature Range).....	±50 ppm/°C.....	±100 ppm/°C
Temperature Cycling (5 Cycles Over Static Temperature Range).....	±2 % TR shift max.....	±4 % TR shift max.
Vibration (15 Gs, 10 Hz to 2 kHz)		
Wiper Bounce.....	0.1 ms max.....	0.1 ms max.
Shock (100 Gs, 6 ms sawtooth)		
Wiper Bounce.....	0.1 ms max.....	0.1 ms max.
Load Life (1,000 hours @ 70 °C).....	±2 % TR shift max.....	±5 % TR shift max.
Rotational Life		
No Load.....	1,000,000 shaft revolutions.....	2,500,000 shaft revolutions
Powered (MIL-PRF-12934).....	1,000,000 shaft revolutions.....	2,500,000 shaft revolutions
Moisture Resistance (Mil-Std-202, Method 103).....	±2 % TR shift max.....	±5 % TR shift max.
IP Rating.....	IP 50.....	IP 50

Mechanical Characteristics ¹	
Mechanical Angle.....	1800 ° +10 °, -0 °
Backlash.....	1.0 ° max.
Stop Strength.....	53 N-cm (75 oz.-in.) min.
Torque	
Starting.....	0.5 N-cm (0.7 oz.-in.) max.
Running.....	0.5 N-cm (0.7 oz.-in.) max.
Clutch.....	1.0 to 4.2 N-cm (1.5 to 6.0 oz.-in.)
Mounting.....	170-200 N-cm (15-18 in.-lb.) max.
Shaft Runout T.I.R.....	0.08 mm (0.003 in.)
Lateral Runout T.I.R.....	0.13 mm (0.005 in.)
Shaft End Play T.I.R.....	0.15 mm (0.006 in.)
Shaft Radial Play T.I.R.....	0.08 mm (0.003 in.)
Pilot Diameter Runout T.I.R.....	0.08 mm (0.003 in.)
Weight	
Single.....	19 gm (0.67 oz.) typ.
Dual.....	35 gm. (1.23 oz.) typ.
Shaft Side Load (Max. Allowable)	
Nickel Plated Brass Shaft w/Brass Bushing.....	50 gmf (1.7 ozf)
Stainless Steel Shaft w/Bronze Bushing.....	250 gmf (8.8 ozf)
Terminals.....	Gold-plated solder lugs
Soldering Condition	
Manual Soldering.....	96.5Sn/3.0Ag/0.5Cu solid wire or no-clean rosin cored wire, 370 °C (700 °F) max. for 3 seconds
Wave Soldering.....	96.5Sn/3.0Ag/0.5Cu solder with no-clean flux, 260 °C (500 °F) max. for 5 seconds
Wash processes.....	Not recommended
Mounting Hardware.....	One lockwasher and one mounting nut is shipped with each potentiometer
Recommended Panel Thickness (Bushing Mount).....	2.46-3.81 mm (0.097-0.150 in.)
Marking.....	Manufacturer's symbol, model number, product code and date code
Standard Packaging.....	Plastic trays (5 pcs./tray)

¹At room ambient: +25 °C nominal and 50 % relative humidity nominal, except as noted.

For other options, please consult factory.

*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.


Users should verify actual device performance in their specific applications.

3548 - 5-Turn Precision Potentiometer

BOURNS®



Product Dimensions

Single Gang, Bushing Mount



Bushing Selection Code	Shaft Dimension "A"	Shaft Material	Bushing Type "B"	Bushing Material
A	6.34 ± 0/-0.022 (0.2497 ± 0/-0.0009)	Nickel Plated Brass	3/8" 32-UNEF- 2A THD.	Brass
B	6.00 ± 0/-0.022 (0.2362 ± 0/-0.0009)	Nickel Plated Brass	M9 X 0.75-8g	Brass
C	6.34 ± 0/-0.007 (0.2497 ± 0/-0.0003)	Stainless Steel	3/8" 32-UNEF- 2A THD.	Bronze
D	6.00 ± 0/-0.007 (0.2362 ± 0/-0.0003)	Stainless Steel	M9 X 0.75-8g	Bronze
G	6.34 ± 0/-0.007 (0.2497 ± 0/-0.0003)	Stainless Steel	3/8" 32-UNEF- 2A THD.	Bronze
H	6.00 ± 0/-0.007 (0.2362 ± 0/-0.0003)	Stainless Steel	M9 X 0.75-8g	Bronze

Dual Gang, Bushing Mount





Specifications are subject to change without notice.
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
Users should verify actual device performance in their specific applications.

3548 - 5-Turn Precision Potentiometer

BOURNS®



Product Dimensions

Single Gang, Servo Mount



TOLERANCES: EXCEPT WHERE NOTED
 DECIMALS: .XX ± (.02) .XXX ± (.005) .XXXX ± (.0005)
 DIMENSIONS: $\frac{\text{MM}}{(\text{IN})}$

Dual Gang, Servo Mount




Specifications are subject to change without notice.
 The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
 Users should verify actual device performance in their specific applications.

3548 - 5-Turn Precision Potentiometer

BOURNS®

Panel Thickness Dimensions

(For Bushing Mount Only)



Anti-rotation pin hole is shown at six o'clock position for reference only. The actual location is determined by the customer's application. Refer to the front view of the potentiometer to see the location of the optional A/R pin.

Panel thickness and hole diameters are recommended for best fit. However, customers may adjust the dimensions to suit their specific application.

DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$ TOLERANCES: $\pm \frac{0.127}{(.005)}$

How To Order

MODEL DESIGNATOR		ELEMENT TYPE		NO. OF SECTIONS		ANTI-ROTATION LUG		INDEPENDENT LINEARITY		RESISTANCE**	
Code	Description	Code	Description	Code	Description	Code	Description	Code	Description	Code	Resolution (%)
3548	5-Turn	H	Hybritron®	1	Single	A	None	A	0.25 %	102 (1K ohms)	—
		S	Wirewound	2	Dual	B	180 °	B	0.15 %	502 (5K ohms)	—
										103 (10K ohms)	—
										201 (200 ohms)	0.069
										501 (500 ohms)	0.054
										102 (1K ohms)	0.043
										202 (2K ohms)	0.044
										502 (5K ohms)	0.038
										103 (10K ohms)	0.029
										203 (20K ohms)	0.023
										503 (50K ohms)	0.017

* Anti-rotation lug is not available for servo mount versions.

** For Single gang, use only first three digits.
For Dual gang, use six digits separated by a "/".

BUSHING MOUNT						
Code	Shaft FMS	Shaft Dia.	Shaft Material	Bushing Dia.	Bushing Material	Slip Clutch
A	13/16 "	1/4 "	Nickel Plated Brass	3/8 "	Brass	N/A
B	20.6 mm	6 mm	Nickel Plated Brass	9 mm	Brass	N/A
C	13/16 "	1/4 "	Stainless Steel	3/8 "	Bronze	N/A
D	20.6 mm	6 mm	Stainless Steel	9 mm	Bronze	N/A
G	13/16 "	1/4 "	Stainless Steel	3/8 "	Bronze	Yes***
H	20.6 mm	6 mm	Stainless Steel	9 mm	Bronze	Yes***

SERVO MOUNT			
Code	Shaft FMS	Shaft Dia.	Shaft Material
E	3/8 "	1/8 "	Stainless Steel

*** Not available in dual gang version.

REV. 10/14

"Hybritron" is a registered trademark of Bourns, Inc.
Specifications are subject to change without notice.
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
Users should verify actual device performance in their specific applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[3548H-1AC-103A](#) [3548H-1AC-102B](#) [3548H-1AC-103B](#) [3548H-1AC-502B](#) [3548S-1AA-102A](#) [3548S-1AA-102B](#)
[3548S-1AA-103A](#) [3548S-1AA-103B](#) [3548S-1AA-202A](#) [3548S-1AA-203B](#) [3548S-1AA-502A](#) [3548H-1BA-103B](#) [3548S-](#)
[1BB-102B](#) [3548H-1AA-102B](#) [3548S-1AC-103B](#) [3548S-1AA-503B](#) [3548S-1BA-103B](#) [3548S-1AC-102B](#) [3548S-1BA-](#)
[202A](#) [3548S-1AC-103A](#) [3548S-1BA-502B](#) [3548S-2AA-502/502B](#) [3548H-1AB-502B](#) [3548S-1BA-102B](#) [3548H-1AA-](#)
[502A](#) [3548S-1AB-502A](#) [3548H-1AA-103B](#) [3548H-1AA-102A](#) [3548S-1BD-503B](#) [3548H-1AB-502A](#) [3548H-1AA-103A](#)
[3548H-1AE-502B](#)