




AC Adapter 12VDC/1500mA

412-112153

Dimensions: mm (in.)



■ Mechanical Specifications:

- Primary voltage: 120VAC 60Hz 50W
- Secondary voltage(±5%): 16.7VDC(no load); 12VDC @ 1500mA (full load)
- Exciting current, open circuit: 65mA max.(no load); 180mA max. (full load)
- DC resistance: 15%:17Ω
- Insulation resistance: 100MΩ 500VDC
- Dielectric strength: Primary-secondary: 1500VAC for 1 minute; Primary-core: 1500VAC for 1 minute; Secondary-core: 500VAC for 1 minute
- Cord length: 6ft.

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

412-112153